



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____

Title:
TYPICAL SCHEMATIC DIAGRAM 3 PHASE(DIR) E8 70/P+9I/P
RS485 COMMS ARGUS 2 NUMERIC OVERCURRENT PROTECTION

First used on: _____

Similar Articles: 2434W10064

Supersedes: _____

Treatment: _____

SIEMENS PROTECTION DEVICES LTD.

Original Scale.

NTS

Drng. No.

2434W10122

1	12/02/07	CHANGE NOTED
ISSUE	DATE	NOTED