



MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.  
 Machine where marked ✓  
 For explanation of dimensions, tolerances, notes etc. see B.S.308.  
 Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
 Limits on untoleranced machined dimensions to B.S.4500;  
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
 over 6 to 30±0.2; over 120 to 315±0.5;  
 General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_  
 Treatment: \_\_\_\_\_

Title: TYPICAL SCHEMATIC DIAGRAM FOR 2 PHASE + EARTH FAULT NUMERIC OVERCURRENT PROTECTION (ARGUS 1) EPSILON

**Reyrolle Protection Hebburn.**

Original Scale: NTS

First used on: \_\_\_\_\_  
 Similar Articles: 2434W10030  
 Supersedes: \_\_\_\_\_  
 Drg. No. 2434W10052

3	RDW	28/03/06	MN993/2793
2		18/4/02	MN434/2292
1		22/11/99	CHANGE NOTED
ISSUE		DATE	