



NOTES

1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.

2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.

3 FOR TERMINAL DIAGRAM SEE 2716W20001 (A2)

4 DRG SHOWS OPTION A (7 OUTPUTS, 1 INPUT)
DRG SHOWS OPTION B (11 OUTPUTS, 5 INPUTS)

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____
Treatment: _____

Title: TYPICAL SCHEMATIC DIAGRAM FOR 2P+E/F+SEF (RESIDUAL CONNECTION) NUMERIC O/C PROTECTION (ARGUS 1) EPSILON E6 CASE

Reyrolle Protection
Hebburn.

Original Scale: NTS

First used on: _____
Similar Articles: 2434W10019
Supersedes: _____
Drg. No. 2434W10079