

SIEMENS



Cross-reference Guide


Type VBII Safety Switches

usa.siemens.com/safetyswitches



General Duty 240 Volt, Type 1 (Indoor)

System	Ampere Rating	VBII	Vacu-Break®	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 240V, Fusible							
	30	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch
	60						DG224FGK
	100						DG225FGK
	200						DG226FGK
	400						
600							
2-Pole, 3-Wire, 240V, Fusible							
	30	GF221N	JN321	GHN321N	TG3221	D221N	DG221NGB
	60	GF222N	JN322	GHN322N	TG3222	D222N	DG222NGB
	100	GF223N	JN323	GHN323N	TG3223	D223N	DG223NGB
	200	GF224N	JN324	GHN324N	TG3224	D224N	DG224NGK
	400	GF225NA	JN325	GHN325N	TG3225	D225N	DG225NGK
600	GF226NA	JN326	GHN326N	TG3226	D226N	DG226NGK	
3-Pole, 3-Wire, 240V, Fusible							
	30	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch
	60						DG324FGK
	100						DG325FGK
	200				DG326FGK		
	400						
600							
3-Pole, 4-Wire, 240V, Fusible							
	30	GF321N	JN421	GHN421N	TG4321	D321N	DG321NGB
	60	GF322N	JN422	GHN422N	TG4322	D322N	DG322NGB
	100	GF323N	JN423	GHN423N	TG4323	D323N	DG323NGB
	200	GF324N	JN424	GHN424N	TG4324	D324N	DG324NGK
	400	GF325NA	JN425	GHN425N	TG4325	D325N	DG325NGK
600	GF326NA	JN426	GHN426N	TG4326	D326N	DG326NGK	
3-Pole, 3-Wire, 240V, Non-Fusible							
	30	GNF321	JU321	GUN321	TGN3321	DU321	DG321UGB
	60	GNF322	JU322	GUN322	TGN3322	DU322	DG322UGB
	100	GNF323	JU323	GUN323	TGN3323	DU323	DG323UGB
	200	GNF324	JU324	GUN324	TGN3324	DU324	DG324UGK
	400	GNF325A	JU325	Use Heavy Duty Switch	TGN3325	DU325	DG325UGK
600	GNF326A	JU326	TGN3326		DU326	DG326UGK	



General Duty 240 Volt, Type 3R (Outdoor)

System	Ampere Rating	VBII	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 240V, Fusible							
	30	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch
	60						DG224FRK
	100						DG225FRK
	200						DG226FRK
	400						
600							
2-Pole, 3-Wire, 240V, Fusible							
	30	GF221NR	NR321	GHN321W	TG3222R	D221NRB	DG221NRB
	60	GF222NR	NR322	GHN322W	TG3221R	D222NRB	DG222NRB
	100	GF223NR	NR323	GHN323W	TG3223R	D223NRB	DG223NRB
	200	GF224NR	NR324	GHN324W	TG3224R	D224NRB	DG224NRK
	400	GF225NRA	NR325	GHN325W	TG3225R	D225NR	DG225NRK
600	GF226NRA	NR326	GHN326W	TG3226R	D226NR	DG226NRK	
3-Pole, 3-Wire, 240V, Fusible							
	30	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch
	60						DG325FRK
	100						
	200						
	400						
600							
3-Pole, 4-Wire, 240V, Fusible							
	30	GF321NR	NR421	GHN421NW	TG4321R	D321NRB	DG321NRB
	60	GF322NR	NR422	GHN422NW	TG4322R	D322NRB	DG322NRB
	100	GF323NR	NR423	GHN423NW	TG4323R	D323NRB	DG323NRB
	200	GF324NR	NR424	GHN424NW	TG4324R	D324NRB	DG324NRK
	400	GF325NRA	NR425	GHN425NW	1	D325NR	DG325NRK
600	GF326NRA	NR426	GHN426NW	1	D326NR	DG326NRK	
3-Pole, 3-Wire, 240V, Non-Fusible							
	30	GNF321R	NFR321	GUN321AW	TGN3321R	DU321RB	DG321URB
	60	GNF322R	NFR322	GUN322AW	TGN3322R	DU322RB	DG322URB
	100	GNF323R	NFR323	GUN323AW	TGN3323R	DU323RB	DG323URB
	200	GNF324R	NFR324	GUN324AW	TGN3324R	DU324RB	DG324URK
	400	Use Heavy Duty Switch	Use Heavy Duty Switch	Use Heavy Duty Switch	Use Heavy Duty Switch	Use Heavy Duty Switch	DG325UGK
600						DG326UGK	

¹ Use 3-Pole, 3-Wire Switch. Order separate neutral.



Heavy Duty 240 Volt, Type 1 (Indoor)

System	Ampere Rating	VBI	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer		
2-Pole, 2-Wire, 240V, Fusible									
	30	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	DH221FGK		
	60						Use 2-Pole 3-Wire Switch		
	100								
	200								
	400					H225	DH225FGK		
	600					H226	DH226FGK		
	800					H227	DH227FGK		
1200	H228	—							
2-Pole, 3-Wire, 240V, Fusible									
	30	HF221N	SN321	HHN321N	TH3221	H221N	DH221NGK		
	60	HF222N	SN322	HHN322N	TH3222	H222N	DH222NGK		
	100	HF223N	SN323	HHN323N	TH3223	H223N	DH223NGK		
	200	HF224N	SN324	HHN324N	TH3224	H224N	DH224NGK		
	400	HF225NA	SN325	HHN325N	TH3225	H225N	DH225NGK		
	600	HF226NA	SN326	HHN326N	TH3226	H226N	DH226NGK		
	800	HF227N	SN327L	HLN327N	1	H227N	DH227NGK		
1200	HF228N	SN328L	HLN328N	1	H228N	—			
3-Pole, 3-Wire, 240V, Fusible									
	30	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	—		
	60						DH322FGK		
	100						DH323FGK		
	200						DH324FGK		
	400						TH3325	H325	DH325FGK
	600						TH3226	H326	DH326FGK
	800						—	H327	DH327FGK
1200	—	H328	DH328FGK						
3-Pole, 4-Wire, 240V, Fusible									
	30	HF321N	SN421	HHN421N	TH4321	H321N	DH321NGK		
	60	HF322N	SN422	HHN422N	TH4322	H322N	DH322NGK		
	100	HF323N	SN423	HHN423N	TH4323	H323N	DH323NGK		
	200	HF324N	SN424	HHN424N	TH4324	H324N	DH324NGK		
	400	HF325NA	SN425	HHN425N	TH4325	H325N	DH325NGK		
	600	HF326NA	SN426	HHN426N	TH4326	H326N	DH326NGK		
	800	HF327N	SN427L	HHN427N	2	H327N	DH327NGK		
1200	HF328N	SN428L	HHN428N	2	H328N	DH328NGK			

1 Use 2-Pole, 2-Wire Switch. Order separate neutral.
 2 Use 3-Pole, 3-Wire Switch. Order separate neutral.



Heavy Duty 240 Volt, Type 3R (Outdoor)

System	Ampere Rating	VBII	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 240V, Fusible							
	30	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch	Use 2-Pole 3-Wire Switch
	60					H225R	DH225FRK
	100					H226R	DH226FRK
	200					H227R	1
	400					H228R	2
	600						
	1200						
2-Pole, 3-Wire, 240V, Fusible							
	30	HF221NR	NRH321	HHN321NW	TH3221R	H221NRB	DH221NRK
	60	HF222NR	NRH322	HHN322NW	TH3222R	H222NRB	DH222NRK
	100	HF223NR	NRH323	HHN323NW	TH3223R	H223NRB	DH223NRK
	200	HF224NR	NRH324	HHN324NW	TH3224R	H224NRB	DH224NRK
	400	HF225NRA	NRH325	HHN325NW	TH3225R	H225NR	DH225NRK
	600	HF226NRA	NRH326	HHN326NW	TH3226R	H226NR	DH226NRK
	800	HF227NR	NRH327L	3	4	H227NR	DH227NRK
1200	HF228NR	NRH328L	3	4	H228NR	DH228NRK	
3-Pole, 3-Wire, 240V, Fusible							
	30	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	Use 3-Pole 4-Wire Switch	DH321FRK
	60				TH3325R	H325R	DH322FRK
	100				TH3326R	H326R	DH323FRK
	200				—	H327R	DH324FRK
	400				—	H328R	DH325FRK
	600						DH326FRK
	800						DH327FRK
1200			DH328FRK				
3-Pole, 4-Wire, 240V, Non-Fusible							
	30	HF321NR	NRH421	HHN421NW	TH321R	H321NRB	DH321NRK
	60	HF322NR	NRH422	HHN422NW	TH322R	H322NRB	DH322NRK
	100	HF323NR	NRH423	HHN423NW	TH323R	H323NRB	DH323NRK
	200	HF324NR	NRH424	HHN424NW	TH324R	H324NRB	DH324NRK
	400	HF325NRA	NRH425	HHN425NW	5	H325NRB	DH325NRK
	600	HF326NRA	NRH426	HHN426NW	5	H326NRB	DH326NRK
	800	HF327NR	NRH427	3	5	H327NRB	DH327NRK
1200	HF328NR	NRH428	3	5	H328NRB	DH328NRK	

1 Use 2-Pole, 3-Wire Switch.

2 Use Two Poles of the 3-Pole, 3-Wire Switch.

3 Use 600V Heavy Duty Switch.

4 Use 2-Pole, 2-Wire Switch. Order separate neutral.

5 Use 3-Pole, 3-Wire Switch. Order separate neutral.



Heavy Duty 240 Volt, Type 4X (Stainless Steel)

System	Ampere Rating	VBII	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer	
2-Pole, 2-Wire, 240V, Fusible								
	30	HF221S	Use 2-Poles of the 3-Wire Switch	1	TH2221SS	H221DS	Use 2-Pole 3-Wire Switch	
	60	HF222S		1	TH2222SS	H222DS		
	100	HF223S		1	Use 2-Pole 3-Wire Switch	H223DS		
	200	HF224S		1		H224DS		
	400	1		—		H225DS		
	600	1		—	—	H226DS		—
	800	1		—	—	—		—
2-Pole, 3-Wire, 240V, Fusible								
	30	2	Use 2-Poles of the 3-Wire Switch Order sep. Neutral	3	TH3221SS	H221NDS	DH221NWK	
	60	2		3	TH3222SS	H222NDS	DH222NWK	
	100	2		3	TH3223SS	H223NDS	DH223NWK	
	200	2		3	TH3224SS	2	DH224NWK	
	400	3		—	TH3225SS	H225NDS	DH225NWK	
	600	3		—	TH3226SS	H226NDS	DH226NWK	
	800	3		—	—	—	DH227NWK	
3-Pole, 3-Wire, 240V, Fusible								
	30	HF321S	F321SS	3	TH3221SS	H321DS	DH321FWK	
	60	HF322S	F322SS	3	TH3222SS	H321DS	DH322FWK	
	100	HF323S	F323SS	3	Use 3-Pole 4-Wire Switch	H321DS	5	
	200	HF324S	F324SS	3		H321DS	DH324FWK	
	400	HF325SA	F325SS	—		H321DS	DH325FWK	
	600	HF326SA	F326SS	—	—	H321DS	DH326FWK	
	800	HF327S	F327SS	—	—	H321DS	DH327FWK	
3-Pole, 4-Wire, 240V, Fusible								
	30	Use 3-Pole 3-Wire Switch Order sep. Neutral	Use 3-Pole 3-Wire Switch Order sep. Neutral	4	TH321SS	H321NDS	DH321NWK	
	60			4	TH322SS	H322NDS ⁶	DH322NWK	
	100			4	TH323SS	H323NDS	DH323NWK	
	200			4	TH324SS	4	DH324NWK	
	400			4	TH325SS	4	DH325NWK	
	600			—	TH326SS	H327NDS	DH326NWK	

1 Use Two Poles of the 3-Pole, 3-Wire Switch.
 2 Use 2-Pole Switch. Order separate neutral.
 3 Use Two Poles of the 3-Wire Switch. Order separate neutral.

4 Use 3-Pole, 3-Wire Switch. Order separate neutral.
 5 Use 3-Pole, 4-Wire switch.
 6 DH328FWK (1200A) is also offered by Cutler Hammer.



Heavy Duty 240 Volt, Type 12 (Industrial)

System	Ampere Rating	VBII	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 240V, Fusible							
	30	HF221J	Use Two Poles of the 3-Pole 3-Wire Switch	Use Heavy Duty 600V Switch	TH2221J	H221AWK	Use 2-Pole 3-Wire Switch
	60	HF222J			TH2222J	H222AWK	
	100	HF223J			Use 2-Pole 3-Wire Switch	H223AWK	
	200	HF224J				H224AWK	
	400	1				H225AWK	DH225FDK
	600	1				H226AWK	DH226FDK
	800	1			—	H227AWK	DH227FDK
1200	—	—	—	H228AWK	—		
2-Pole, 3-Wire, 240V, Fusible							
	30	2	Use Two Poles of 3-Pole 3-Wire Switch Order sep. Neutral	Use Heavy Duty 600V Switch	TH3221J	Use 2-Pole 2-Wire Order sep. Neutral	DH221NDK
	60	2			TH3222J		DH222NDK
	100	2			TH3223J		DH223NDK
	200	2			TH3224J	DH224NDK	
	400	3			TH3225J	H225NAWK	DH225NDK
	600	3			TH3226J	H226NAWK	DH226NDK
	800	3			—	H227NAWK	DH227NDK
1200	5	—	—	H228NAWK	—		
3-Pole, 3-Wire, 240V, Fusible							
	30	HF321J	F321H	Use Heavy Duty 600V Switch	TH3321J	H321AWK	DH321FDK
	60	HF322J	F322H		TH3322J	H322AWK	DH322FDK
	100	HF323J	F323H		Use 3-Pole 4-Wire Switch	H322AWK	DH323FDK
	200	HF324J	F324H			H324AWK	DH324FDK
	400	HF325JA	F325H			H325AWK	DH325FDK
	600	HF326JA	F326H			H326AWK	DH326FDK
	800	HF327J	F327HL		—	H327AWK	DH327FDK
1200	5	—	—	H328AWK	DH328FDK		
3-Pole, 4-Wire, 240V, Fusible							
	30	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use Heavy Duty 600V Switch	TH4321J	4	DH321NDK
	60				TH4322J	4	DH321NDK
	100				TH4323J	4	DH321NDK
	200				TH4324J	4	DH321NDK
	400				TH4325J	H325NAWK	DH321NDK
	600				TH4326J	H326NAWK	DH321NDK
	800				—	H327NAWK	DH327NDK
1200	5	—	H328NAWK	DH328NDK			

1 Use Two Poles of the 3-Pole, 3-Wire Switch.

2 Use 2-Pole Switch. Order separate neutral.

3 Use Two Poles of the 3-Pole, 3-Wire Switch. Order separate neutral.

4 Use 3-Pole, 3-Wire Switch. Order separate neutral.

5 Use 600V switch.



Heavy Duty 600 Volt, Type 1 (Indoor)

System	Ampere Rating	VBII	Vacu-Break®	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 600V, Fusible							
	30	HF261	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	—	1	DH261FGK
	60	HF262			TH2262DC	1	DH262FGK
	100	HF263			TH2263DC	1	DH263FGK
	200	1			1	1	DH264FGK
	400	HF365A			1	H265	DH266FGK
	600	HF366A			1	H266	DH266FGK
	800	1			1	H267	DH267FGK
1200	1	1	H268	1			
3-Pole, 3-Wire, 600V, Fusible							
	30	HF361	F351	HNN361	TH3361	H361	DH361FGK
	60	HF362	F352	HNN362	TH3362	H362	DH362FGK
	100	HF363	F353	HNN363	TH3363	H363	DH363FGK
	200	HF364	F354	HNN364	TH3364	H364	DH364FGK
	400	HF365A	F355	HNN365	TH3365	H365	DH365FGK
	600	HF366A	F356	HNN366	TH3366	H366	DH366FGK
	800	HF367	F357L	HLN367	TC72367	H367	DH367FGK
1200	HF368	F358L	HLN368	TC72368	H368	DH368FGK	
3-Pole, 4-Wire, 600V, Fusible							
	30	HF361N	SN451	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	H361N	DH361NGK
	60	HF362N	SN452			H362N	DH362NGK
	100	HF363N	SN453			H363N	DH363NGK
	200	HF364N	SN454			H364N	DH364NGK
	400	HF365NA	SN455			H365N	DH365NGK
	600	HF366NA	SN456			H366N	DH366NGK
	800	HF367N	2			H367N	DH367NGK
1200	HF368N	2	H368N	DH368NGK			
2-Pole, 2-Wire, 600V, Non-Fusible							
	30	HNF261	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	THN2261DC	1	DH261UGK
	60	HNF262			THN2262DC	1	DH262UGK
	100	HNF263			THN2263DC	1	1
	200	1			1	1	DH264UGK
	400	HNF365A			1	HU265	DH265UGK
	600	HNF366A			1	HU266	DH266UGK
	800	1			—	1	HU267
1200	1	—	1	HU268	1		
3-Pole, 3-Wire, 600V, Non-Fusible							
	30	HNF361	NF351	HUN361	THN3361	HU361	DH361UGK
	60	HNF362	NF352	HUN362	THN3362	HU362	DH362UGK
	100	HNF363	NF353	HUN363	THN3363	HU363	DH363UGK
	200	HNF364	NF354	HUN364	THN3364	HU364	DH364UGK
	400	HNF365	NF355	HUN365	THN3365	HU365	DH365UGK
	600	HNF366	NF356	HUN366	THN3366	HU366	DH366UGK
	800	HNF367	NF357	—	TC36367	HU367	DH367UGK
1200	HNF368	NF358	—	TC36368	HU368	DH368UGK	

1 Use Two Poles of the 3-Pole, 3-Wire Switch.

2 Use 3-Pole, 3-Wire Switch. Order separate neutral.



Heavy Duty 600 Volt, Type 3R

System	Ampere Rating	VBI	Vacu-Break®	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 600V, Fusible							
	30	HF261R	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	TH2261RDC	1	DH261FRK
	60	HF262R			TH2262RDC	1	DH262FRK
	100	HF263R			TH2263RDC	1	DH263FRK
	200	1			1	1	DH264FRK
	400	HF365RA			1	H265R	DH265FRK
	600	HF366RA			1	H266R	DH266FRK
	800	1			TC72267R	H267R	DH267FRK
1200	1	TC72268R	H268R	1			
3-Pole, 3-Wire, 600V, Fusible							
	30	HF361R	FR351	HHN361AW	TH3361R	H361RB	DH361FRK
	60	HF362R	FR352	HHN362AW	TH3362R	H362RB	DH362FRK
	100	HF363R	FR353	HHN363AW	TH3363R	H363RB	DH363FRK
	200	HF364R	FR354	HHN364AW	TH3364R	H364RB	DH364FRK
	400	HF365RA	FR355	HHN365AW	TH3365R	H365R	DH365FRK
	600	HF366RA	FR356	HHN366AW	TH3366R	H366R	DH366FRK
	800	HF367R	FR357L	HHN367AW	TC72367R	H367R	DH367FRK
1200	HF368R	FR358L	HHN368AW	TC72368R	H368R	DH368FRK	
3-Pole, 4-Wire, 600V, Fusible							
	30	HF361NR	NRH451	HHN461NW	Use 3-Pole, 3-Wire Switch Order sep. Neutral	H361NRB	DH361NRK
	60	HF362NR	NRH452	HHN462NW		H362NRB	DH362NRK
	100	HF363NR	NRH453	2		H363NRB	DH363NRK
	200	HF364NR	NRH454	2		H364NRB	DH364NRK
	400	HF365NRA	NRH455	2		H365NRB	DH365NRK
	600	HF366NRA	NRH456	2		H366NRB	DH366NRK
	800	HF367NR	NRH457	2		H367NRB	DH367NRK
1200	HF368NR	NRH458	—	—	H368NRB	DH368NRK	
2-Pole, 2-Wire, 600V, Non-Fusible							
	30	HNF261R	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	THN2661RDC	1	DH261URK
	60	HNF262R			THN2662RDC	1	DH262URK
	100	HNF263R			THN2663RDC	1	DH263URK
	200	1			1	1	DH264URK
	400	HNF365RA			1	HU265R	DH265URK
	600	HNF366RA			1	HU266R	DH266URK
	800	1			—	—	HU267R
1200	1	—	—	HU268R	1		
3-Pole, 3-Wire, 600V, Non-Fusible							
	30	HNF361R	NFR351	HUN361AW	THN3661R	HU361RB	DH361URK
	60	HNF362R	NFR352	HUN362AW	THN3662R	HU362RB	DH362URK
	100	HNF363R	NFR353	HUN363AW	THN3663R	HU363RB	DH363URK
	200	HNF364R	NFR354	HUN364AW	THN3664R	HU364RB	DH364URK
	400	HNF365RA	NFR355	HUN365AW	THN3665R	HU365RB	DH365URK
	600	HNF366RA	NFR356	HUN366AW	THN3666R	HU366RB	DH366URK
	800	HNF367R	NFR357	—	—	HU387RB	DH367URK
1200	HNF368R	NFR358	—	—	HU361RB	DH368URK	


1 Use Two Poles of the 3-Pole, 3-Wire Switch.
 2 Use 3-Pole, 3-Wire Switch. Order separate neutral.



Heavy Duty 600 Volt, Type 4X (Stainless Steel)

System	Ampere Rating	VBII	Vacu-Break [®]	Murray	General Electric	Square D	Cutler Hammer
2-Pole, 2-Wire, 600V, Fusible							
	30	HF261S	Use 2-Poles of the 3-Wire Switch	Use 2-Poles of the 3-Wire Switch	TH2261SSDC	1	DH261FWK
	60	HF262S			TH2262SSDC	1	1
	100	HF263S			TH2263SSDC	1	1
	200	1			1	1	DH264FWK
	400	HF365SA			1	H265DS	1
	600	HF366SA			1	H266DS	1
	800	1			—	—	1
3-Pole, 3-Wire, 600V, Fusible							
	30	HF361S	F351SS	HHN361AS	TH3361SS	H361DS	DH361FWK
	60	HF362S	F352SS	HHN362AS	TH3362SS	H361DS	DH362FWK
	100	HF363S	F353SS	HHN363AS	TH3363SS	H361DS	DH363FWK
	200	HF364S	F354SS	HHN364AS	TH3364SS	H361DS	DH364FWK
	400	HF365SA	F355SS	HHN365AS	TH3365SS	H361DS	DH365FWK
	600	HF366SA	F356SS	—	TH3366SS	H361DS	DH366FWK
	800	HF367S	F357SSL	—	—	—	DH367FWK
1200	HF368S	—	—	—	—	DH368FWK	
3-Pole, 4-Wire, 600V, Fusible							
	30	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	2	Use 3-Pole, 3-Wire Switch Order sep. Neutral	H361NDS	DH361NWK
	60			2		H362NDS	DH362NWK
	100			2		2	DH363NWK
	200			2		H364NDS	DH364NWK
	400			2		H365NDS	DH365NWK
	600			—		H366NDS	DH366NWK
	800			—		—	DH367NWK ³
2-Pole, 2-Wire, 600V, Non-Fusible							
	30	HNF261S	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	THN2261SSDC	1	Use Two Poles of the 3-Pole 3-Wire Switch
	60	HNF262S			THN2262SSDC	1	
	100	HNF263S			THN2263SSDC	1	
	200	1			1	1	
	400	HNF365SA			1	HUD265DS	
600	HNF366SA	—	1	HUD266DS	1		
3-Pole, 3-Wire, 600V, Non-Fusible							
	30	HNF361S	NF351SS	HUN361AS	THN3361SS	HU361DS	DH361UWK
	60	HNF362S	NF352SS	HUN362AS	THN3362SS	HU362DS	DH362UWK
	100	HNF363S	NF353SS	HUN363AS	THN3363SS	HU363DS	DH363UWK
	200	HNF364S	NF354SS	HUN364AS	THN3364SS	HU364DS	DH364UWK
	400	HNF365S	NF355SS	HUN365AS	THN3365SS	HU365DS	DH365UWK
	600	HNF366S	NF356SS	—	THN3366SS	HU366DS	DH366UWK
	800	HNF367S	NF357SS	—	—	—	DH367UWK
1200	HNF368S	NF358SS	—	—	—	DH368UWK	

1 Use Two Poles of the 3-Pole, 3-Wire Switch.
 2 Use 3-Pole, 3-Wire Switch. Order separate neutral.
 3 DH368NWK offered.



Heavy Duty – 600 Volt, Type 12 (Industrial)

System	Ampere Rating	VBII	Vacu-Break®	Murray	General Electric	Square D	Cutler Hammer	
2-Pole, 2-Wire, Fusible								
	30	HF261R	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	TH2261RDC	1	DH261FDK	
	60	HF262R			TH2262JDC	1	DH262FDK	
	100	HF263R			TH2263JDC	1	DH263FDK	
	200	1			1	1	DH264FDK	
	400	HF365RA			1	H265AWK	DH265FDK	
	600	HF366RA			—	1	H266AWK	DH266FDK
	800	1			—	—	H267AWK	DH267FDK
1200	1	—	—	—	H268AWK	—		
3-Pole, 3-Wire, Fusible								
	30	HF361J	F351H	HN361AJ	TH3361J	H361AWK	DH361FDK	
	60	HF362J	F352H	HN362AJ	TH3362J	H362AWK	DH362FDK	
	100	HF363J	F353H	HHN363AJ	TH3363J	H363AWK	DH363FDK	
	200	HF364J	F354H	HN364AJ	TH3364J	H364AWK	DH364FDK	
	400	HF365JA	F355H	HHN365AJ	TH3365J	H365AWK	DH365FDK	
	600	HF366JA	F356H	—	TH3366J	H366AWK	DH366FDK	
	800	HF367J	F357HL	—	—	H367AWK	DH367FDK	
1200	HF368J	—	—	—	H368AWK	DH368FDK		
3-Pole, 4-Wire, Fusible								
	30	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	Use 3-Pole, 3-Wire Switch Order sep. Neutral	2	DH361NDK	
	60					H361NAWK	DH362NDK	
	100					H362NAWK ³	DH363NDK	
	200					H364NAWK	DH364NDK	
	400					H365NAWK	DH365NDK	
	600					H366NAWK	DH366NDK	
	800					—	—	2
1200	2	—	—	2	H368NAWK	—		
2-Pole, 2-Wire, Non-Fusible								
	30	HNH261J	Use Two Poles of the 3-Pole 3-Wire Switch	Use Two Poles of the 3-Pole 3-Wire Switch	THN2261JDC	1	DH261UDK	
	60	HNH262J			THN2261JDC	1	DH262UDK	
	100	HNH263J			THN2261JDC	1	DH263UDK	
	200	1			1	1	DH264UDK	
	400	HNH365JA			1	HU265AWK	DH265UDK	
	600	HNH366JA			1	HU266AWK	DH266UDK	
	800	1			—	1	HU267AWK	DH267UDK
1200	1	—	—	1	HU268AWK	—		
3-Pole, 3-Wire, Non-Fusible								
	30	HNH361J	NF351H	HUN361AJ	THN3361J	HU361AWK	DH361UDK	
	60	HNH362J	NF352H	HUN362AJ	THN3362J	HU362AWK	DH362UDK	
	100	HNH363J	NF353H	HUN363AJ	THN3363J	HU363AWK	DH363UDK	
	200	HNH365JA	NF354H	HUN364AJ	THN3364J	HU364AWK	DH364UDK	
	400	HNH366JA	NF355H	HUN365AJ	THN3365J	HU365AWK	DH365UDK	
	600	HNH366J	NF356H	HUN366AJ	THN3366J	HU366AWK	DH366UDK	
	800	HNH367J	NF357H	—	—	HU367AWK	DH367UDK	
1200	HNH368J	—	—	—	HU368AWK	DH368UDK		

1 Use Two Poles of the 3-Pole, 3-Wire Switch.
 2 Use 3-Pole, 3-Wire Switch. Order separate neutral.
 3 Need footnote.

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

1-800-241-4453
info.us@siemens.com

Subject to change without prior notice.
Order No: S5XR-00100-0415
All rights reserved.
Printed in USA
©2015 Siemens Industry, Inc.

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.