


3VA Circuit Breakers: Compact. Global. Next Gen!

Stocking suggestion and conversion tool

3VA Breaker Crosses


Description	Sentron	VL	G frame	EG	3VA
15A 3P 25K @480V	ED63B015L	N/A	NGG3B015L	NEG3B015L	3VA5195-4EC31-0AA0
20A 3P 25K @480V	ED63B020L	N/A	NGG3B020L	NEG3B020L	3VA5120-4EC31-0AA0
50A 3P 25K @480V	ED63B050L	NDK3B050L	NGG3B050L	NEG3B050L	3VA5150-4EC31-0AA0
100A 3P 25K @480V	ED63B100L	NDK3B100L	NGG3B100L	NEG3B100L	3VA5110-4EC31-0AA0
125A 3P 25K @480V	ED63B125L	NDK3B125L	NGG3B125L	NEG3B125L	3VA5112-4EC31-0AA0
150A 3P 35K @480V	FXD63B150L/FD63B150L	NDK3B150L	N/A	N/A	3VA5215-5EC31-0AA0
200A 3P 35K @480V	FXD63B200L/FD63B200L	NFK3B200L/NFG3B200L	N/A	N/A	3VA5220-5EC31-0AA0
225A 3P 35K @480V	FXD63B225L/FD63B225L	NFK3B225L/NFG3B225L	N/A	N/A	3VA5222-5EC31-0AA0
250A 3P 35K @480V	FXD63B250L/FD63B250L	NFK3B250L/NFG3B250L	N/A	N/A	3VA5225-5EC31-0AA0



- Note: 1) 3VA breakers do not come with lugs, part numbers listed for other legacy products include lugs .
 2) Breakers crossed have at a minimum the ratings in the description box, in some cases higher.
 3) For a non-adjustable instantaneous version breaker sub -ED- in place of -EC- in the part number.


3VA Lugs

Description	3VA "Standard" lugs	Description	Cables Per Phase
125A TMTU	3VA9133-0JB11	3-Pole #14-3/0	1
250A TMTU	3VA9233-0JB12	3-Pole #6-350KCMIL	1
150A ETU	3VA9143-0JB11	3-Pole #14-1/0	1
250A ETU	3VA9243-0JB12	3-Pole #6-350KCMIL	1
400A-600A ETU	3VA9373-0JB13	3-Pole #1 - 600KCMIL	1




3VA Internal Accessories

Description	MLFB Part Number
Shunt Trip Flex 120V	3VA9978-0BA22
Shunt Trip 24VDC	3VA9978-0BA20
HQ Aux 1 Slot	3VA9978-0AA12
UVR 120V	3VA9978-0BB24
Trip Alarm Switch	3VA9978-0AB12



3VA Handle Kits

Description	125A(3VA51) TMTU	250A(3VA52) TMTU
Max Flex 1/3R/12- 36" cable	3VA9138-0CK12	3VA9278-0CK12
Rotary Handle 1/3R/12 - 300mm shaft	3VA9137-0FK31	3VA9277-0FK31
Rotary Handle 1/3R/13 Illuminated- 300mm shaft	3VA9137-0FK33	3VA9277-0FK33
Flange Mount 1/3R/12 - 200-400mm adj. shaft	3VA9138-0DK74	3VA9278-0DK74



Note: The above sample of available products as well as the full catalog of over 2000 breaker and accessories currently available can be found in our catalog or via our configurator. Please visit usa.siemens.com/3VA



Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

1-800-241-4453
info.us@siemens.com

Subject to change without prior notice
Order No. PDFL-3VASTK-0417
Printed in USA
All Rights Reserved
© 2017, Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.