











ALPHA FIX Terminal Blocks

ALPHA FIX IDC Terminals with Insulation Displacement Connection

Through-type terminals

Selection and ordering data

Dimensions	Version	Color	DT	Order No.	PS*	Weight per PU approx. kg
Through-type terminals						
Terminal size 1.5 mm ² , width 5 mm  AWG 24-16						
Through-type terminals, with two clamping points						
	IDC/IDC	Gray	A	8WA3 011-1DE20	50 units	0.008
		Blue	A	8WA3 011-1BE23	50 units	0.008
8WA3 011-1DE20	IDC/spring	Gray	A	8WA3 021-1DE20	50 units	0.008
		Blue	A	8WA3 021-1BE23	50 units	0.008
	IDC/screw	Gray	A	8WA3 031-1DE20	50 units	0.009
		Blue	A	8WA3 031-1BE23	50 units	0.009
8WA3 021-1DE20						
8WA3 031-1DE20						
Through-type terminals, with three clamping points						
	IDC/IDC	Gray	A	8WA3 011-1DE30	50 units	0.011
		Blue	A	8WA3 011-1BE33	50 units	0.011
8WA3 011-1DE30						
Through-type terminals, with four clamping points						
	IDC/IDC	Gray	A	8WA3 011-1DE40	50 units	0.014
		Blue	A	8WA3 011-1BE43	50 units	0.014
8WA3 011-1DE40						
Accessories						
Cover plates						
	For through-type terminals with two clamping points	Gray	A	8WA3 522-7WE01	50 units	0.214
		Blue	A	8WA3 522-7WE03	50 units	0.214
8WA3 522-7WE01	For through-type terminals with three clamping points	Gray	A	8WA3 522-7WE31	50 units	0.270
		Blue	A	8WA3 522-7WE33	50 units	0.270
	For through-type terminals with four clamping points	Gray	A	8WA3 522-7WE41	50 units	0.165
		Blue	A	8WA3 522-7WE43	50 units	0.165
Connection combs						
	For two terminals	Yellow	A	8WA8 522-7VF02	60 units	0.060
	For three terminals	Yellow	A	8WA8 522-7VF03	60 units	0.099
	For four terminals	Yellow	A	8WA8 522-7VF04	60 units	0.132
	For ten terminals	Yellow	A	8WA8 522-7VF10	20 units	0.124
8WA8 522-7VF02						
Covers, with warning arrow						
		Yellow	A	8WA3 522-7WE06	20 units	0.003
Test adapter						
		Black	A	8WA3 522-7WE07	25 units	0.200
Reduction sleeve						
		White	A	8WA3 522-7WE00	100 units	0.015

* This quantity or a multiple thereof can be ordered.

Siemens LV 10 · 2004

14/3