




# *Environmental product declaration*

<b>Product</b>	Device type	<b>MXG461.32-12, MXG461.32-12P MXG461.40-20, MXG461.40-20P MXG461.50-30, MXG461.50-30P</b>
	Designation	<b>Precision valve with magnetic actuator for standard applications to 120°C</b>
	Product range	<b>Valves and actuators</b>
<b>Process control</b>	Siemens Building Technologies AG, HVAC Products Laubisrütistrasse 50, CH-8712 Stäfa	
	Management system certified	since by
	ISO 14001 (environment)	<b>13 Dec. 1996 BVQI</b>
	ISO 9001 (quality)	<b>7 Feb. 1991 BVQI</b>
<b>Product use</b>	Typical energy consumption per year	<b>53 kWh bei 100% Einschaltdauer</b>
	Maintenance	<b>need no maintenance</b>
	Environmental benefits	<b>see notes page 2</b>
<b>Environmental risk (fire)</b>	Fire protection as per	<b>EN 60730</b>
	Fire load	<b>approx. 10 MJ</b>
	Parts containing halogens (result in corrosive smoke)	<b>pc board without components cover, base, hand wheel, insert</b>
<b>Packaging</b>	Paperboard, cardboard boxes, paper	<b>(*) folding box with insert 374 g</b>
	Transportation protection	<b>(*) styrofoam 79 g</b>
	Notes on disposal	<b>can be recycled</b>

Materials		total weight of device	(*)	5,175 g
Plastics	PC; GF10, FR(16) containing halogens	cover, base, hand wheel	(*)	172 g
	PBT; GF30, FR(62) halogen-free	coil cover, coil	(*)	142 g
	Rubber, Vetronit	O-ring, wiper, insulating ring(*)		5 g
Metals	Brass, bronze	stem, bushing, seat, disc	(*)	260 g
	Steel, zinc-plated, nickel-plated	screws, core, cover	(*)	21 g
	Copper wire	coil winding	(*)	540 g
	Cr/Ni steel	bolt, disc, stem	(*)	52g
	Steel	U-bracket, bushing	(*)	1,212 g
	Free-cutting steel 95MnPb	armature, core	(*)	575 g
	Cast iron	valve body	(*)	2,114 g
	Zinc	cover	(*)	0 g
	Miscellaneous	Oil, grease	silicone oil, silicon grease	
Circuit board	FR 4; containing halogens	circuit board with components		69 g
		pc board without components	(21 g)	
<b>Special Components</b>	FR4, containing halogens, SnPb solder	on the circuit board		(4 g)
	1x Al capacitor	on the circuit board		(36 g)
	Misc. components	stroke measurement element, on the circuit board		(8 g)

### Disposal



Do not dispose of the device as part of standard household garbage, but as special waste from electrical and electronic components. This particularly applies to electronic circuit boards.

Additionally, the law may mandate special treatment for specific components or special treatment may be ecologically sensible.

**Observe all local and applicable laws.**

### Environmental benefits:

- Reduced energy consumption (domestic hot water, cold water) for HVAC and industrial applications due to high control accuracy and positioning speed.
- Long lifetime due to few moving parts in the magnetic actuator. Thus high protection of investment and significant savings in raw material resources.

(\*) Information applies to **MXG461.32-12**.

	PC; FR(16)	PBT; FR(62)	Rubber	Brass/bronze	Steel, zinc-plated	Copper wire.	Cr/Ni steel
<b>MXG461.40-20</b>	121 g	197 g	11 g	407 g	26 g	924 g	86 g
<b>MXG461.50-30</b>	121 g	197 g	11 g	640 g	26 g	924 g	100 g
	Steel	95MnPb	Cast iron	Zinc	Box.	Styrofoam	Tot. weight
<b>MXG461.40-20</b>	2,075 g	1,061 g	3,315 g	202 g	366 g	50 g	8,502 g
<b>MXG461.50-30</b>	2,075 g	1,061 g	5,222 g	202 g	440 g	50 g	10,657 g

### Legal disclaimer: This declaration is for information purposes only.

The above information may be inaccurate or incomplete. Siemens Building Technologies Ltd. therefore does not assume liability for any error or any consequences which may arise from the use of this information to the maximum extent under the law.