



DESIGO™ INSIGHT

Management station Econel 50

DESIGO INSIGHT management station consisting of server hardware and pre-installed system software.

Use

The DESIGO INSIGHT management station contains both the computer (PRIMERGY Econel 50) as well as the complete DESIGO INSIGHT software.

Licensing of individual functions (e.g. starter pack, plant viewer, data points) is provided separately via the SAP web GGU; a dongle (USB or parallel) is also required.

The DESIGO INSIGHT management station is easily expanded with new hardware (e.g. hard drives, RAM) and with additional functions (e.g. remote access).

It communicates via the industrial Ethernet system bus with connected PX automation stations as well as with VISONIK, UNIGYR, Integral and SIMATIC S7.

A separate PROFIBUS card is required to connect UNIGYR via PROFIBUS.

Features

The DESIGO INSIGHT management station is based in design on a modern server PC from Fujitsu Siemens Computers.

The mini-tower contains free PCI slots for fast I/O cards and an integrated graphic processor.

The Pentium 4 processor has a speed of 3.0 GHz and 1 GB of RAM.

A 80 GB SATA hard drive. Max. 4 hard drives can be inserted at RAID level 1 (on-board RAID controller).

The operator console can be connected via the installed graphic process (not included, but recommended is a TFT monitor).

An on-board twisted-pair connection 10/100/1000+ (RJ45).

One DVD R/W drive (including CD R/W) is also included with the package.

Optional extensions

- Backup:
DAT streamer (DDS-5) with a capacity of 36 GB MO drive 2.3 GB
- Interface multiplier to extend the number of serial interfaces (e.g. for message printer).
- Hard drives as memory extension and for operation as a mirrored drive
- RAM DDR2 SDRAM
- Soundcard
- Graphic card 64 MB NVIDIA
- PCI PROFIBUS card for UNIGYR connection
- Uninterrupted power supply (UPS).

Software

The operating system is Windows XP multilanguage. The complete functionality of DESIGO INSIGHT is installed under this operating system.

Norton Ghost and NETOP Remote Control Host is also installed and licensed.

DESIGO INSIGHT functionality is only available after the appropriate licenses are received via SAP CGU Web:

Starter Pack

→Object Viewer
→Alarm Viewer
→Alarm Router
→Time Scheduler

Options

→Plant Viewer
→Trend Viewer
→Log Viewer
etc.

Add-on

→Remote access
→Third party software

A dongle (USB or parallel) is further required for operation.

Ordering

When ordering, please specify the quantity, ASN and type designation.

<i>Type designation</i>	<i>ASN</i>
DESIGO INSIGHT Management Station Econel 50	CDI50-T.02

The order CDI50-T.02 includes:

- Basic unit PRIMERGY **Econel 50**
- **Windows XP** Multilanguage
- Complete pre-installation of **DESIGO INSIGHT** (without licenses)
- **Norton Ghost** (with license)
- **NETOP** Remote Control Host (with license)

Technical data

	Type	CDI50-T.02
System unit	CPU	Pentium 4 3.0 Ghz processor
	Second level cache	256 KB ECC
	Memory	1 GB DDR2 SDRAM (expandable to 4 GB)
	Hard disk drives	1 x 80 GB, SATA (max. 4 hard drives connected to RAID level 1)
	Diskette drive	3.5 inch, 1.44 MB
	DAT drive (optional)	DDS-5, 36 GB
	DVD R/W drive (including CD R/W)	5.25 inch, 4x/8x speed
	Graphics card	on-board, 8 MB
	Network card	Intel 10/100/1000+ on-board with RJ-45 plug
	Keyboard, mouse	3-button mouse
	Interfaces	<ul style="list-style-type: none"> • 3 x RS-232-C (serial, 9-pin) • 2 x Centronics (parallel, 25-pin, EPP/ECP compatible) • 6 x USB • 2 x PS/2, mouse, keyboard • 1 x VGA (15-pin)
	Slots	5 x PCI, 2 x PCI Express (1x1, 1x8)
		Mounting slots
	– for HD drives	4 x 3.5 inch for Standard SATA
	– for operatable drives	2 x 5.25 inch
Visualization	Color monitor for operator console	17 to 21 inch (TFT monitor recommended)
Power	Power supply	240 W (permanent supply)
	Mains supply	AC 100 to 240 V
	Mains frequency	50 to 60 Hz
Dimensions / weight	Dimensions (H x W x D) in mm	390 x 203 x 500
	Weight	ca. 19 kg
Ambient conditions	Ambient temperature	10...35 °C as per IEC 721
	Noise class	0 as per ISO 9296
Standards	Product safety	EN 60950 / IEC 60950
	FCC guidelines	Class A
	Electromagnetic compatibility	EN 55022 class B; EN 55024
	CE labeling as per EU directives	89/336/EEC (EMC) 72/23/EEC (LVD)

Bold faced components are included in the basic version (**CDI50-T.02**)