

Cerberus[®] PRO Modular system

Fiber-Optic Interface
and Bracket for DNET

Models DFM-BRK, DFM

Architect & Engineer Specifications

- Provides a multimode fiber-optic interface for the Cerberus PRO Modular system digital audio network (DNET)
- Supports `Class B` (Style 4) or `Class A` (Style 7) wiring
- Uses 62.5 / 125 μm fiber at distances up to 2km. (or 6,562 ft)
- UL | ULC-S527 Listed;

Product Overview

The Model DFM-BRK provides a multimode fiber-optic interface for the Cerberus PRO Modular system digital audio network (DNET), which interconnects the Model DAC-NET modules.

Model DFM supports either `Class B` (Style 4) or `Class A` (Style 7) wiring. Model DFM uses 62.5 / 125 μm fiber at distances up to 6,562 ft. (2 km.)

Standard ST connectors are provided for connection of the optical fiber.

Model DFM-BRK is the mounting bracket for Model DFM, and mounts in the rear of the CAB-1 | CAB-2 | CAB-3 of a Cerberus PRO Modular voice-system enclosure, occupying one (1) module space.



Model DFM BRK
Fiber-Optic Interface
and Bracket
for DNET



Model DFM
Fiber-Optic Interface



Temperature and Humidity Range

Products are UL | ULC Listed for indoor dry locations within a temperature range of 120+/-3°F (49+/-2°C) to 32+/-3°F (0+/-2°C) and a relative humidity of 93+/-2% at a temperature of 90+/-3°F (32+/-2°C).

Electrical Ratings

| | |
|--|-------------------------|
| 24V CURRENT DRAW: [Backplane] | 0 |
| 24V CURRENT DRAW: [Screw Terminal] | 135mA, per Model DFM |
| 6.2V CURRENT DRAW: [Backplane] | 0 |
| 24V CURRENT DRAW: [Standby] | 135mA, per Model DFM |

Fiber Ratings

| | |
|---------------------------|----------------------|
| FIBER-OPTIC CABLE: | 62.5 / 125 µm |
| DISTANCE: | 6,562 ft (2Km.) max. |
| POWER BUDGET: | 12dB |
| WAVELENGTH: | 850 nm |
| CONNECTORS | ST |

Details for Ordering

| MODEL OR TYPE | PART NUMBER | PRODUCT |
|---------------|-------------|------------------------------------|
| DFM | 500-634910 | DNET Fiber Module |
| DFM-BRK | 500-633779 | DNET Fiber Module Mounting Bracket |

NOTICE – The information contained in this data-sheet document is intended only as a summary, and is subject to change without notice.

The product(s) described here has/have a specific instruction sheet(s) that cover various technical, limitation and liability information.

Copies of install-type, instruction sheets – as well as the *General Product Warning and Limitations* document, which also contains important data, are provided with the product, and are available from the Manufacturer.

Data contained in the aforesaid type of documentation should be consulted with a fire-safety professional before specifying or using the product.

Any further questions or assistance concerning particular problems that might arise, relative to the proper functioning of the equipment, please contact the Manufacturer.

SIEMENS

Cerberus® PRO

Siemens Industry, Inc.
Building Technologies Division
8 Fernwood Road • Florham Park, NJ 07932
Tel: (973) 593-2600

October 2017 – New Issue
(Rev. 0)