



Differential Pressure Sensor

QBE64-DP4

for neutral and mildly corrosive liquids and gases

Differential pressure sensor, suitable for gases or liquids, for the measurement of positive or negative pressures and pressure differentials in HVAC systems.

- **Measuring system based on ceramic lever technology**
- **Simple, robust construction for highly reliable operation**
- **For neutral and mildly corrosive liquids and gases**
- **Supply voltage AC 24 V or DC 18...33 V**
- **DC 0...10 V output signal**
- **Male-threaded G^{1/8}" connection**
- **Delivery includes 2 screwed fittings for copper pipes, 6 mm diameter**

Use

The QBE64-DP4 differential pressure sensor is particularly suitable for use in HVAC systems for continuous monitoring of the level or flow rate of neutral or mildly corrosive gases or liquids.

The pressure to be monitored acts on a ceramic sensor element. The measured pressure is converted electronically into a linear DC 0 ...10 V output signal.

Ordering and delivery

When ordering, please specify the quantity, product name and type code.

Example: 1 differential pressure sensor QBE64-DP4

A suitable fixing bracket is supplied with the sensor.

Any accessories required must be ordered separately.

Compatibility

The QBE64-DP4 differential pressure sensors can be used in conjunction with all devices or systems capable of processing the DC 0...10 V output signal.

Technology

The pressure to be monitored acts on a ceramic sensor element. The ceramic element has the following significant advantages

- Very low susceptibility to temperature
- Resistance to high temperature
- No mechanical ageing or creepage

The sensor signal is linearised, temperature-compensated and amplified by the sensor electronics.


Mechanical design

The QBE64.DP4 differential pressure sensor comprises the following:

- Sensor cover with connecting cable and gland
- Pressure sensor casing with ceramic element, screw connections and purging points
- Printed circuit board
- 2 screwed fittings for copper pipe, 6 mm diameter
- Fixing bracket, enclosed loose, with sensor

Accessories

AQB2002 Mounting kit for remote mounting with 1 m copper capillary line, both ends prefabricated ready for connection. Thread adapters and terminal nuts made of brass. Pressure connection with G1/8" or G1/2" outer threading.



Mounting instructions

Mounting instructions are enclosed with the differential pressure sensor.

The QBE64-DP4 sensor can be connected directly with R $\frac{1}{8}$ " screwed fittings. Special precautions must be taken on site when mounting the sensors to ensure airtight screw connections.


Recommended measures

- Use standard T-fittings or drill and de-bur measuring holes, each 5 mm diameter, for the pressure tapping points (A).
- An isolating bypass (5) can be fitted, to avoid overloading the pressure sensor on one side while making adjustments.
- For inspection purposes, measuring circuits can be fitted with a measuring-T at the sensor head.

Important note

Mounting for use with liquids:

- Always mount the sensor lower than the pressure measuring points
- Mount on a vibration-free surface
- Always evacuate the system



- Key:
- A Measuring holes
 - 1 Isolating valves
 - 2 T-joints
 - 3 Connection pieces (from mounting kit AQB 2002)
 - 4 Copper pipes (from mounting kit AQB 2002)
 - 5 Isolating bypass

Remote mounting

For remote mounting, the sensor can be operated together with the AQB pressure mounting kit in ambient temperatures of up to 70 °C for medium temperatures of up to 180 °C. Care must be taken in this case to ensure that the cooling efficiency of the copper pipe is not reduced by additional heat sources or by restrictions to the air circulation.

Disposal

- Dispose of the device via the channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.




Technical data

| | | |
|----------------------------------|---|---|
| Electrical interface | Power supply | Low voltage (SELV, PELV) |
| | Operating voltage | AC 24 V ± 15 %, 50/60 Hz or DC 18...33 V |
| | Current consumption | with AC 24 V: <5 mA with maximum output signal |
| | External supply line protection | Fuse slow max. 10 A or Circuit breaker max. 13 A Characteristic B, C, D according to EN 60898 or Power source with current limitation of max. 10 A |
| Product data | Output signal | DC 0...10 V, short-circuit-proof and proof polarity reversal |
| | Working resistance | > 10 kΩ |
| | Differential pressure range | 0 ... 4 bar |
| | Measuring element | Ceramic |
| | Measuring accuracy | Factory calibrated |
| | Sum of linearity, hysteresis and repeatability | <±0.5 % FS (FS = Full Scale) |
| | Zero point, Full scale | <±0.4 % FS |
| | TC zero point | <±0.04 % FS/K |
| | TC sensitivity | <±0.015 % FS/K |
| | Overload on one side P1 / P2 | 8 / 8 bar |
| | System pressure | 25 bar (P1 and P2 simultaneously) |
| | Bursting pressure | 37.5 bar (1.5 x system pressure) |
| | Dynamic response: | |
| | Response time | < 5 ms |
| | Load alternation | < 50 Hz |
| Suitable media | Air, mildly corrosive gases, liquids | |
| Admissible temperature of medium | - 15...+ 85 °C | |
| Maintenance | No maintenance required | |
| Degree of protection | Protection degree of housing | IP65 according to EN 60529 |
| | Protection class | III according to EN 60730-1 |
| Connections | Connecting cable | 3-core, 1.5 m long |
| | Cable entry | Cable gland |
| | Pressure connections | Male-threaded G ¹ / ₈ ", With screwed fittings for copper pipes, 6 mm diameter |
| Mountings | Mounting bracket | For mounting in ducts, on walls or ceilings and in control panels |
| | Orientation | Any (factory-calibrated with pressure connections at bottom). When used with liquids: Purging points at top |
| Environmental conditions | Perm. ambient temperature | |
| | Operation | - 15...+ 85 °C |
| | Storage/ Transport | - 40...+ 85 °C |
| | Perm. ambient humidity | <90 % r. h. (non-condensing) |
| Directives and Standards | Product standard | EN 61326-1 Electrical equipment for measurement, control and laboratory use. EMC requirements. General requirements. |
| | EU Conformity (CE) | CA1T1923xx ^{*)} |
| | RCM Conformity | 8000078879 ^{*)} |
| | EAC Conformity | Eurasia Conformity |
| Environmental compatibility | The product environmental declaration CE1E1921 ^{*)} contains data on environmentally compatible product design and assessments (RoHS compliance, materials composition, packaging, environmental benefit, disposal). | |


*) The documents can be downloaded from <http://siemens.com/bt/download>.

| | | |
|-----------|------------------------------|---|
| Materials | Pressure casing, cover | Aluminium (AlMgSi1) |
| | Parts in contact with medium | Stainless steel (1.4305), ceramic element |
| | Sealant | FPM (fluoroelastomer) |
| | Mounting bracket | Stainless steel (1.4305) |
| | Mounting kit AQB2002 | See "Accessories" |
| Weight | Including packaging | 0.43 kg |

Connection terminals

| | Color | |
|---|-------|---|
| G  | Brown | Supply voltage AC 24 V or DC 18...33 V |
| U  | Green | DC 0...10 V output signal (reference point GND) |
| M  | White | GND |

Dimensions



Dimensions in mm

Published by:
Siemens Switzerland Ltd.
Building Technologies Division
International Headquarters
Gubelstrasse 22
6301 Zug
Switzerland
Tel. +41 58-724 24 24
www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd 2004
Delivery and technical specifications subject to change