



LE3, Stabex HF

Test lamps

AlgoRex
Synova™
Sinteso™





- **LE3 Test lamp**

- The LE3 test lamp is used for testing the operation of all flame detectors. It is supplied with all the necessary accessories in a suitable carrying case. The carrying case also provides a means of storing the test lamp free of dust.
- To aim the test lamp the built-in quartz halogen lamp generates a continuous beam of light which is then modulated to trigger alarm in the detector being tested. The light intensity can be adapted according to the distance at which the test takes place.
- Power is supplied by rechargeable battery. As light color depends on the charged condition of the battery it must be continuously charged in floating operation. A special charging unit is available for this purpose.

- **Stabex HF Test lamp**


- The Stabex HF test lamp is used to carry out a performance check on intrinsically safe flame detectors in explosion-hazard areas in zones 1 and 2.
- To make the check, the lamp is held in front of the detector. The beam of light must be modulated at a half-second pulse using the sliding switch.


Technical data

Test lamps	LE3	Stabex HF
		
	Forbidden in explosion-hazard areas!	Open the lamp only in <u>non</u> explosion-hazard areas!
Power consumption	50 W	–
Modulation frequency	4 Hz	–
Max. distance for alarm triggering	10 m	a few cm
Measuring capacity with fully charged battery and at max. distance		
– Number of detectors	~ 50	–
Operating and storage temperature	-20... + 45 °C	-20... + 40 °C
Explosion protection	–	II 2 G EEx ib e IIC T4
Ex Approvals	–	PTB 98 ATEX 2062
Application range	non explosion-hazard area	zones 1 and 2
Protection category	–	IP65
Incandescent lamp	Halogen 12 V / 50 W	Halogen 2.8 V / 0.5 A
Battery	12 V / 7 Ah, lead, gas-tight	2 x Alkali battery 1.5 V single-cell UM-1
Charging time	min. 16 h	–
Mains supply for charging unit	220 / 240 VAC, 50... 60 Hz	–

Details for ordering

	Type	Part no	Designation	Weight
	LE3	BPZ:3669510001	Test lamp for flame detectors (incl. carrying case and charger, without battery)	5.260 kg
	FA2003-A1	A5Q00019353	Battery 12 V / 7 Ah / VDS	2.293 kg
Spare part	–	BPZ:3679630001	Halogen lamp 12 V / 50 W	0.395 kg
	Stabex HF	BPZ:4620910001	Test lamp for explosion-hazard area	0.175 kg

	LE3	Siemens Schweiz AG; Theilerstrasse 1a CH-6300 Zug Technical data: see doc. 000252
LE3 - Test lamp. Test equipment for use in fire detection and fire alarm systems installed in buildings.		
2014/30/EU (EMC): EN 50130-4 / EN 61000-6-3 / EN 61010-1 / EN 55024 ; 2011/65/EU (RoHS): EN 50581		
The declared conformity can be seen in the EU Declaration of Conformity (DoC), which is obtainable via the Customer Support Center: Tel. +49 89 9221-8000 or http://siemens.com/bt/download		
DoC: No.: CED-LE3		

	STABEX HF	Couper Crouse-Hinds GmbH; Neuer Weg-Nord 49 D-69412 Eberbach Technical data: see doc. A6V10203222
STABEX HF - Stabex HF Hand lamp. Test equipment for use in fire detection and fire alarm systems installed in buildings.		
2014/34/EU (ATEX): EN 60079-0 / EN 60079-7 / EN 60079-11 / EN 60079-31 ; 2011/65/EU (RoHS): EN 50581		
The declared conformity can be seen in the EU Declaration of Conformity (DoC), which is obtainable via the Customer Support Center: Tel. +49 89 9221-8000 or http://siemens.com/bt/download		
DoC: No.: CED-STABEX_HF		

Disposal



The device is considered an electronic device for disposal in accordance with the European Guidelines and may not be disposed of as domestic garbage.

- Dispose of the device through channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.
- Dispose of empty batteries in designated collection points.

Issued by
Siemens Switzerland Ltd
Building Technologies Division
International Headquarters
Theilerstrasse 1a
CH-6300 Zug
Tel. +41 58 724 24 24
www.siemens.com/buildingtechnologies

© Siemens Switzerland Ltd, 2009
Technical specifications and availability subject to change without notice.