



## SC-MFLT4-FRNC Sensor Cable

FibroLaser™

- 
- Detects hot gases and radiant heat using linear temperature measurement
  - Flame Retardant and Non Corrosive sheath
  - Consistent sensitivity throughout the entire sensor cable length
  - Redundancy due to double optical fibers – for safety on the highest level
  - Infrared absorbing cable insulation (FRNC)
  - No electronic parts – immune to electromagnetic interferences
  - Robust construction – resistant to environmental influences
  - Easy installation
  - No maintenance required
  - High durability (up to 30 years)
  - VdS approval (G211076)

## Sensor cable setup


---

The sensor cable comprises an infrared absorbing cable insulation FRNC (Flame Retardant Non Corrosive). FRNC is a halogen-free, flame-retardant material. During the combustion of FRNC, no acids are released.

The fiber optic cables are multimode waveguides with the gradient 62.5/125/250  $\mu\text{m}$  as well as international standard dimensions and properties.

## Cross-section through a sensor cable

---



## Application-dependent advantages

---

### Road tunnels:

- Early fire detection in spite of exhaust gases, dirt and moisture
- No operational interruptions for maintenance purposes
- No electromagnetic interferences

### Railway tunnels:

- Early fire detection in spite of dirt and moisture
- No operational interruptions for maintenance purposes
- No electromagnetic interferences

### Recycling facilities:

- No false alarms caused by dust and dirt

### Conveyor belts:

- Early fire detection even in changing climatic conditions

### Cable trays:

- Early fire detection by slowly increasing temperatures
- No electromagnetic interferences

## Optical fiber characteristics

fiber type	graded index 62.5 / 125 / 250 $\mu\text{m}$
------------	---

**The sensor cable complies with the manufacturer's guidelines of system calibration for the undisturbed operation as fire detection system.**

## Mechanical characteristics

Cable diameter	4.0 mm
Outer sheath color	black
Outer sheath material	FRNC
Number of fibers	2
Cable weight	17 kg / 1000 m
Max. tensile strength long- / short term	400 N / 800 N
Min. bending radius without- / with tensile loading	60 mm / 80 mm
Repeating bending (5 windings / radius 40mm)	3
Impact resistance (number impacts with 1,5Nm)	3
Max. crush resistance	2000 N/dm
Max. distance between fixations / recommended	3 m / 1 m

## Temperature range

Storage and operating temperature	-40...+85 °C
Installation temperature	-5...50 °C
Short term temperature (max. 60min)	-50...+150 °C

## Standards

Flame propagation	IEC 60332-1 -2
Smoke density	IEC 61034-2
Content of halogen acid gas	IEC 60754-2
Temperature cycling	EN 50200 – PH 30 (30 min, 830 °C, $\Delta\alpha < 3 \text{ dB @ } 1300 \text{ nm}$ )
Cable Standard	EN 18700, IEC 60794
Fibre Standard	IEC 60793
Additional Tests	IEC 60794-1-2, E10, F1, F5, G7; IEC 60794-2-50

## Ordering information

---

Name	Lios part number
SC-MFLT4-FRNC	18030606

Transportation on cable drum (weight = 15 kg / width = 520 mm, diameter = 800 mm)

Siemens Switzerland Ltd  
Infrastructure & Cities Sector  
Building Technologies Division  
International Headquarters  
Gubelstrasse 22  
CH-6301 Zug  
Tel. +41 41 724 24 24  
[www.siemens.com/buildingtechnologies](http://www.siemens.com/buildingtechnologies)

© 2014 Copyright by  
Siemens Switzerland Ltd  
Data and design subject to change without notice.  
Supply subject to availability