


**RWD32 Universal Controller**  
**Application 31**  
**Remote set point**

Room temperature control  
 Hot water control valve - 3 pos  
 230Vac control system

- Control ( P or PI )
- Room temperature control
- Proportional control of the 3 position hot water valve.
- Remote set point adjustment
- Optional day / night set point adjustment .



**Supplemental features**

**Control**

- Room temperature sensor can be selected as Ni1000, Pt1000, or active sensor.
- Adjustable proportional band of 3-position output Q1, Q2.
- Integral action function selection and adjustment.
- Timing of 3-position valve actuator
- 230Vac controller supply voltage
- 230Vac two position control valves
- Remote set point adjustment via auxiliary analogue input X2.

**Operating modes**

- Day / night set points can be selected via time clock or switch.

**Description of operation**

The temperature sensor senses the room conditions and on a fall in temperature the RWD32 via Q1, Q2 digital outputs modulates the three position heating valve as determined by the heating set point and proportional band settings.

The remote set point adjuster, passive or active, is connected to X2.


Three position control has no feedback from the valve actuator to determine it's position, so the timing of the actuator must be known to the controller. During commissioning the actuator timing must be entered. A common actuator timing for small three position valve and damper actuators is 150 seconds from fully open to fully closed, so this means that the controller modulates the actuator over the Xp proportional band range for 150 seconds.

E.g. An Xp proportional band of 4° C and 150 second cycle time means that for a 4° C change the controller will drive the actuator for 150 seconds.


A synchronous check on the position of the actuator is carried out on a regular basis.

**Function diagram**

Heating sequences



**Connection diagram**



**RWD32**

- N1 RWD32 controller
- X1 Main temperature sensor
- X2 Remote set point adjuster
- S1 Time clock or switch
- Q1 Opening contact for 230Vac 3 - position control valve
- Q2 Closing contact for 230Vac 3 - position control valve
- HCV 3 – position 230Vac heating control valve
- PC Personal computer

## Main Display

The main display shows ,

- Whether Q1 is On or Off (  = off,  = on )
- Whether Q2 is On or Off (  = off,  = on )
- Whether day or night set point is selected. (☐ = day, ☐ = night)
- X1 value ( room temperature) in ° C.
- Auxiliary application selected ( REM for remote set point adjustment )

Other displays are available by pressing the + button, and the various displays are listed below in sequence from the main display.

On entering any of the four set point displays, the setpoint on display can be adjusted by pushing the ● enter/save button, increase value by pressing the ▲+ button or decrease the value by pressing the ▼- button, and when the required value is reached, press the ●enter/save button to save the new value.

The alternative displays return to the main display after 20 seconds duration.

Press buttons	Action	Current display	Selected display	Selected display comments
▲	Push + button	REM Q1 Q2 ☐ X1	SP – h ☐ 20.0c	heating day set point.
▲	Push + button	SP – h ☐ 20.0c	SP – h ☐ 16.0c	<b>heating night set point.</b>
▲	Push + button	SP – c ☐ 16.0c	X1 21.0c	X1 - main temperature sensor reading
▲	Push + button	X1 21.0c	X2SP 22° C	X2 – actual remote set point setting
▲	Push + button	X2SP 22° C	3P 50%	Percentage opening position of the heating control valve
▲	Push + button	3P 50%	Q1 OFF	Q1 – heating valve opening digital output
▲	Push + button	Q1 OFF	Q2 OFF	Q2 – heating valve closing digital output
▲	Push + button	Q2 OFF	REM 31 3P	Control sequence diagram and application number display.
▲	Push + button	REM 31 3P	REM Q1 Q2 ☐ X1	Back to main display

Values shown are either default values or nominated for information only.

## Alternatives

- Supply air temperature control.