

QPA20xx Series Indoor Air Quality Room Sensors


Description

The QPA20xx Series Indoor Air Quality Sensors optimize room comfort by enabling demand-controlled ventilation. Models are available that measure CO₂, CO₂ and temperature, or CO₂, temperature and relative humidity.

For models with humidity, a capacitive humidity sensing element changes capacitance as a function of the relative humidity. An electronic measuring circuit converts the humidity signal to a voltage or current (field-selectable) signal that corresponds to a relative humidity range of 0 to 100%. For models with temperature, the sensor acquires room temperature with a sensing element that changes electrical resistance as a function of the temperature. The resistance is converted to a voltage or current output signal that corresponds to a temperature range of 32°F to 122°F (0°C to 50°C) or -31°F to 95°F (-35°C to 35°C).

The QPA2002 models measure both CO₂ and volatile organic compounds (VOC) for optimized indoor air quality. A single output signal is automatically adjusted to reflect the higher of the two values. A secondary output provides CO₂ data. This enables the combination CO₂ + VOC sensor to be easily substituted for a CO₂ sensor in any demand control ventilation control system.

These wall-mounted sensors are designed for use with all systems and devices capable of acquiring and handling a 0 to 10 Vdc or 0 to 5 Vdc output signal.



QPA20xx Series Room Indoor Air Quality Room Sensor and QPA20xxD Series Room Indoor Air Quality Room Sensor with Display.

Features

- Non-Dispersive Infrared (NDIR) CO₂ sensing technology is ideal for use in facilities that are occupied 24/7.
- Combination units enable a single sensor to take the place of up to three individual sensors.
- Maintenance-free infrared CO₂ sensing element never requires re-calibration.
- Field-selectable output provides 0 to 10V, 0 to 5V, or 4 to 20 mA signal(s).

Ordering Information

Part Number	Description
QPA2000	Room CO ₂ Sensor
QPA2002	Room CO ₂ + VOC Sensor*
QPA2002D	Room CO ₂ + VOC Sensor w/Display*
QPA2060	Room CO ₂ + Temperature Sensor
QPA2060D	Room CO ₂ + Temperature Sensor w/Display
QPA2062	Room CO ₂ + Temperature + RH Sensor
QPA2062D	Room CO ₂ + Temperature + RH Sensor w/Display
ARG70	Mounting Plate (Required for installation on 2" x 4" electrical box.)

* Siemens CO₂ + VOC sensors are designed to help maximize occupant comfort and are not suitable for use in life safety applications

General Specifications

Output Signal:

0-10V, 0-5V, or 4-20 mA, selectable, linear

CO₂ Measuring:

Range: 0-2000 ppm

Accuracy: $\leq (\pm 50 \text{ ppm} + 2\% \text{ of measured value})^*$

Temperature dependency: $\pm 2 \text{ ppm}/^\circ\text{C}$ (typical)

Long term drift: $\leq \pm 5\%$ measuring range/5 yrs

* Allow up to 96 hours for unit to reach published accuracy.

Temperature Measuring:

Range: -31°F to 113°F (-35°C to 45°C)

Accuracy: $\pm 1.4^\circ\text{F}$ ($\pm 0.8^\circ\text{C}$)

Humidity Measuring

Range: 0 to 100% rh

Accuracy: $\pm 3\%$ rh (typical 30 to 70% rh)

Power Supply:

Operating voltage (SELV): 24 Vac or 15 to 35 Vdc
 $\pm 20\%$

Frequency: 50/60 Hz

Power consumption: $\leq 2 \text{ VA}$

Electrical:

Screw terminals: 2 \times 16 AWG or 1 \times 14 AWG

Environmental:

Transport:

Temperature: -13°F to 158°F

(-25°C to 70°C)

Humidity: < 95% rh


Physical:

Weight (including packaging): 0.60 lb (0.272 kg)

Miscellaneous:

No calibration required for 8 years.

Dimensions



Dimensions in Inches (mm).

Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced. Products or company names mentioned herein may be the trademarks of their respective owners.
© 2019 Siemens Industry, Inc.