

EU type examination certificate

EU-Baumusterprüfbescheinigung

CE-0085CL0280

Product Identification No.
Produkt-Identnummer

Field of Application <i>Anwendungsbereich</i>	EU Gas Appliances Regulation (EU/2016/426) <i>EU-Gasgeräteverordnung (EU/2016/426)</i>
Owner of Certificate <i>Zertifikatinhaber</i>	Siemens Switzerland Ltd. Building Technologies Division Gubelstrasse 22, CH-6301 Zug
Distributor <i>Vertreiber</i>	Siemens Switzerland Ltd. Building Technologies Division Gubelstrasse 22, CH-6301 Zug
Product Category <i>Produktart</i>	accessories for gas appliances/pressure equipment: Manostat for gas, air and flue gas (4107)
Product Description <i>Produktbezeichnung</i>	Differential manostat for air and non-aggressive gases
Model <i>Modell</i>	QBM81-...; QMB9903-...
Countries of Destination <i>Bestimmungsländer</i>	AT, BE, BG, CH, CY, CZ, DE, DK, EE, ES, FI, FR, GB, GR, HU, IE, IS, IT, LT, LU, LV, MT, NL, NO, PL, PT, RO, SE, SI, SK
Test Reports <i>Prüfberichte</i>	type testing: 18/114/4107/295 from 17.04.2018 (EBI)
Test Basis <i>Prüfgrundlagen</i>	EU/2016/426 A III B (09.03.2016) DIN EN 1854 (01.10.2010)


Date of Expiry / File No. 04.05.2028 / 18-0236-GEA
Ablaufdatum / AZ

06.06.2018 Kö A-1/2

Date, Issued by, Sheet, Head of Certification Body
Datum, Bearbeiter, Blatt, Leiter der Zertifizierungsstelle

DVGW CERT GmbH is an accredited body by DAkkS according to DIN EN ISO/IEC 17065:2013 and notified by the government of the Federal Republic of Germany for certification of gas appliances under EU Regulation

DVGW CERT GmbH ist von der DAkkS nach DIN EN ISO/IEC 17065:2013 akkreditierte und von der Deutschen Bundesregierung benannte Stelle für die Zertifizierung von Gasgeräten gemäß EU-Verordnung EU/2016/426.




DVGW CERT GmbH
Zertifizierungsstelle
Josef-Wirmer-Str. 1-3
53123 Bonn
Tel. +49 228 91 88 - 888
Fax +49 228 91 88 - 993
www.dvgw-cert.com
info@dvgw-cert.com

Type <i>Typ</i>	Technical Data <i>Technische Daten</i>	Remarks <i>Bemerkungen</i>
QBM81-...; QBM9903-...	ambient temperature range: -30...+85 °C max. operating pressure: 50 mbar	

Type Variation <i>Ausführungsvariante</i>	Explanations <i>Erläuterungen</i>
QBM81-3; QBM9903-3	set range: 0,2...3 mbar
QBM81-5; QBM9903-5	set range: 0,5...5 mbar
QBM81-10; QBM9903-10	set range: 1...10 mbar
QBM81-20	set range: 5...20 mbar
QBM81-50	set range: 10...50 mbar
...-30T85	max. operating pressure: 50 mbar, temperature range: -30°C...+85°C
...-30T75	max. operating pressure: 75 mbar, temperature range: -30°C...+75°C

Hints of Utilization /Remarks

Verwendungshinweise / Bemerkungen

Medium: air and non-aggressive gases

pressure connection: hosesport Ø 6 mm

protection class: II

Power supply: 30V/ 50 Hz; 250 V/ 50 Hz; 30 V DC

degree of protection: IP 54, optionally IP 00 (without hood)

switch type: 6/1 (changeover switch, single pole)

installation position: any, for switching-on points < 0,3 mbar vertical or horizontal with electric connections downward