

Sinteso™ Cerberus™ PRO

Line adapter (Ex)

FDCL221-Ex



Addressed (FDnet-Ex/C-NET-Ex)

For operating FDnet-Ex/C-NET-Ex peripheral devices in areas at risk of explosion

- Electrical isolation between non-intrinsically safe and intrinsically safe circuits
- Use on FDnet/C-NET detector lines, on stubs, or loops
- Status indicator/operating indicator with two LEDs
- MC link connection
- Installation in fire control panels or in an installation housing FDCH222

Features

- Protected electronics
- Integrated operating indicator
- Integrated LED for signaling the isolation of the area at risk of explosion

Eco-friendly

- Environmentally friendly processing
- Reusable materials
- Electronic parts and synthetic materials can be separated

Functions


- The line adapter (Ex) is used for electrical isolation purposes and for limiting the electrical energy between non-intrinsically safe and intrinsically safe circuits.
- It is not necessary for the housing to be connected to local ground
- The power required for the line adapter (Ex) to supply itself is taken from the FDnet/C-NET. It is not necessary to connect an external power supply
- Operation possible on an FDnet/C-NET detector line or a stub. There is therefore no line separation function in the area not at risk.
- The line adapter (Ex) has two connections for the detector line (FDnet/C-NET) in the area not at risk and one connection in the area at risk of explosion (FDnet-Ex/C-NET-Ex).
- Two LEDs for displaying the operating status and faults, and for localizing the device




Observe national guidelines and regulations.

- Fields of application:
 - The line adapter (Ex) must not be mounted in the area at risk of explosion.
 - The line adapter (Ex) is used where the operation of Ex peripheral devices is required. It separates the area at risk of explosion from the area not at risk
 - The line adapter (Ex) only makes it possible to operate FDnet-Ex and C-NET-Ex devices There are other safety barriers (SB2, SB3) available for collective systems
 - Changing from existing collective systems to addressable Sinteso and Cerberus PRO fire detection systems

Application in the C-NET



Application in the FDnet



Type Overview

Type	Designation	Order number	Weight [kg]
FDCL221-Ex	Line adapter (Ex)	S54329-F4-A1	0.240

Accessories for the line adapter (Ex) FDCL221-Ex

Type	Designation	Order number	Weight [kg]
TS35 (L = 122 mm)	U-rail TS35/7.5/122	BPZ:5644780001	0.041
TS35 (L = 288 mm)	U-rail TS35/7.5/288	BPZ:5644230001	0.098
FDCH222	Installation housing	S54329-F10-A	1.673

Product documentation

Document ID	Name
008164	Equipment overview Sinteso™ Detector system FD20
A6V10225323	Equipment overview Cerberus™ PRO Detector system FD720
008331	List of compatibility (for 'Sinteso™' product line)
A6V10229261	List of compatibility (for 'Cerberus™ PRO' product line)
A6V10333771	Technical Manual Line adapter (Ex) FDCL221-Ex
A6V10324618	Planning, Mounting/Installation, Commissioning, Maintenance of fire detection installations with addressed detector lines in potentially explosive atmospheres

Related documents such as environmental declarations, CE declarations, etc., can be downloaded at the following Internet address:

<http://siemens.com/bt/download>

Mounting

!	NOTICE
	Ex installations must be carried out by qualified technical personnel. Observe acceptance and documentation specifications.

- The line adapter (Ex) can be accommodated in an intermediate distributor in the riser zone on different floors, or at the former location of the collective control panel. Ideally, it is mounted as close as possible to the area at risk because the cable lengths permitted in the area at risk, which are calculated individually in each case, are limited.
- Installation materials, protective spacing, and necessary markings in potentially explosive areas must correspond to the national directives.
- Observe specifications for insulation between Ex and non-Ex detector lines.

Mounting in fire control panels or in an installation housing

- The line adapter (Ex) can be mounted in a fire control panel FC20xx or FC72x or in an installation housing FDCH222 (accessories). The line adapter (Ex) is installed on a U-rail in both cases.



Disposal


	<p>The device is considered an electronics device for disposal in terms of European Directive 2012/19/EU and may not be disposed of as domestic garbage.</p> <ul style="list-style-type: none"> • Dispose of the device through channels provided for this purpose. • Comply with all local and currently applicable laws and regulations.
--	--

Technical data

	FDCL221-Ex
Operating voltage <ul style="list-style-type: none"> Nominal voltage (U_n) Maximum voltage (U_m) 	DC 12...33 V AC 253 V
Operating current (quiescent) / (max. load)	1.5 µA / 2.5 mA
Operating temperature	-25...+60 °C
Storage temperature	-30...+75 °C
Air humidity	≤95 % rel.
Communication protocol	FDnet/C-NET // FDnet-Ex/C-NET-Ex
Colors: <ul style="list-style-type: none"> Line adapter (Ex) Housing FDCH222 Housing cover 	Black / light blue Gray Transparent
Protection category (IEC/EN 60529) <ul style="list-style-type: none"> Without housing With installation housing FDCH222 	IP20 IP66
Ex classification IECEX	[Ex ia Ga] IIC, Ta = -25...+60 °C [Ex ia Da] IIIC, Ta = -25...+60 °C
Directive 94/9/EC: (ATEX directive)	II (1) G [Ex ia Ga] IIC, Ta = -25...+60 °C II (1) D [Ex ia Da] IIIC, Ta = -25...+60 °C
Standards for areas at risk of explosion	EN 60079-0:2012 EN 60079-11:2012 EN 60079-26:2007 EN 54-18
Ex approvals <ul style="list-style-type: none"> EC-type examination certificate IECEX 	BVS 12 ATEX E 094 BVS 12.0079
EN 54 approvals <ul style="list-style-type: none"> VdS DNV GL (marine) 	G213108 59 825 - 13 HH
System compatibility <ul style="list-style-type: none"> FDnet C-NET 	FS20, AlgoRex, SIGMASYS FS720

Ex-related connection data, intrinsically safe	U_0	28 V
	I_0	92 mA
	P_0	644 mW
	L_0	2.9 mH
	C_0	82 nF
	U_m	253 V

Symbol	Meaning
C_0	Maximum external capacitance
I_0	Maximum output current
L_0	Maximum external inductance
P_0	Maximum output power
U_m	Maximum root mean square value of AC voltage. Maximum permissible voltage of an associated item of electrical equipment without canceling the energy limitation.
U_0	Maximum output voltage

14  0786 0102	FDCL221-Ex	Siemens Switzerland Ltd; Gubelstrasse 22 CH-6301 Zug Technical data: see doc. A6V10333771
		FDCL221-Ex - Input/output device for use in fire detection and fire alarm systems installed in buildings.
305/2011/EU (CPR): EN 54-18 ; 2014/30/EU (EMC): EN 50130-4 / EN 61000-6-3 ; 2011/65/EU (RoHS): EN 50581 ; 2014/34/EU (ATEX): EN 60079-0 / EN 60079-11 / EN 60079-26		
The declared performance and conformity can be seen in the Declaration of Performance (DoP) and the EU Declaration of Conformity (DoC), which is obtainable via the Customer Support Center: Tel. +49 89 9221-8000 or http://siemens.com/bt/download		
DoP No.: 0786-CPR-21322; DoC No.: CED-FDCL221-Ex		

FDCL221-Ex line adapter (Ex)

