

SIEMENS

Ingenuity for life

Desigo® Fire Safety Detectors and Peripherals

Thermal (Heat) Detector Model FDT421

Architect & Engineer Specifications

- Compatible with Siemens Model `H'-series devices on the same loop (with Desigo Fire Safety Modular | FireFinder XLS/V | FC/FV20-series fire-alarm control panels)
- Contains seven (7) field-selectable settings in a temperature range of 135°F – 174°F (57.2°C – 78.9°C)
- Provides a low-temperature warning of 40°F (4.4°C)
- Field programmable as rate-of-rise or fixed temperature
- Tri-color detector-status light-emitting diode (LED) with 360 ° view
- Compatible with Model DPU (device programmer / loop tester)
- Utilizes advanced, microprocessor-based signal processing
- Each detector is self-testing:
 - complete diagnostics performed every 10 seconds
- Polarity insensitive via *SureWire™* technology
- Functions with Model DB-11-series mounting bases
- Superior electromagnetic interference (EMI) and radio-frequency interference (RFI) immunity
- Restriction of Hazardous Substances (RoHS compliant)
- UL 521 Listed, ULC Listed; FM (#3230, #3210), CSFM (#7272-0067:0258) Approved

Product Overview

The Intelligent Thermal (Heat) Detector (Model FDT421) provides an advanced method of detection, address programming supervision – combined with sophisticated FACP communication. Model FDT421 uses a state-of-the-art thermistor, microprocessor and advanced signal analysis, providing high reliability and accuracy.

Additionally, Model FDT421 is a cost-effective, two-wire / addressable thermal detector that provides a distinctive, advanced feature: seven (7) field-selectable temperature settings specially tailored for application-specific detection needs.

The temperature-range settings for each Model FDT421 detector is between 135°F (57°C) – 174°F (79°C) with fixed and rate-of-rise programmability. This variance provides the customer with maximum flexibility to program the temperature settings to suit multiple application needs and changing environmental conditions.

Model FDT421 can be configured to provide a low-temperature warning signal at 40°F (4.4°C). This feature – along with a compatible FACP (Desigo Fire Safety Modular | FireFinder XLS/V or with Desigo FC /FV2025 or FC /FV2050 FACPs) – serves as prevention of water freezing in pipes for sprinkler systems, meeting NFPA 72.

Field-Device Programmer / Test Unit

Model FDT421 is compatible with the Siemens field-device programmer / test unit (Model DPU), which is a compact, portable and menu-driven accessory for electronically programming and testing these addressable detectors promptly and reliably. For instance, the field technician selects the accessory's program mode, and enters the desired address.

Model DPU eliminates the need for cumbersome, unreliable mechanical programming methods (e.g. – dials and rotary switches), and reduces installation and service costs by electronically programming and testing the detector prior to installation. When set in `test' mode, Model DPU will perform a series of diagnostic tests without altering the address or other stored data, allowing technicians to determine if the detector is operating properly.


Each field-device programmer / test unit operates on AC power or rechargeable batteries, providing flexibility and convenience in the programming / testing of fire-safety equipment from practically any location. Additionally, with the use of a Model DPU unit, there is no longer a cause for concern with any vibration, corrosion and other deteriorating conditions that can accompany the vitality of a mechanical-addressing mechanism.

The encompassing result is an intelligent detector that provides enhanced detection capability to a wide range of products of combustion – while offering unsurpassed rejection to nuisance-alarm sources, including: dust | steam | aerosols and other deceptive phenomena that could cause false alarms.



Model FDT421
Thermal (Heat) Detector





1. Thermistor

Model FDT421

Operation

Model FDT421 also utilizes a modern, accurate and shock-resistant thermistor to sense significant changes in temperature.

Each Model FDT421 detector has seven (7) pre-programmed parameter sets that can be selected by the Siemens FACP.

Detector Supervision and Testing

Model FDT421 contains a tri-color LED indicator, capable of flashing any one (1) of three (3) distinct colors: **GREEN** | **YELLOW** | **RED**. During each flash interval, the microprocessor-based detector monitors the following fire-system conditions:

- Temperatures reaching programmed thresholds
- Internal sensors and electronics are functional

Based on the results of the monitoring, the LED indicator flashes the following:

FLASH COLOR	CONDITION	FLASH INTERVAL [in seconds]
GREEN*	Normal supervisory operation. Temperature has not reached programmed alarm thresholds or set points.	10
YELLOW:	Detector is not operating at normal capacity and needs replacement.	4
RED:	'Alarm' condition	1
NO FLASH:	Detector is not powered.	–

* denotes LED can be turned OFF

Please follow the corresponding description of the panel used.

A quick visual inspection is sufficient to indicate the condition of the detector at any time.

If more detailed information is required, a printed report can be provided from the respective Desigo Fire Safety Modular | FireFinder XLS/V or Model FC20-series FACPs that indicates the status and settings assigned to each individual detector.

Installation

All Model FDT421 detectors use a surface-mounting base, Model DB-11 or Model DB-11E, which mounts on a 4-inch (10.2 cm.) octagonal, square or single-gang electrical box. The base utilizes screw-clamp contacts for electrical connections and self-wiping contacts for increased reliability.

The Model DB-11 detector base can be used with the optional Siemens Model LK-11 detector locking kit, which contains 50 detector locks and an installation tool to prevent unauthorized removal of the detector head. Model DB-11 has aesthetically conducive plugs to cover the outer mounting-screw holes.

Model FDT421 may be installed on the same initiating circuit with the Siemens Model 'H'-series detectors [when used with Desigo Fire Safety Modular | Model FC20-series | FireFinder XLS/V FACPs] –

- HFP-11, HFPT-11
- Model 'XTRI'-series interfaces
- Model 'HTRI'-series interfaces
- Model 'HMS'-series manual stations
- Model HCP output-control detection devices
- Model 'HZM'-series of addressable, conventional zone modules

1. Dust cover

2. Thermal (heat) detector

NOTE: Each detector consists of a dust-resistant chamber, a solid state, functional internal sensor, and microprocessor-based electronics with a low-profile plastic housing. Every Model FDT421 fire detector is shipped with a protective dust cover.



Application Data

Installation of Model FDT421 intelligent, addressable thermal detectors requires a two-wire circuit. In many retrofit cases, existing wiring may be used. 'T-tapping' is permitted only for Style 4 (Class B) wiring. Model FDT421 is polarity insensitive, which can greatly reduce installation and debugging times.

Model FDT421 can be applied within the maximum 50-feet (15.24 m.) center spacing (2,500 sq. ft. [762 sq. m.]) per Underwriters' Laboratories. This application guide is based on ideal conditions, specifically, smooth-ceiling surfaces, minimal air movement, and no physical obstructions between potential fire sources and the actual detector. Do not mount detectors in close proximity to heating | ventilation | air-conditioning (HVAC) outlets. Exposed joists or beamed ceilings may also affect safe spacing limitations for detectors.

Should questions arise regarding detector placement, observe NFPA 72 guidelines. Good fire-protection system engineering and common sense dictate how and when fire detectors are installed and used. Contact your local Siemens – Fire Safety distributor or sales office whenever you need assistance applying Model FDT421 in unusual applications.

Be sure to follow NFPA guidelines and UL Listed / ULC Listed installation instructions – included with every Siemens – Fire Safety detector – and local codes for all fire-protection equipment.

Specifications

Model FDT421 is a plug-in, (2) two-wire thermal (heat) detector, compatible with Desigo Modular | FireFinder XLS/V and Model FC20-series FACP's. Each Model FDT421 detector has microcomputer-chip technology and highly stable, solid-state electronic circuitry. Model FDT421 detectors utilize a modern, accurate and shock-resistant thermistor to sense temperature changes. This electronic-sensing method virtually eliminates thermal lag associated with mechanical temperature-sensing devices, and provides almost instantaneous temperature status to the FACP.

Model FDT421 provides seven (7) field-selectable, pre-programmed temperature settings:


- Fixed 135°F (57°C)
- Fixed 145°F (63°C)
- Fixed 155°F (68°C)
- Fixed 165°F (74°C)
- Fixed 174°F (79°C)
- Rate-of-Rise: 15°F / min. (8.3°C) at fixed 135°F (57°C)
- Rate-of-Rise: 15°F / min. (8.3°C) at fixed 174°F (79°C)

Additionally, the Model FDT421 detector has the following optional feature:

- Model FDT421 provides indication of potential water freezing for sprinkler systems, via configuration for reporting a low-temperature warning of 40°F (4.4°C).

This feature is compatible with Desigo Modular systems, as well as with FireFinder XLS/V and Desigo FC/FV2025 or FC/FV2050 FACP's.

Mounting Diagrams | Dimensions



Technical Data	
OPERATING TEMPERATURE:	+32° – +120°F (0° – +49°C) [with 145°F (63°C) 155°F (68°C) 165°F (74°C) and 174°F (79°C) alarm-threshold settings]
THERMAL RATING:	Model FDT421 provides seven (7) field-selectable, pre-programmed temperature settings: <ul style="list-style-type: none"> • Fixed 135°F (57°C) • Fixed 145°F (63°C) • Fixed 155°F (68°C) • Fixed 165°F (74°C) • Fixed 174°F (79°C) <ul style="list-style-type: none"> • Rate-of-Rise: 15°F / min. (8.3°C) at fixed 135°F (57°C) • Rate-of-Rise: 15°F / min. (8.3°C) at fixed 174°F (79°C)
RELATIVE HUMIDITY:	0 – 95% (non-condensing)
AIR PRESSURE:	No effect
INPUT VOLTAGE RANGE:	16VDC – 30VDC
'ALARM' CURRENT, MAX.:	410µA
'STANDBY' CURRENT, MAX.:	250µA, max. (average)
MAXIMUM SPACING:	50-ft. (15.24 m.) centers (2500 sq. ft. 762 sq. m.), per NFPA 72 and ULC-S524
DETECTOR WEIGHT:	0.317 Lbs. (0.144 kg.)

Panel Compatibilities		
MODEL OR TYPE	DATA SHEET	PANEL
XLS	6300	FireFinder (fire)
XLSV	6340	FireFinder (fire w/ voice)
DESIGO MODULAR	7300	Desigo Modular (overview)
FC2005	6813	Desigo Fire Safety 50-point addressable
FC2025	6815	Desigo Fire Safety 252-pt. addressable (fire)
FC2050		Desigo Fire Safety 504-pt. addressable (fire)
FV2025	6821	Desigo Fire Safety 252-point addressable (fire w/ Intelligent Voice Communication [IVC])
FV2050		504-pt. addressable (fire w/ Intelligent Voice Communication [IVC])

Details for Ordering		
MODEL OR TYPE	PART NUMBER	PRODUCT
FDT421	S54320-F5-A1	Thermal (Heat) Detector
Compatible Devices:		
MODEL OR TYPE	PART NUMBER	PRODUCT
ABHW-4B	S54320-F13-A1	Sounder base with Loop-Power Option
ABHW-4S	S54320-F14-A1	Sounder base for Sleeping Areas
ADB-BOX	500-698360	Surface Mount Adapter Box for Audible Base
DB2-HR	S54370-F12-A1	Relay base compatible with Siemens standard and advanced detectors
DB-11	500-094151	Detector Mounting Base
DB-11E	500-094151E	Detector Base, small
RL-HC	500-033230	Remote Alarm Indicator: 4" (10.2 cm) octagon-box mount, red
RL-HW	500-033310	Remote Alarm Indicator: single-gang box mount, red
LK-11	500-695350	Base Locking Kit
See: www.STI-USA.com for further details on ordering Model STI-9604		
In Canada order:		
MODEL OR TYPE	PART NUMBER	PRODUCT
DB-11C	500-095687	Detector Mounting Base, ULC Listed

NOTICE – The information contained in this data-sheet document is intended only as a summary, and is subject to change without notice. The product(s) described here has/have a specific instruction sheet(s) that cover various technical, limitation and liability information.

Copies of install-type, instruction sheets – as well as the *General Product Warning and Limitations* document, which also contains important data, are provided with the product, and are available from the Manufacturer.

Data contained in the aforesaid type of documentation should be consulted with a fire-safety professional before specifying or using the product.

Any further questions or assistance concerning particular problems that might arise, relative to the proper functioning of the equipment, please contact the Manufacturer.

SIEMENS

Desigo® Fire Safety

Siemens Industry, Inc.
Building Technologies Division
8 Fernwood Road • Florham Park, NJ 07932
Tel: (973) 593-2600

March 2018 – Supersedes sheet dated 10/2017
(Rev. 6)