



TX-I/O™

## Blinds module

## TXM1.8RB

- 8 non-floating relay outputs for...
  - 4 blinds motors with 2 end switches, or
  - 2 blinds motors with 3 end switches, or
  - 2 blinds motors with 2 end switches  
+ 1 blinds motor with 3 end switches
- Switching voltage AC 100...250 V
- Green status LED to indicate status for each I/O point
- Current measurement for each blinds motor for end position detection
- Compact design as per DIN, requiring little space
- Separation into terminal base and electronics unit for optimal handling
  - Self-connecting bus for the easiest possible installation
  - Isolating terminal function for fast commissioning
  - Exchange of electronics unit within seconds without a need of rewiring, at full functionality of the remaining I/O modules
- Terminal strips are required to connect N and PE of the field devices
- Simple display concept
  - Lit I/O status LEDs for the outputs when relays are active
  - LEDs for fast fault diagnosis
- Double-sided labeling of all I/O points with label

## Functions

The module supports the following I/O function:

Signal type	Description
<b>BO Blind Relay</b>	Maintained contact relay, for blinds control with 2 / 3 end switches

See document "TX-I/O™ Functions and operation", CM110561, for a detailed description of this function.

## Compatibility

For signal type support and functionality in the various building automation and control systems, see TX-I/O™ engineering and installation manual, CM110562.

## Ordering

Type	Stock number	Designation
TXM1.8RB	S55661-J105	Blinds module

## Delivery

Terminal base and electronics unit are assembled and delivered in a box.


## Accessories

Address keys, printable label sheets and replacement label holders are available as accessories. See data sheet CM2N8170.

## Design and technology

See the TX-I/O™ Engineering and installation manual, CM110562, for a description of the properties for all TX-I/O™ modules.

## Operating and display elements



## Output status LEDs

- The output status LEDs indicate the relay status. The LEDs are also used for diagnostics.

## Module status LED

- The module status LED illuminates the transparent address key.
- The LED (green) indicates the status for the entire module (contrary to the I/O point status).
- It can also be used for diagnostic purposes.

## Address key

- The module only works with the address key.
- The module address is mechanically encoded in the address key.
- Swing out the address key when exchanging the electronics unit. The key remains in the terminal base.

## Terminal

- The relay contact lines are interconnected (in the electronics unit). Active mains power must be supplied separately to each terminal strip.
- Different phases for the different terminals strips are allowed.


## End position detection

- The end position of the blind is detected using a current measurement. Measurement reports "On" when the motor exceeds a minimum current / motor power (see technical data).

## Module labeling

---

The electronics unit has a removable, transparent lid (label holder) allowing for insertion of the label.



## Disposal

---



"The device is considered electronics device for disposal in terms of European Directive 2012/19/EU and may not be disposed of as domestic garbage. The device must be disposed of via the proper channels. Observe all local and applicable laws.

## Engineering, mounting, installation

---

Please consult the following documents:

Document	Number
TX-I/O™ Functions and operation	CM110561
TX-I/O™ Engineering and installation manual	CM110562

## Mounting

### Allowed mounting positions

TX-I/O™ devices can be mounted in any position:

You must ensure, however, that sufficient ventilation is available to maintain the permissible ambient temperature (max. 50°C).

### Technical data

Power supply (side bus connector)	Operating voltage	DC 21.5 ... 26 V
	Safety extra-low voltage SELV or protection by extra-low voltage PELV per HD384	
	Max. power consumption (see CM110562 for supply design)	1.4 W
Protection	Bus connector on side	No protection against shortcut and incorrect wiring with AC / DC 24 V
Switching outputs	Number of switching outputs	8 (NO contacts)
	External supply line fusing	
	<ul style="list-style-type: none"> <li>• Non-renewable fuse, slow</li> <li>• Miniature circuit breaker MCB</li> </ul>	Max. 10 A Max. 13 A
	Tripping characteristic MCB	B, C, D as per EN 60898
	Contact data	
	Switching voltage	Max. AC 100 to 250 V
	Motor current	Max. 3 A
	⚠ *) Switch-on current (max. 1 s) *)	Max. 10 A *)
	Minimum current	Min. 1 mA at AC 250 V
	Pickup/dropout time	7 ms / 3 ms typical
Current measurement	"On"	$I \geq 0.2 \text{ A}$
	"Off"	$I \leq 0.1 \text{ A}$
Contact life for AC 250 V (guide values)	Up to 2 A	$1 \times 10^5$ switchings
	Up to 3 A	$5 \times 10^4$ switchings
	Insulating strength	AC 3000 V, as per EN 60730-1

\*) **Caution:** Some motor manufacturers do not comply with these specifications (very short switch-on current peaks >10 A).

This is not always stated in the data sheets. For customer projects, clarify the type and properties of motors in an early phase. If in doubt, investigate or perform tests / measurements.

This applies for blinds motors as well as linear actuators for window applications.

Connection terminals	Mechanical design	Screw-type terminal
	Wire	1 x 0.5 mm <sup>2</sup> to 4mm <sup>2</sup> or 2 x 0.6 mm dia. to 1.5 mm <sup>2</sup>
	Copper stranded wire without ferrules	1 x 0.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> or 2 x 0.6 mm dia. to 1.5 mm <sup>2</sup>
	Stranded wire with ferrule (DIN 46228/1)	1 x 0.25 mm <sup>2</sup> to 2.5 mm <sup>2</sup> or 2 x 0.6 mm dia. to 1.5 mm <sup>2</sup>
	Screwdriver	No. 1 Screwdriver for slotted or recessed-head * screws with shaft diameter ≤ 4.5 mm * Combined slotted / recessed-head screws from mid-2012
	Max. tightening torque	0.6 Nm
Test plug socket (test terminals)	Pin diameter	1 x 1.8 to 2.0 mm

Classification per EN 60730	Operation of automatic controller Degree of pollution Mechanical design	Type 1 2 Devices suited for use with equipment of safety classes I and II
Housing protection type	Degree of protection as per EN 60529 Front parts in DIN excerpt Terminal part	IP30 IP20
Environmental conditions	Operation	As per IEC 60721-3-3
	Climatic conditions	Class 3K5
	Temperature	-5...50 °C
	Relative humidity	5...95% r.h.
	Mechanical conditions	Class 3M2
	Transport / storage	As per IEC 60721-3-2
	Climatic conditions	Class 2K3
	Temperature	-25...70 °C
	Relative humidity	5...95% r.h.
	Mechanical conditions	Class 2M2
Standards and directives	Product standard	EN 60730-1
	EU conformity (CE)	T10870xx *)
	Electromagnetic compatibility	For residential, commercial and industrial environments
	RCM conformity (EMC)	T10870en_C1 *)
	UL approbation	UL 916
	*) The documents can be downloaded from <a href="http://siemens.com/bt/download">http://siemens.com/bt/download</a> .	
Environmental compatibility	Product environmental declaration (contains data on RoHS compliance, materials composition, packaging, environmental benefit, disposal)	CM1E8178
Color	Terminal base and electronics unit	RAL 7035 (light-gray)
Dimensions	Housing as per DIN 43880, see dimensions	
Weight	With/without packaging	208 / 229 g

**Connection diagrams (example)**


**Terminal assignment**

Output	TXM1.8RB							
	(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)
Supply line *)	11				28			
NO contact	6 ▼	8 ▲	14 ▼	16 ▲	23 ▼	25 ▲	31 ▼	33 ▲

\*) Different phases allowed for terminals 11 and 28


**Blinds with 2 end switches**

2 blinds can be connected per terminal strip



**Blinds with 3 end switches**

1 set of blinds can be connected per terminal strip (the 4<sup>th</sup> terminal must remain free)




**Note!**

- Because of the current measurement, interposing relays for the control of several blinds in parallel are not admitted.
- **Parallel operation of more than one blinds motor on the same terminal is not admissible!**

# Dimensions

Dimensions in mm



Published by:  
Siemens Switzerland Ltd.  
Building Technologies Division  
International Headquarters  
Gubelstrasse 22  
6301 Zug  
Switzerland  
Tel. +41 41-724 24 24  
[www.siemens.com/buildingtechnologies](http://www.siemens.com/buildingtechnologies)

© Siemens Switzerland Ltd 2012  
Delivery and technical specifications subject to change