



LMV2/3 – flexible and easy burner management system

Highlights

- Integrated electronic air-fuel ratio control and gas valve proving
- One unit for oil- and gas-fired operation with predefined fuel trains
- Straightforward and quick commissioning
- Modbus communication
- Continuous operation with ionization current supervision
- Global approvals (CE, UL, CSA, AGA)

The LMV2/3 burner management system, with integrated electronic air-fuel ratio control, is used for the control of modulating or multistage oil or gas burners of medium capacity.

The benefits offered by electronic air-fuel ratio control are independent ratio curve settings and flexibility in terms of burner design. Fuel and air actuators can be fitted anywhere without having to give consideration to mechanical linkage.

Depending on the individual unit versions, the LMV2/3 burner management system provides a number of variable program sequences for control of the burner. There is a choice of gas and oil programs, with or without pilot burner, depending on the applications and the basic unit version.

In the case of LMV26 dual-fuel burner controls for Europe, or LMV36 for North America, any 2 fuel trains can be combined.

Variable speed drive control integrated in the different versions of the LMV2/3 is the ideal solution for efficient and favorably priced operation.

Straightforward and flexible connection of the load controller is made possible via Modbus, analog 4...20 mA interface, or 3-position step control.

Technical data (extract)


For further information, see documentation 7541/7544/7546/7547.

Mains voltage	AC 120 V -15% / +10% AC 230 V -15% / +10%
---------------	--

AZL – the small supporter for LMV2/3

The AZL2 display and operator units are designed for use with LMV2/3 air-fuel ratio control to be mounted directly on the burner or in control panels close to the burner. They are designed for the display, operation and parameterization of specific safety and non-safety-related burner functions. Key plant data and lockout codes can be called up and displayed.

Alternatively the ACS410 software tool can be used with all LMV2/3 air-fuel ratio controls. It serves as a tool to display data, to set parameters and to store data.



Standards and certificates (extract)



Conformity to EC directives:

- Electromagnetic compatibility EMC (immunity) 2004/108/EC
- Gas-fired appliances directive 90/396/EC
- Low-voltage directive 2006/95/EC
- Directive for pressure devices 97/23/EC



ISO 9001: 2008
ISO 14001: 2004



Manufacturer declaration for SIL3

Siemens AG
Building Technologies Division
Control Products & Systems
Berliner Ring 23
76437 Rastatt
Germany
Tel +49 7222 598 279
Fax +49 7222 598 269

www.siemens.com/buildingtechnologies-oem

Type reference (extract)

For further information, see documentation 7541/7544/7546/74547

LMV26.300A2	LMV27.100A2	LMV36.520A1	LMV37.400A2	LMV37.420A1 (US)	
Operating modes					
x	x	x	x	x	- Intermittent operation - Continuous operation (only with ionization probe, without AGM60...)
Basic applications, single-fuel operation					
x	x	x	x	x	- Light oil direct ignition, 2- or 3-stage electronic ratio control - Light oil direct ignition, electronic modulating ratio control - Gas direct ignition, electronic/pneumatic modulating ratio control - Gas pilot ignition, electronic/pneumatic modulating ratio control - Dual-fuel burner gas / light oil with gas pilot ignition
Application dual-fuel operation					
x		x	x	x	- VSD control with separate curve adjustment and speed feedback - Dual fuel switch unit AGM60...
Flame detectors for intermittent operation					
x	x	x	x	x	- Ionization probe - UV detector QRA2..., QRA4.U, QRA10... - Photoresistive flame detector QRB... - Blue-flame detector QRC...
Flame detectors for continuous operation					
		x	x	x	Ionization probe
External integration of load controller					
x	x	x	x	x	- Input heat request - Preset burner output via Modbus from building automation - Input multistage, shifting multistage or modulating (3-position signal) - 4...20 mA signal input for preset burner output
Inputs/outputs					
x		x			- Fuel selection
x	x	x	x	x	- Preset burner output 4...20 mA
x	x	x	x	x	- Current burner output DC 0...10 V
x		x	x	x	- VSD control DC 0...10 V (alternative to indication of output)
Special feature					
			x	x	- Switching back to pilot

Communication in nearly all languages

Communication is becoming more and more important. For this reason, the LMV2/3 burner management system can be integrated into different types of higher level process management systems via the open and affordably priced standardized Modbus communication interface. Important actual values and setpoints can be continuously monitored. Information about parameter settings and the plant's error history can be read out, evaluated and assessed.

