


4300 Power Meter



Application

The Siemens 4300 power meter is designed for high-accuracy electrical metering of power distribution equipment in industrial, commercial, institutional and utility applications. It continuously collects, displays and communicates real-time and minimum/maximum data. Data may be viewed at the meter's high visibility display or via communications at a supervisory computer. Operators may select specific data to display or configure the meter by using the sealed membrane keypad.

A communications port allows the 4300 power meter to be used as a stand-alone power monitoring station or as one element in a large energy-management network.

The 4300 power meter replaces multiple analog meters and selector switches, thus making it economical for 3-phase digital power metering.

Construction

The 4300 power meter is built for use in industrial environments. Rugged microprocessor-based technology meets ANSI/IEEE C37.90 requirements for radio frequency interference (RFI), surge withstand and fast transient tests. Complies with FCC/DOC emissions standard. Recognized under UL 1244. Programmed settings, energy counters, minimum/maximum values and other important data is saved on-board in non-volatile memory when power is turned off.

4300 Power Meter Features

The 4300 Power Meter provides the following features:

- Metering includes phase currents and average phase current, phase to phase voltages and average phase to phase voltage, line voltages and average line voltage, peak kW demand, 3-phase kW total, 3-phase kVAR total, 3-phase kVA total, kW demand, kW hours, power factor and frequency
- Large, easy to read, 20 character LCD display
- Convenient installation in new or retrofit applications. Display unit fits standard U.S. analog meter drilling pattern and is connected to the instrument compartment module via cable. This dual module system eliminates the need for voltage transformers on most low voltage applications
- Communications module connects to the Siemens ACCESS™ electrical distribution communications system
- Configuration is password protected and may be done at the meter or remotely through communications
- Easy upgrades using RS-485 communications port

4300 Power Meter

Technical Specifications

4300 Power Meter

Metered Values

The following table provides a listing of metered values.

Parameter	Accuracy	Resolution	Range
Volts & Volts Demand	0.5%	0.1%	0-999,999 ¹
Amps & Amps Demand	0.5%	0.1%	0-9,999
kW & kW Demand	1.0%	0.1%	0-999,999
Power Factor	2.0%	1.0%	0.6 lag to 0.6 lead
kVAH ²	1.0%	1kVAH	0-999,999 ²
kVA & kVA Demand	1.0%	0.1%	0-999,999 ²
kVAR	1.0%	0.1%	0-999,999 ²
Frequency	0.2 Hz	0.1 Hz	45-70 Hz

1. Reads in kV (x1000) for readings over 9,999
2. Reads in M (x1,000,000) for readings over 9,999


Input Ratings

The following table provides input and power supply information for the 4300 Power Meter.

Voltage Inputs	
Standard	120 to 347VAC nominal full-scale input (programmable)
Overload withstand	600VAC continuous, 1500VAC for 1 second
Input impedance	1MΩ
Current Inputs	
Standard	5.000A AC nominal full-scale input
Overload withstand	15A continuous, 300A for 1 second
Input impedance	0.002Ω
Burden	0.05VA
1 Amp Option	1.0 A AC nominal full scale
Power Supply	
Standard	108-132VAC / 0.05A / 47 to 66 Hz
Optional	216-264VAC / 0.125A / 47 to 66 Hz
Operating temperature	0°C to +50°C (-32°F to +122°F) ambient air
Storage temperature	-30°C to +70°C (-22°F to +158°F)
Humidity	5% to 95%, non-condensing


Mounting Dimensions

Below is a diagram displaying the dimensions of the 4300 Power Meter.



Ordering Information

The order number is generated by inserting the selection code into the appropriate box. For additional information on ordering SIEMENS ACCESS products, please call 1-800-427-2256 or your SIEMENS representative.



Siemens Energy & Automation, Inc.
Power Distribution Solutions
3333 Old Milton Parkway
Alpharetta, GA 30005

For Nearest Sales Office
1.800.964.4114
www.sea.siemens.com/sales/salesoffices.html

For More Information Visit
www.sea.siemens.com/access

© Siemens Energy & Automation, Inc.
Siemens is a registered trademark of Siemens AG.
Specifications are subject to change without notice.

All registered trademarks are of Siemens AG.

Order No. XXTA-00106-0899
3M0799CP Printed in the U.S.A.