


Fan coil unit with variable fan, heating and cooling coil (4 pipe) on analog output

DXR2.E09-101A



- Heating with LTHW and cooling with CHW
- Modulating control of heating and cooling valve (4 pipe) on analog output
- Automatic or manual variable fan speed control DC 0...10 V
- Room temperature and fan speed operation via KNX PL-Link room operator unit with temperature measurement


Plant diagram



|         |                                |    |  |
|---------|--------------------------------|----|--|
| DXR2... | Room automation station        | R  | Room                                       |
| B1      | Extract air temperature sensor | R1 | Room operator unit with temperature sensor |
| B3      | Supply air temperature sensor  | YC | Cooling coil valve                         |
| D1      | Window contact                 | YH | Heating coil valve                         |
| D2      | Presence detector              |    |  |
| Q1      | Variable speed fan             |    |  |


Function diagrams

Heating/cooling valves



|     |                            |
|-----|----------------------------|
| Q   | Fan output signal          |
| SpC | Effective cooling setpoint |
| SpH | Effective heating setpoint |
| TR  | Room temperature           |

DC 0...10 V fan



|    |                     |
|----|---------------------|
| Y  | Valve output signal |
| YC | Cooling coil valve  |
| YH | Heating coil valve  |

## Fan coil unit with variable fan, heating and cooling coil (4 pipe) on analog output

DXR2.E09-101A

### Description of functions

#### Basic functions

- PID control for heating and cooling.
- The 4 pipe system provides hot and chilled water for the heating coil and the cooling coil.
- 0...10 V valves controlled by analog outputs for heating and cooling.
- The fan is controlled manual on the room operator unit or automatic with variable speed.
- The temperature is measured in the room operator unit.
- The application allows customers to adjust the room temperature setpoints via the room operator unit.
- The operating modes are Comfort, Pre-Comfort, Economy and Protection.
- Change of operating mode via room unit, presence detector, window contact or central command.
- The air flow for heating and cooling is operated in sequence to the valves. Parallel operation can be configured.

#### Auxiliary functions

- Green Leaf (RoomOptiControl) function.
- Multisegment use of DXR2 automation stations with fan coil unit application.
- Standard hot and cold water supply chain control.
- The application allows for control via centralized commands (e.g. scheduler program for room operating mode).
- Central optimum start control provides best room comfort at the start of occupancy.
- Central operation or reset of setpoints, timed valve kick function or outside temperature dependent heating limit.
- Central override functions for valves.
- Seasonal compensation of room temperature setpoints.

#### Options

- Optimal energy efficiency by including the option for room/supply air cascade control, presence detector or window contact.
- Optional system alarms displayed on the management station notify building operators of possible faults.
- Optional trends can be activated for room sensors.

#### Variants

- The room temperature can be measured by:
  - KNX PL-Link wall-mount sensor
  - KNX PL-Link flush-mount room operator unit
  - KNX PL-Link flush-mount sensors
  - Analog extract air temperature sensor
- Presence can be detected by KNX PL-Link sensor or binary sensor.

| Siemens devices | Legend  | Type of unit  | Data sheet | Product No.   | Qty. |
|-----------------|---------|---|------------|---------------|------|
|                 | DXR2... | Compact room automation station, BACnet/IP, 230 V, flat housing, 1 DI, 2 UI, 3 DO relays, 3 AO 0...10 V | N9204      | DXR2.E09-101A | 1    |
|                 | R1      | KNX PL-Link room operator unit with temperature sensor, segmented backlit display, touchkeys            | N1602      | QMX3.P34      | 1    |
|                 | YC      | 2-port, 3-port valve or 3-port valves with bypass, PN16   | N4845      | V..P45..      | 1    |
|                 |         | Electromotive actuator, AC/DC 24 V, DC 0...10 V   | N4864      | SSP61         | 1    |
|                 | YH      | 2-port, 3-port valve or 3-port valves with bypass, PN16   | N4845      | V..P45..      | 1    |
|                 |         | Electromotive actuator, AC/DC 24 V, DC 0...10 V   | N4864      | SSP61         | 1    |

| Optional <sup>1)</sup> | Legend | Type of unit   | Data sheet    | Product No. | Qty.          |
|------------------------|--------|--|---------------|-------------|---------------|
|                        | B1     | Cable temperature sensor PVC 2 m, LG-Ni1000          | N1831         | QAP22       | 1             |
|                        | B3     | Cable temperature sensor PVC 2 m, LG-Ni1000          | N1831         | QAP22       | 1             |
|                        | D1     | Door/window contact, white                           | <sup>2)</sup> | S 290/11    | <sup>3)</sup> |
|                        | D2     | KNX PL-Link presence detector with brightness sensor | <sup>2)</sup> | UP 258D12   | 1 - 4         |

<sup>1)</sup> Can be combined according to available on-board I/Os on controller.

<sup>2)</sup> Further documents on [www.siemens.com/gamma-td](http://www.siemens.com/gamma-td).


<sup>3)</sup> Type of operation (NO or NC). Multiple devices of the same type can be connected.

Fan coil unit with variable fan, heating and cooling coil (4 pipe) on analog output

DXR2.E09-101A

| Variants        | Legend | Type of unit                                       | Data sheet | Product No.            | Qty. |
|-----------------|--------|--|------------|------------------------|------|
| R1 <sub>a</sub> |        | KNX PL-Link wall-mount room sensor for temperature | N1602      | QMX3.P30               | 1    |
| R1 <sub>b</sub> |        | KNX PL-Link flush-mount room operator unit         | N1601      | QMX3.P36               | 1    |
| R1 <sub>c</sub> |        | KNX PL-Link flush-mount room sensors               | N1411      | AQR253...<br>AQR257... | 1    |

Connection diagram



## Fan coil unit with variable fan, heating and cooling coil (4 pipe) on analog output

DXR2.E09-101A

### Application configuration

|                     | Equipment                   | Values/Range  | Template settings                |
|---------------------|-----------------------------|---|----------------------------------|
| On-board output     | Fan speed                   | 1-stage; Q14; Normally open<br>2-stage; Q14, Q24; Normally open<br>3-stage; Q14, Q24, Q34; Normally open<br>Variable speed; Y10; 0...10 V | Variable speed; Y10;<br>0...10 V |
|                     | Enable fan speed            | Q14; Normally open  | Q14; Normally open               |
|                     | Cooling coil valve position | Water; Y20; 0...10 V  | Water; Y20; 0...10 V             |
|                     | Heating coil valve position | Water; Y30; 0...10 V<br>Electric modulating; Y30; 0...10 V  | Water; Y30; 0...10 V             |
| KNX PL-Link devices | Room operator unit device 1 | QMX3.P02, QMX3.P34, QMX3.P36, QMX3.P37, QMX3.P74  | QMX3.P34                         |

### Optional configuration

|                     | Equipment                   | Values/Range | Template settings   |
|---------------------|-----------------------------|--------------|---------------------|
| On-board input      | Room temperature (B1)       |              | X1; LG-Ni1000       |
|                     | Supply air temperature (B3) |              | X2; LG-Ni1000       |
|                     | Presence detector 2 (D2a)   |              | X1, Normally open   |
|                     | Window contact (D1)         |              | D1; Normally closed |
| KNX PL-Link devices | Sensor device 1...4 (D2)    |              | UP 258D12           |

### Default values


|                       | Parameter                              | Values/Range   | Template settings        |
|-----------------------|--|--|--------------------------|
| Temperature setpoints | Cooling setpoint for Comfort           | 0 ... 50 °C  | 24 °C                    |
|                       | Delta cooling setpoint for Pre-comfort | 0 ... 10 K   | 1 K                      |
|                       | Cooling setpoint for Economy           | 0 ... 50 °C  | 35 °C                    |
|                       | Cooling setpoint for Protection        | 0 ... 50 °C  | 40 °C                    |
|                       | Heating setpoint for Comfort           | 0 ... 50 °C  | 21 °C                    |
|                       | Delta heating setpoint for Pre-comfort | 0 ... 10 K   | 1 K                      |
|                       | Heating setpoint for Economy           | 0 ... 50 °C  | 15 °C                    |
|                       | Heating setpoint for Protection        | 0 ... 50 °C  | 12 °C                    |
| Room operator unit    | Room unit, display temperature         | None<br>Display room temperature                         | Display room temperature |
|                       | Room unit, display windows status      | Yes, No  | No                       |
|                       | Room unit, display heat./cool. status  | Yes, No  | Yes                      |
|                       | Enable operation: room temp. setpoint  | Yes, No  | Yes                      |
|                       | Room unit, room temp. setpoint display | Absolute temperature setpoint<br>Relative setpoint shift | Relative setpoint shift  |
|                       | Enable operation: fan speed setpoint   | Yes, No  | Yes                      |
|                       | Enable operation: presence button      | Yes, No  | No                       |
|                       | Enable operation: temporary Comfort    | Yes, No  | No                       |
|                       | Enable operation: room op. mode        | Yes, No  | No                       |
|                       | Enable operation: Green Leaf           | Yes, No  | Yes                      |

**Fan coil unit with variable fan, heating and cooling coil (4 pipe) on analog output**

DXR2.E09-101A

**Engineering**

- ABT Site engineering tool is required to configure the DXR2 automation stations.
- See the Siemens Download Center at [www.siemens.com/bt/download](http://www.siemens.com/bt/download) for the latest application configuration and workflow tutorials.
- Option combination according to available on-board I/Os on controller.
- B1 (optional extract air temperature sensor) to be configured under 'Room temperature' in order to serve for room temperature control.
- D2<sub>a</sub> (on-board presence detector) to be configured in ABT Site under 'Presence detector 2' for maximum combination of optional devices.  
Type of operation (NO or NC). Multiple devices of the same type can be connected.

**Management station**

Sample presentation of a fan coil unit application on the Desigo CC management station.

Siemens Switzerland Ltd  
Building Technologies Division  
International Headquarters  
Gubelstrasse 22  
CH-6301 Zug  
Tel. +41 41-724 24 24  
Fax +41 41-724 35 22  
[www.siemens.com/buildingtechnologies](http://www.siemens.com/buildingtechnologies)

© 2015 Siemens Switzerland Ltd  
Subject to change