


t [s]

Time in Seconds





Time Current Characteristics Curve
SIEMENS DG Frame Circuit Breaker

Thermal Magnetic Circuit Breaker 2, 3 & 4-Pole
 For application and coordination purposes only.
 Based on 40°C ambient, cold start. Tested
 in open air with current in all poles.

Interruption Ratings


Type	Maximum Trip Unit Rating (I_n)	Symmetrical RMS Amperes		
		240V	480V	600V
NDGA	50 Amp	65kA	35kA	18kA
HDGA		100kA	65kA	20kA
LDGA		200kA	100kA	25kA

806992KA0



$I_i - \text{Min.}$ $I_i - \text{Max.}$


Magnetic Pickup Tolerance



For Max. Interruption Rating
 See table above.

t [s]

Time in Seconds





Time Current Characteristics Curve
SIEMENS DG Frame Circuit Breaker

Thermal Magnetic Circuit Breaker 2, 3 & 4-Pole
 For application and coordination purposes only.
 Based on 40°C ambient, cold start. Tested
 in open air with current in all poles.


Interruption Ratings

Type	Maximum Trip Unit Rating (I_n)	Symmetrical RMS Amperes		
		240V	480V	600V
NDGA	60, 70 Amp	65kA	35kA	18kA
HDGA		100kA	65kA	20kA
LDGA		200kA	100kA	25kA

806992KB0




Magnetic Pickup Tolerance



For Max. Interruption Rating
 See table above.

t [s]

Time in Seconds









Time Current Characteristics Curve
SIEMENS DG Frame Circuit Breaker

Thermal Magnetic Circuit Breaker 2, 3 & 4-Pole
For application and coordination purposes only.
Based on 40°C ambient, cold start. Tested
in open air with current in all poles.


Interruption Ratings

Type	Maximum Trip Unit Rating (I_n)	Symmetrical RMS Amperes		
		240V	480V	600V
NDGA	80, 90, 100, 110, 125, 150 Amp	65kA	35kA	18kA
HDGA		100kA	65kA	20kA
LDGA		200kA	100kA	25kA

806992KC0



Magnetic Pickup Tolerance



For Max. Interruption Rating
See table above.