

## Type QT circuit breakers

### Features and benefits

- 1/2 inch width-per-pole construction: dual and quad styles
- Requires 1/2 the space of 1 inch width circuit breakers
- SWD rated — 15 and 20 amp.
- HACR rated
- UL listed
- CSA certified

Siemens type QT dual circuit breakers are 1 inch wide and consist of (2) 1-pole breakers, in varying combinations of ampere ratings from 15 to 30 amp. Type QT quad circuit breakers are 2 inches wide and consist of either (1) 2-pole and (2) 1-pole, or (2) 2-pole breakers. 2-pole constructions range from 15-50 amps and are available with internal common trip.

All type QT circuit breakers are plug-in style and load terminals are provided with the units. They are rated for 120/240V AC and calibrated for 40C maximum ambient applications. The standard interrupting rating is 10k AIC.



Q1515

Q22020CT2

Breaker type	Dimensions (inches)		
	Length	Width	Depth
Dual	3-1/8	1	3
Quad	3-1/8	2	3

## Selection information

### QT dual breaker,(2) 1-Poles 10k AIC interrupting rating

Ampere rating	Complete breaker unenclosed		Wire range	
	Catalog number		Cu	Al
15-15	Q1515 <sup>①</sup>		#14 - #8	#12 - #8
15-20	Q1520 <sup>①</sup>		#14 - #8	#12 - #8
20-20	Q2020 <sup>①</sup>		#14 - #8	#12 - #8
20-30	Q2030		#14 - #6	#12 - #6

**Shipping:** 12 per carton, 48 per master carton (Wt. 20 lbs.)

### QT quad breaker,(1) 2-Pole & (2) 1-Poles,<sup>②</sup> common trip 10k AIC interrupting ratings

Ampere rating	Complete breaker unenclosed		Wire range	
	Catalog number		Cu	Al
15-15	Q21515CT		#14 - #8	#12 - #8
15-20	Q21520CT		#14 - #8	#12 - #8
15-25	Q21525CT		#14 - #8	#12 - #8
15-30	Q21530CT		#14 - #6	#12 - #6
15-40	Q21540CT		#8 - #6	#8 - #4
15-50	Q21550CT		#8 - #6	#8 - #4
20-20	Q22020CT		#14 - #8	#12 - #8
20-30	Q22030CT		#14 - #6	#12 - #6
20-40	Q22040CT		#8 - #6	#8 - #4
20-50	Q22050CT		#8 - #6	#8 - #4

**Shipping:** 6 per carton, 24 per master carton (Wt. 20 lbs.)

① For Non-CTL version, add "NC" to end of catalog number.

② The 1-Pole circuit breakers are always 15 or 20 amp. Example: The Q21540CT is (1) 2-Pole, 40 amp and (2) 1-Pole, 15 amp.



### QT quad breaker,(2) 2-Poles, common trip 10k AIC interrupting rating

Ampere rating	Catalog number	Wire range	
		Cu	Al
15-15	Q21515CT2 <sup>①</sup>	#14-#8	#12-#8
15-30	Q21530CT2	#14-#6	#12-#6
20-20	Q22020CT2 <sup>①</sup>	#14-#8	#12-#8
20-50	Q22050CT2	#8-#6	#8-#4
30-20	Q23020CT2 <sup>①</sup>	#14-#6	#12-#6
30-25	Q23025CT2	#14-#6	#12-#6
30-30	Q23030CT2 <sup>①</sup>	#14-#6	#12-#6
30-50	Q23050CT2	#8-#6	#8-#4
40-20	Q24020CT2 <sup>①</sup>	#8-#6	#8-#4
40-30	Q24030CT2 <sup>①</sup>	#8-#6	#8-#4
40-40	Q24040CT2 <sup>①</sup>	#8-#6	#8-#4

**Shipping:** 6 per carton, 24 per master carton (Wt. 20 lbs.)

## Knockout diagrams

Quad (dual would be same profile, but 1" wide) dimensions (inches)



Siemens Industry, Inc.  
5400 Triangle Parkway  
Norcross, GA 30092  
1-800-964-4114  
info.us@siemens.com

Subject to change without prior notice  
Order No.: CBFL-SQ198-1112

All rights reserved  
Printed in USA  
© 2012 Siemens Industry, Inc.

[www.usa.siemens.com](http://www.usa.siemens.com)

The information provided in this flyer contains merely general descriptions or characteristics of performance which in case of actual use do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.

All product designations may be trademarks or product names of Siemens AG or supplier companies whose use by third parties for their own purposes could violate the rights of the owners.