

Outdoor Combination Metering

CATALOG NUMBER:

JC0404L1400RLM


FOR OVERHEAD AND UNDERGROUND SERVICE SURFACE MOUNT

SUITABLE ONLY FOR USE AS SERVICE EQUIPMENT.

CAUTION: CIRCUIT MAY BE LIVE WITH METER REMOVED.

DEVICE RATING:
400 AMPS MAXIMUM; 120/240 V ~ (4 JAW) OR 208Y/120 V ~ (5 JAW); SINGLE PHASE, THREE WIRE.

METER SOCKET: 4 JAW; LEVER OPERATED BYPASS WITH JAW TENSION RELEASE.
RATING: 400 AMPS (320 AMPS CONTINUOUS)



ENCLOSURE
TYPE 3R

TERMINAL TIGHTENING TORQUES LB.-IN.:

| kcil OR AWG | □ | ⊗ | ⊕ | ⊙ |
|----------------|-----|-----|----|-----|
| 600 - 500 kcil | 500 | - | - | - |
| 500 - 350 kcil | 500 | - | - | 450 |
| 350kcil-3/0 | 500 | 250 | - | 450 |
| 2/0 | - | 250 | 50 | - |
| 1/0-#6 | - | 250 | 50 | - |

TERMINAL RANGES, kcil OR AWG:

- = LIMITED TO (1)600kcil-#4 OR (2)350kcil-1/0
- ⊗ = (1)#250kcil-6
- ⊕ = (1)2/0-#12
- ⊙ = LIMITED TO (1) 500kcil-3/0 OR (2) 250kcil-3/0

ACCESSORIES

| | |
|---------------------------------|----------|
| FILLER PLATE | QF3 |
| 5TH JAW SHIELD | S35815-2 |
| FOR HUB, ORDER FROM "HD" SERIES | |
| COVERPLATE | S56933 |
| 3" HUB | S56856-2 |
| 3 1/2" HUB | S56857-2 |
| 4" HUB | S56858-2 |

HARDWARE TIGHTENING TORQUES:
3/8 NUTS 250-350 IN.-LBS.


4099821 Rev.B

THIS DEVICE HAS A MAXIMUM SHORT CIRCUIT CURRENT RATING OF 65,000 AMPS RMS SYMMETRICAL, 120/240 V ~. WATTHOUR METER IS NOT INCLUDED IN SHORT CIRCUIT CURRENT RATING. THE ACTUAL RATING IS EQUAL TO THE LOWEST INTERRUPTING RATING OF ANY INSTALLED CIRCUIT BREAKERS. USE ONLY MURRAY TYPE MP-T, MP-HT, MP-MT, MD-T, MD-HT, MD-MT, MD-TR, MD-HTR, OR MD-MTR CIRCUIT BREAKERS. ANY CIRCUIT BREAKER INSTALLED, REPLACED, OR ADDED IN THIS PANELBOARD MUST BE ONE OF THESE TYPES. USE OF OTHER CIRCUIT BREAKERS IN THIS EQUIPMENT WILL VOID THE WARRANTY.

WARNING: THIS DEVICE HAS BEEN DESIGNED FOR USE ONLY WITH THOSE CIRCUIT BREAKERS AS LISTED ABOVE. THE USE OF OTHER CIRCUIT BREAKERS COULD RESULT IN PROPERTY DAMAGE OR PERSONAL INJURY.

ALL OPENINGS MUST BE FILLED WITH BREAKERS OR FILLER PLATES.

FOR BREAKERS WITH TRIPPED POSITION IN CENTER, RESET BREAKER BY MOVING HANDLE TO "OFF" AND THEN TO "ON". DEVICE SUITABLE FOR USE WITH BREAKERS MARKED 60/75°C. FOR INSTALLATION IN ACCORDANCE WITH ALL LOCAL ELECTRICAL CODES AND/OR THE NATIONAL ELECTRICAL CODE.®



TERMINALS SUITABLE FOR USE WITH 60/75°C, AL/CU INSULATED WIRE.

CAUTION: PAINTS, PLASTER, HYDROCARBON BASED SPRAYS, LUBRICANTS OR SOLVENTS CAN DAMAGE THIS EQUIPMENT. DO NOT ALLOW THESE OR OTHER CONTAMINANTS TO CONTACT INTERIOR COMPONENTS.

® THE NATIONAL ELECTRICAL CODE IS A REGISTERED TRADEMARK OF THE NATIONAL FIRE PROTECTION ASSOCIATION.

D

Murray Electrical Products
Siemens Energy & Automation, Inc.
Alpharetta, Georgia U.S.A.



4099822 Rev.A