

TPS3 L5

True 10 Mode Protection

Surge Protection Device (SPD) for P4 & P5 Panelboards and Distribution Switchboards

Features:

- Mounts internal to:
 - P4 & P5 panelboards and distribution switchboards
- UL 1449 3rd Edition – 2009, cUL
- UL 1283
- Type 1 SPD (Type 2 cUL)
- Large block, individually fused, thermally protected, 50kA MOV's
- 20kA I_n (most models)
- 200kA SCCR (most models)
- All UL-required OCP & safety coordination included
- UL96A Lightning Protection Master Label compliant (@20kA In)
- Panelboard
 - Copper or aluminum bus
 - MB or MLO
- Switchboard Features
 - Copper or aluminum bus
 - 200% rated neutral bus for harmonic-rich applications
 - CSA, UL 891, UL 67 and NEMA PB-2
- Applications
 - Provides main service or downstream protection for sensitive computer and electronic loads
 - Standard redundancy use: 150kA per phase
 - Maximum redundancy use: 300kA per phase
- SPD Specifications
 - Directly connected discrete protection elements between all possible modes providing true 10 mode protection
 - Surge Current Rating Per Phase

Per Phase	L-N	L-G	N-G
150kA	50kA	50kA	50kA
300kA	100kA	100kA	100kA
 - 100% monitoring – every MOV is monitored, incl. N-G
 - EMI/RFI filtering: active tracking up to -50db from 10kHz to 100MHz
 - Repetitive impulse: 5,000 hits
 - Less than ½ nanosecond response time
 - Relative humidity range: 1-95% non-condensing
 - Operating frequency: 47-63Hz
 - Operating temperature: -25°C (-15°F) to +60°C (140°F)



UL 1449 3rd Edition SPD

SIEMENS

- SPD Features
 - UL 1449 3rd Edition effective September 2009
 - Designed, manufactured & tested consistent with:
 - ANSI/IEEE C62.41.1-2002, C62.41.2-2002, and C62.45-2002
 - 1992/2000 NEMA LS-1
 - NEC Article 285
 - IEC 61643, CE
 - Large block, individually fused, thermally protected, 50kA MOV's
 - Direct bus connected or can be wired to a circuit breaker (include W option)
 - 10 year warranty


- SPD Monitoring
 - LED indicators
 - Audible alarm with silence switch and test button
 - Dry contacts
 - Internal rotary disconnect switch

- Available Options
 - Surge counter

- Key Specifications
 - UL 1449 3rd Edition - 2009, cUL
 - UL 1283
 - Type 1 SPD ❶
 - Audible alarm with silence switch and test button
 - Dry Contacts
 - EMI/RFI Filtering
 - Protection modes on L-N, L-G, L-L, N-G
 - I_n Rating - 20kA
 - Short Circuit Current Rating - 200kA
 - Surge Current Rating
 - Per Phase = L-N + L-G + L-L
 - 150kA 50kA 50kA 50kA

Ordering Information

Catalog #




- Example: TPS3CL530X = 10 mode SPD for a 208/120V Power Panel with a surge current capacity of 300kA per phase and a surge counter option
- When an option is not selected include, a zero (0) in the field


Available Accessories: Ordered Separately

- RMSIE = Remote monitor


UL 1449 3rd Edition - 2009 Test Data Summary									
Voltage Protection Rating (VPR - 6kV, 3kA)									
Voltage Code	Service Voltage	L-N	L-G	N-G	L-L	Type ❶	I _n	SCCR	MCOV
A	120/240V, 1Ø, 3W (Fig 1)	700	700	700	1200	Type 1	20kA	100kA	150
B	120/240V, 3Ø, 4W (Fig 3)	800 / 1500	700 / 1200	700	1800/1800	Type 1	20kA	200kA	150 / 320
C	120/208V, 3Ø, 4W (Fig 2)	700	700	700	1000	Type 1	20kA	200kA	150
E	277/480V, 3Ø, 4W (Fig 2)	1500	1200	1200	1800	Type 1	20kA	200kA	320
K	380/220V, 3Ø, 4W (Fig 2)	1500	1200	1200	1800	Type 1	20kA	200kA	320
S	400/230V, 3Ø, 4W (Fig 2)	1500	1200	1200	1800	Type 1	20kA	200kA	320



Split
2 Hots, 1 Neu, 1 Grnd



Wye
3 Hots, 1 Neu, 1 Grnd



Hi-Leg Delta (B High)
3 Hots, (B High),
1 Neu, 1 Grnd

Siemens Industry, Inc.
Building Technologies Division
5400 Triangle Parkway
Norcross, GA 30092

888-333-3545
info.us@siemens.com

©2010 Siemens Industry, Inc.
All Rights Reserved. Siemens is a registered trademark of Siemens AG. Product names mentioned may be trademarks or registered trademarks of their respective companies. Specifications are subject to change without notice.

Notes:

- ❶ Type 2 cUL