



SIEMENS

Ingenuity for life

Medium-voltage vacuum generator circuit breakers

Drawout type GMSG-GCB

Siemens drawout vacuum generator circuit breaker offering for 10 MW to 80 MW machines

Siemens type GM-SG or GM-SG-AR indoor and outdoor metal-clad switchgear can be supplied with IEEE C37.013-tested drawout vacuum generator circuit breakers. The features and benefits of metal-clad construction are available with this offering.

Features and benefits:

- One-high or two-high drawout construction
- Up to 50 full-fault interruptions
- Front accessible circuit breaker operating mechanism for ease of maintenance
- Closed door racking
- Floor rollout circuit breaker in lower cell without a dolly
- Visible secondary disconnect
- Circuit breaker ships inside of cell, thus reducing installation cost and potential transit damage
- Pair with Siemens protective relays to provide complete generator protection
- Drawout type GMSG-GCB vacuum generator circuit breaker with type 3AH3 operating mechanism

- Uses the latest developments in vacuum interrupter technology
- Highly reliable vacuum interrupters - MTTF over 50,000 years
- Common type 3AH3 operator platform
- Over 120,000 type 3AH3 operators produced since 1998
- Generator circuit breakers tested to IEEE C37.013/C37.013a
- 10,000 operations to overhaul
- Three-cycle interrupting time (optional)
- Meets or exceeds the latest ANSI, IEEE, and NEMA standards
- UL or C-UL Listing available
- Available in lineups of conventional type GM-SG or GM-SG-AR switchgear, indoor or outdoor
- SIERS integrated electrical-racking system available (optional)
- Optional arc-resistant construction to ANSI/IEEE C37.20.7, up to 63 kA, 0.5 sec, accessibility type 2B.

For larger machines up to 200 MW, refer to Siemens stationary type vacuum generator circuit breaker offering.



Rated values and related capabilities	IEEE C37.013 clause	Units	Circuit breaker type ³		
			15-GMSG-GCB-40-XXXX-110	15-GMSG-GCB-50-XXXX-137	15-GMSG-GCB-63-XXXX-173
Rated maximum voltage (V)	5.1	kV	15.0	15.0	15.0
Power frequency	5.2	Hz	60	60	60
Rated continuous current	5.3	A	1,200, 2,000, 3,000, 4,000 FC	1,200, 2,000, 3,000, 4,000 FC	1,200, 2,000, 3,000, 4,000 FC
Rated dielectric strength (withstand voltage) 1. Power frequency, one minute 2. Impulse	5.4.2 C37.013a, Table 4	kV kV peak	38 95	38 95	38 95
Rated short-circuit duty cycle	5.5		CO-30 min-CO	CO-30 min-CO	CO-30 min-CO
Rated interrupting time ^{1,2}	5.6	ms	< 80 ms	< 80 ms	< 80 ms
Rated short-circuit current 1. System source (100%) (I) 2. Generator source (50%)	5.8.1 5.8.2.3	kA sym kA sym	40 20	50 25	63 31.5
dc component		%	75	64	61
Asymmetry ratio (historical "S" factor)		----	1.46	1.35	1.32
Asymmetrical interrupting (ref)		kA rms	57.9	67.5	83
Delayed current zero capability		ms	40	30	30
Close and latch capability (274% I)		kA peak	110	137	173
Short-time current carrying capability (100% I)	5.8.2.7	kA sym	40	50	63
Short-time current duration	5.8.2.7	s	3	3	3
Transient recovery voltage (TRV) rating System source 1. E ₂ peak voltage 2. RRRV (TRV rate) 3. T ₂ time-to-peak	5.9 C37.013a, Table 5	kV kV/μs μs	27.6 (1.84 V) 3.5 9.3 (0.62 V)	27.6 (1.84 V) 4.5 7.2 (0.48 V)	27.6 (1.84 V) 4.5 7.2 (0.48 V)
Generator source 1. E ₂ crest voltage 2. RRRV (TRV rate) 3. T ₂ time-to-peak	C37.013a, Table 6	kV kV/μs μs	27.6 (1.84 V) 1.6 20.25 (1.35 V)	27.6 (1.84 V) 1.8 18.0 (1.20 V)	27.6 (1.84 V) 1.8 18.0 (1.20 V)
Out-of-phase 1. E ₂ crest voltage 2. RRRV (TRV rate) 3. T ₂ time-to-peak	C37.013a, Table 9	kV kV/μs μs	39.0 (2.6 V) 3.3 13.4 (0.89 V)	39.0 (2.6 V) 4.1 10.8 (0.72 V)	39.0 (2.6 V) 4.1 10.8 (0.72 V)
Rated load-current switching capability	5.10	A	1,200, 2,000, 3,000	1,200, 2,000, 3,000, 4,000	1,200, 2,000, 3,000, 4,000
Out-of-phase current switching capability	5.12	kA	20	25	31.5
Mechanical endurance		operations	10,000	10,000	10,000

Footnotes:

¹ Interrupting time is based on the first current zero occurring not later than 66 ms after fault initiation, for example, %dc component <100.

² Interrupting time of 50 ms available, provided that the first current zero occurs no later than 50 ms after fault initiation.

³ "xxxx" in type designation refers to the continuous current rating 1,200 A, 2,000 A, or 3,000 A, as appropriate. The 4,000 A fan-cooled rating is achieved using a 3,000 A circuit breaker in combination with fan cooling in the switchgear structure (indoor only). Assuming 13.8 kV generator voltage and load current of 4,000 A with fan cooling.

Published by Siemens Industry, Inc. 2018

Siemens Industry
7000 Siemens Road
Wendell, North Carolina 27591

For more information, including service and parts, please contact our Customer Support Center.
Phone: +1 (800) 333-7421

usa.siemens.com/mvswitchgear

Article No. E50001-F710-A256-V3-4A00

© 2018 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.