

# Commercial/Residential Portable Generators

**A/C Rated output watts: 1800**  
**A/C Maximum output watts: 2050**

Emissions certification: 49/CSA



## Features

- OHV splash lubrication
- High performance alternator
- Steel fuel tank with fuel gauge
- Hardened steel tube cradle
- Circuit breaker protected outlet
- Low tone muffler

## Customer connections

### Connection outlets


A: (2) 5-20R 120V

### Circuit breakers

M: (1) 15A

### Other features

H: Off/On/Start switch



## Data Sheet

[www.usa.siemens.com/generators](http://www.usa.siemens.com/generators)


**SIEMENS**

## Specifications

Product series	PG0018
Configuration/emissions	49/CSA
A/C rated output watts:	1800
A/C maximum output watts:	2050
A/C voltage	120VAC
A/C frequency	60 Hz
Rated 120/240 VAC amperage	15.0
Max 120/240 VAC amperage	17.1
Engine displacement	163cc
Engine type	OHV
Engine RPM	3600
Recommended oil	5W30
Lubrication method	Splash sump
Choke type	Manual lever
Fuel shut off	Manual lever
Idle control	Full speed
Starting method	Manual
Battery	N/A
Battery size	N/A
Low oil shutdown method	Low level
Start switch type	On/Off toggle
Switch location	On control panel
Single-point lifting eye	N/A
Fuel gauge	Built-in tank
Fuel tank capacity (Gal)	4.00
Fuel tank capacity (Ltrs)	15.14
Run time at 50% (Hours)	14.50
Cord set	N/A
Handle style	N/A
Wheel type	N/A
Maintenance kit	Sold separately

## Dimensions and weights

Length (L)	23.5
Width (W)	17.0
Height (H)	17.5
Extended length (EL)	23.5
Carton length	24.3
Carton width	18.0
Carton height	18.3
Unit Weight (lbs)	79.0
Shipping Weight (lbs)	90.5



Siemens Industry, Inc.  
 Building Technologies Division  
 5400 Triangle Parkway  
 Norcross, GA 30092

1-800-964-4114  
 info.us@siemens.com

©2010 Siemens Industry, Inc.  
 All Rights Reserved. Siemens is a registered trademark of Siemens AG. Product names mentioned may be trademarks or registered trademarks of their respective companies. Specifications are subject to change without notice.

RPFL-PG018-0110

[www.usa.siemens.com/generators](http://www.usa.siemens.com/generators)