


**I-T-E® Molded Case Circuit Breakers**  
 Multiples of Circuit Breaker Continuous Current Rating



**Time-Current Characteristic Curve**  
**I-T-E® Circuit Breaker**

**EQ-Frame, Types QP, BQ** **1 Pole**  
**Types QP, BQ, BL, QT®** **60 Hz** **120/240 Volts**

For application and coordination purposes only. Based on 40°C ambient cold start. Connected with 4 feet of rated wire (75°C) per terminal. Tested in open air with current in all poles.

**Instantaneous Trip Table**

Rating Amperes	Fixed Instantaneous Trip Amperes
15-20	160-210
25-40	350-550
45-50	450-700
55-70	575-800

**Interrupting Rating**

Breaker Type	Symmetrical Rms Amperes			
	120V	120/240V	240V	277V
QP	-	10,000	-	-
BL-BQ	-	10,000	-	-
QT	-	10,000	-	-

① Single pole test data at 25°C  
 ② Sample instantaneous shown (20 Amp Only). For other instantaneous trip values, see table.  
 ③ One and Two pole units (15 and 20 amp. only).