

The Siemens logo is displayed in a bold, teal, sans-serif font.

Ingenuity for life

A photograph showing a row of Siemens VersiCharge electric vehicle charging station posts installed outdoors. The posts are white and mounted on a concrete curb. A white electric car is plugged into the first post. The background features green bushes and a building.

VersiCharge electric vehicle charging station post



- **Mount VersiCharge™**
Enjoy the freedom of installing any VersiCharge EV charger wherever it is needed with a freestanding post.
- **Secure your charger**
A convenient loop design is included in the VersiCharge post so you can easily add a lock of choice to secure the charger to the post.
- **PV and rust resistant finish**
The VersiCharge Post is built to the standard of all other Siemens NEMA 4R enclosures and ready to withstand tough weather conditions, PV rays and salt water spray. It can be located indoor or outdoor.
- **Multiple wiring options**
With the VersiCharge Post, you have the option to run the power supply under ground to come in through the bottom of the post or to come in via a convenient knock out located at the bottom of the post if the wires are ran through conduit above ground.
- **Cord management system**
An arm located on the side of the post easily holds the cord when not in use.
- **Space for personalized logo**
Add a company sticker on the post to make it your own.



Catalog number: VCPPOST (compatible with VC30GRYU, VC30GRYHW)

usa.siemens.com/versicharge

Dimensions



Published by
Siemens Industry, Inc. 2017.

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

For more information, please contact
our Customer Support Center.
Phone: 1-800-241-4453
E-mail: info.us@siemens.com

usa.siemens.com/versicharge

Order No.: RPFL-VERPO-1117 BA
Printed in U.S.A.
© 2017 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.