

Power Mod™

Cross Bus Main modules (type WXB) offer two distinct functions: first they can be used to connect Siemens Sentron Busway to a Power Mod line-up. Second they can be utilized to offer lower service disconnect ampacities or unique configurations where an incoming tapbox is preferred. See application pages for examples.

Features include:

- QuickSystem™ features
- Incoming & outgoing bus connections (right to left or left to right)
- Standardized connection points to Siemens Sentron Busway
- 65K AIC standard, 100K AIC available for all models
- Externally accessible breaker handle with padlock capability
- Broad ampacity ratings up to 1200 Amps with non-standard amperages available (such as 700, 900, etc.)
- Field installable shunt trips

Cross Bus Mains quick reference

- 200-1200A
- 1200A thru-bus rating
- UL Standard # UL67
- UL file # E27100
- AIC rating (65k & 100k)
- Voltage:
 - Single phase 120/240V AC max
 - Three phase 240V AC max
- All swing latches and rivets are stainless steel
- NEMA 3R rated
- G90 galvanized steel
- ANSI 61 paint
- Custom options available! Details on p. 62



Cross Bus Main modules

Power Mod: Type WXB Main Units

Connects via thru
bussing only - NO LUGS
and NOT SERVICE
ENTRANCE RATED



1-phase, 3-wire SN, 120/240V AC^②

Catalog number (65k AIC)	Catalog Number (100k AIC) ^①	Ampere rating	Service Feed	Breaker Type	Dimensions ^①		
					Height	Width	Depth
WXB1200 ^③	WXB1200U	200	Thru Bus	JXD6	27.05	15.59	10.82
WXB1250 ^③	WXB1250U	250	Thru Bus	JXD6	27.05	15.59	10.82
WXB1300 ^③	WXB1300U	300	Thru Bus	JXD6	27.05	15.59	10.82
WXB1350 ^③	WXB1350U	350	Thru Bus	JXD6	27.05	15.59	10.82
WXB1400	WXB1400U	400	Thru Bus	JXD6	27.05	15.59	10.82
WXB1450 ^③	WXB1450U	450	Thru Bus	LXD6	27.05	15.59	10.82
WXB1500 ^③	WXB1500U	500	Thru Bus	LXD6	27.05	15.59	10.82
WXB1600	WXB1600U	600	Thru Bus	LXD6	27.05	15.59	10.82
WXB1700 ^③	WXB1700U	700	Thru Bus	MXD6	36.05	18.70	12.63
WXB1800	WXB1800U	800	Thru Bus	MXD6	36.05	18.70	12.63
WXB1900 ^③	WXB1900U	900	Thru Bus	NXD6	36.05	18.70	12.63
WXB11000	WXB11000U	1000	Thru Bus	NXD6	36.05	18.70	12.63
WXB11200	WXB11200U	1200	Thru Bus	NXD6	36.05	18.70	12.63

3-phase, 4-wire SN, 240V AC max^②

Catalog number (65k AIC)	Catalog Number (100k AIC) ^①	Ampere rating	Service Feed	Breaker Type	Dimensions ^①		
					Height	Width	Depth
WXB3200 ^③	WXB3200U	200	Thru Bus	JXD6	27.05	15.59	10.82
WXB3250 ^③	WXB3250U	250	Thru Bus	JXD6	27.05	15.59	10.82
WXB3300 ^③	WXB3300U	300	Thru Bus	JXD6	27.05	15.59	10.82
WXB3350 ^③	WXB3350U	350	Thru Bus	JXD6	27.05	15.59	10.82
WXB3400	WXB3400U	400	Thru Bus	JXD6	27.05	15.59	10.82
WXB3450 ^③	WXB3450U	450	Thru Bus	LXD6	27.05	15.59	10.82
WXB3500 ^③	WXB3500U	500	Thru Bus	LXD6	27.05	15.59	10.82
WXB3600	WXB3600U	600	Thru Bus	LXD6	27.05	15.59	10.82
WXB3700 ^③	WXB3700U	700	Thru Bus	MXD6	36.05	18.70	12.63
WXB3800	WXB3800U	800	Thru Bus	MXD6	36.05	18.70	12.63
WXB3900 ^③	WXB3900U	900	Thru Bus	NXD6	36.05	18.70	12.63
WXB31000	WXB31000U	1000	Thru Bus	NXD6	36.05	18.70	12.63
WXB31200	WXB31200U	1200	Thru Bus	NXD6	36.05	18.70	12.63

^① Dimensions shown are representative of outside box dimensions and do not include allowances for mounting bumps, endwalls, covers, hubs, or hardware protrusions. Dimensions are subject to change.

^② Connects via thru bussing only - NO LUGS and NOT SERVICE ENTRANCE RATED

^③ Non Standard Item - extended lead time applies