




REVISION	DATE	BY	DATE	BY
			15/11/23	PP
1	DESIGN UPDATE	16/10/06	PP	VERIF'D

Confidential - Property of Siemens Industry, Inc.		
CUSTOMER		
ORDER NO.	DWG. NO.	1
	3F3Y015FCD16	SH 1 OF 2


SIEMENS

CATALOG NO. 3F3Y015FCD16 SERIAL NO. 15 kVA 60 Hz 3 PHASE 3.9 % IMP AT 135 °C	SERIES H 30 °C AVG. AMBIENT 40 °C MAX. AMBIENT (H1 H2 H3) 480V V 10 kV BIL (X0 X1 X2 X3) 208Y/120V V 10 kV BIL	 <p style="text-align: center;">VOLTS CONNECT</p> <p style="text-align: center;">1 2 3 4 5 6 7</p>
WINDING MATERIAL CU ENCLOSURE TYPE 3R WEIGHT 215 LBS ENERGY EFFICIENCY EXCEEDS CSA C802.2-2012 DOE 10 CFR PART 431:2016 SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 3 INCHES		
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA <small>dsu0086e</small>		
  TYPE K DRY TYPE TRANSFORMER LR 3902 E112313 SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY OSP-0136-10 IBC 2012/ASCE 7-10 SDS<=2.0g z/h=1 p=1.5		




3F3Y015FCD16

FRONT VIEW



SIDE VIEW



All Dimensions in inches

ENCLOSURE COLOR : ANSI-61 GREY PAINT OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR #14-2 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential - Property of
Siemens Industry, Inc.

REVISION	DATE	BY	DATE	BY
			15/11/23	PP
				CHEK'D
1	16/10/06	PP		VERIF'D

CUSTOMER		
ORDER NO.	DWG. NO.	1
	3F3Y015FCD16	SH 2 OF 2

1.0_jwen 2016/10/06 09:37