

Table 1-4-1
MECHANICAL SWITCHING RATINGS AND TEST VALUES
FOR AC CONTROL-CIRCUIT CONTACTS AT 50 OR 60 HERTZ (see 4.1.2)

Contact Rating Designation	Thermal Continuous Test Current, Amperes	Maximum Current, Amperes									
		120 Volts		240 Volts		480 Volts		600 Volts		Voltamperes	
		Make	Break	Make	Break	Make	Break	Make	Break	Make	Break
A150	10	60	6.00	7200	720
A300	10	60	6.00	30	3.00	7200	720
A600	10	60	6.00	30	3.00	15	1.50	12	1.20	7200	720
B150	5	30	3.00	3600	360
B300	5	30	3.00	15	1.50	3600	360
B600	5	30	3.00	15	1.50	7.5	0.75	6	0.60	3600	360
C150	2.5	15	1.5	1800	180
C300	2.5	15	1.5	7.5	0.75	1800	180
C600	2.5	15	1.5	7.5	0.75	3.75	0.375	3.00	0.30	1800	180
D150	1.0	3.60	0.60	432	72
D300	1.0	3.60	0.60	1.80	0.30	432	72
E150	0.5	1.80	0.30	216	36

Table 1-4-2
MECHANICAL SWITCHING RATINGS AND TEST VALUES FOR DC CONTROL-CIRCUIT CONTACTS
(see 4.2.2)

Contact Rating Designation	Thermal Continuous Test Current, Amperes	Maximum Make or Break Current, Amperes			Voltamperes
		125 Volts	250 Volts	301 to 600 Volts	
		N150	10	2.2	
N300	10	2.2	1.1	275	
N600	10	2.2	1.1	0.40	275
P150	5.0	1.1	...	138	
P300	5.0	1.1	0.55	138	
P600	5.0	1.1	0.55	0.20	138
Q150	2.5	0.55	...	69	
Q300	2.5	0.55	0.27	69	
Q600	2.5	0.55	0.27	0.10	69
R150	1.0	0.22	...	28	
R300	1.0	0.22	0.11	28	