



**TIME-CURRENT CHARACTERISTIC CURVE  
I-T-E® CIRCUIT BREAKER**

**TYPE BQCH** **2 & 3 POLES**

For application and coordination purposes only. Based on 40°C ambient cold start. Connected with four (4) feet of rated wire (60/75°C) per terminal. Tested in open air with current in all poles.

**MAXIMUM VOLTS**

<b>BREAKER TYPE</b>	<b>AC VOLTS</b>
BQCH	60 Hz 277/480

**BREAKER RATING**

<b>CONTINUOUS AMPERES</b>	<b>INSTANTANEOUS TRIP, AMPERES</b>
15-100	See Curve

**INTERRUPTING RATING (UL Listed)**

<b>BREAKER TYPE</b>	<b>SYMMETRICAL RMS AMPERES</b>	
	<b>240 VOLTS</b>	<b>277/480 VOLTS</b>
BQCH	65,000	14,000