



General Duty

Type 1	
Old Catalog Number	New Catalog Number
2 Pole, 400 A	
GF225N	GF225NA
GF225NH	
GHN325N	
GHN325NH	GFC225NA
GFC225N	
ID225	
2 Pole, 600 A	
GF226N	GF226NA
GF226NH	
GHN326N	
GHN326NH	GFC226NA
GFC226N	
ID226	
3 Pole, 400A	
GF325NR	GF325NRA
GF325NRH	
GHN425NW	
GHN425NWH	GF325NA
GF325N	
GF325NH	
GHN425N	GNF325A
GHN425NH	
GNF325	
GFC325N	GFC325NA
3 Pole, 600A	
GF326NR	GF326NRA
GF326NRH	
GHN426NW	
GHN426NWH	GF326NA
GF326N	
GF326NH	
GHN426N	GNF326A
GHN426NH	
GNF326	
GFC326N	GFC326NA

Type 3R	
Old Catalog Number	New Catalog Number
2 Pole, 400A	
GF225NR	GF225NRA
GF225NRH	
3 Pole, 400 A	
GHN325NW	GF226NRA
GHN325NWH	
2 Pole, 600A	
GF226NR	GF226NRA
GF226NRH	
3 Pole, 600A	
GHN326NW	GFC226NA
GHN326NWH	

SIEMENS



usa.siemens.com/safetyswitches

Siemens new 400/600 amp enclosed switch

Siemens Industry, Inc.
3333 Old Milton Parkway
Alpharetta, GA 30005

1-800-241-4453
info.us@siemens.com

Subject to change without prior notice.
Order No: SSBR-46AES-0715
All rights reserved.
Printed in USA
©2015 Siemens Industry, Inc.

usa.siemens.com/safetyswitches

Key product features:

- UL98 and CSA certified, HP rated and approved for service entrance applications.
- Compact one piece light weight construction with enables easier installation even in tight spaces.
- Multiple break current path for excellent loaded endurance, reduces heat and increases switching speed.
- Extended endurance cycles provides three time the UL requirement.
- 400 amp switch has two lugs 1/0 – 600 MCM; using two smaller wires vs. one large wire can significantly reduce installation cost.
- Lay-in lugs provide for easier wiring. Lug cap is removable and dramatically reduces the need for vertical insertion of wire into the lug.
- Spring loaded heat sink fuse clip providing maintenance free consistent contact pressure for optimum performance.
- One piece line and load base to assure consistent phase-to-phase alignment.
- Enclosure incorporates an upward flange to prevent water, ice, and snow access from the top of the enclosure. Reduction in seams and large overlaps improve sealing characteristics.
- Extra ground lug on neutral eliminates the need for installers to add addition lug when required for local codes.
- Tangential knock outs for consistent installation.



- Rugged metal handle with large red grip which provides highly visible
- Generous wire gutters that meet and/or exceed NEC wire bending space requirements.
- A unique enclosure design that adds rigidity and strength. It also offers a touch-safe edge for the installer's hand.

Heavy Duty

Type 1	Old Catalog Number	New Catalog Number
2 Pole, 400 A		
HF225N		HF225NA
HF225NH		
HHN325N		
HHN325NH		HFC225NA
HFC225N		
HFC225NH		
2 Pole, 600 A		
HF226N		HF226NA
HF226NH		
HHN326N		
HHN326NH		HFC226NA
HFC226N		
HFC226NH		
3 Pole, 400A		
HF325N		HF325NA
HF325NH		
HHN425N		
HHN425NH		HF365A
HF265		
HF365		
HF365H		HF365NA
HHN365		
HHN365H		
HFC265		HNF365A
HFC365		
HFC365H		
HF365N		HNF366A
HNF265		
HNF365		
HUN365		HNF366NA
HNFC265		
HNFC365		
ID365NF		HNF366A
HFC325N		
HFC325NH		
HFC365N		HFC326NA
ID365		
3 Pole, 600A		
HF326N		HF326NA
HF326NH		
HHN426N		
HHN426NH		HF366A
HF266		
HF366		
HF366H		HF366NA
HHN366		
HHN366H		
HFC266		HNF366A
HFC366		
HFC366H		
HF366N		HNF366NA
HNF266		
HNF366		
HUN366		HNF366A
HNFC266		
HNFC366		
ID366NF		HFC326NA
HFC326N		
HFC326NH		
HFC366N		HFC366NA
ID366		

Type 3R	Old Catalog Number	New Catalog Number
2 Pole, 400 A		
HF225NR		HF225NRA
HF225NRH		
HHN325NW		
HHN325NWH		HFC225NRA
HFC225NR		
HFC225NRH		
2 Pole, 600 A		
HF226NR		HF226NRA
HF226NRH		
HHN326NW		
HHN326NWH		HFC226NRA
HFC226NR		
HFC226NRH		
3 Pole, 400 A		
HF325NR		HF325NRA
HF325NRH		
HHN425NW		
HHN425NWH		HF365RA
HF265R		
HF365R		
HF365RH		HF365NRA
HHN365AW		
HHN365AWH		
HFC265R		HNF365RA
HFC365R		
HFC365RH		
HF365NR		HNF366RA
HNF265R		
HNF365R		
HUN365AW		HNF366NA
HNFC265R		
HNFC365R		
HFC325NR		HFC326NRA
HFC325NRH		
HFC365NR		
3 Pole, 600A		
HF326NR		HF326NRA
HF326NRH		
HHN426NW		
HHN426NWH		HF366RA
HF266R		
HF366R		
HF366RH		HF366NRA
HHN366AW		
HHN366AWH		
HFC266R		HNF366RA
HFC366R		
HFC366RH		
HF366NR		HNF366NA
HNF266R		
HNF366R		
HUN366AW		HNF366A
HNFC266R		
HNFC366R		
HFC326NR		HFC326NRA
HFC326NRH		
HFC366NR		

Type 4x	Old Catalog Number	New Catalog Number
3 Pole, 400 A		
HF325S		HF325SA
HFC325S		
HF265S		
HF365S		HF365SA
HFC265S		
HFC365S		
HNF265S		HNF365SA
HNF365S		
HNFC265S		
HNFC365S		HF365SWA
HF365SW		
HFC365SW		
HNF365SW		HNF365SWA
HNFC365SW		
HFC325NS		
HFC365NS		
HFC365NSW		
3 Pole, 600A		
HF326S		HF326SA
HFC326S		
HF266S		
HF366S		HF366SA
HFC266S		
HFC366S		
HNF266S		HNF366SA
HNF366S		
HNFC266S		
HNFC366S		HNF366NA
HF366SW		
HFC366SW		
HFC326NS		HFC326NSA
HFC366NS		

Type 12	Old Catalog Number	New Catalog Number
3 Pole, 400 A		
HF325J		HF325JA
HFC325J		
HF265J		
HF365J		HF365JA
HFC265J		
HFC365J		
HNF265J		HNF365JA
HNF365J		
HUN365AJ		
HNFC265J		HNF365JWA
HNFC365J		
HF365JW		
HFC365JW		HF365JWA
HNF365JW		
HNFC365JW		
HFC325NJ		HFC325NJA
HFC365NJ		
HFC365NSW		
HFC365NJW		HFC365NJWA
3 Pole, 600 A		
HF326J		HF326JA
HFC326J		
HF266J		
HF366J		HF366JA
HFC266J		
HFC366J		
HNF266J		HNF366JA
HNF366J		
HNFC266J		
HNFC366J		HNF366JWA
HF366JW		
HFC366JW		
HFC326NJ		HFC326NJA
HFC366NJ		
HFC366NJW		
		HFC366NJWA