



| REVISION | DATE | BY | DATE | BY |
|----------|------|---------|----------|----|
| | | DRAWN | 16/03/24 | PP |
| | | CHEK'D | | |
| | | VERIF'D | | |


Confidential - Property of
Siemens Industry, Inc.

| | |
|-----------|--------------------------|
| CUSTOMER | |
| ORDER NO. | DWG. NO. |
| | 3F3Y225FCD16CC SH 1 OF 2 |

SIEMENS


| | | |
|---|---|---|
| CATALOG NO. 3F3Y225FCD16CC SERIAL NO. SERIES H 225 kVA 60 Hz 3 PHASE 2.9 % IMP AT 135 °C | |  |
| 115 °C RISE 30 °C AVG. AMBIENT 220 °C TEMP CLASS 40 °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V 10 kV BIL SECONDARY(X0 X1 X2 X3) 208Y/120V V 10 kV BIL | VOLTS CONNECT 504 1 492 2 480 3 468 4 456 5 444 6 432 7 | TYPE J  LR 3902 SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY IBC 2012/ASCE 7-10 SDS<=2.0g Z/h=1 Ip=1.5 dsu0088e |
| WINDING MATERIAL CU ENCLOSURE TYPE - WEIGHT 1700 LBS ENERGY EFFICIENCY EXCEEDS CSA DOE 10 CFR PART 431:2016 C802.2-2012 | SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class AN Dry Type Transformer | |






All Dimensions in inches

H.V.1. TERMINAL DETAIL



L.V.1. TERMINAL DETAIL



CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT
- DIMENSIONS ARE APPROXIMATE

Confidential – Property of
Siemens Industry, Inc.

| REVISION | DATE | BY | DATE | BY |
|----------|------|---------|----------|----|
| | | DRAWN | 16/03/24 | PP |
| | | CHEK'D | | |
| | | VERIF'D | | |

| | |
|-----------|----------------------------|
| CUSTOMER | |
| ORDER NO. | DWG. NO. 3F3Y225FCD16CC |
| SH 2 OF 2 | |