



REVISION	DATE	BY	DATE	BY
		DRAWN	16/03/24	PP
		CHEK'D		
		VERIF'D		


Confidential - Property of
Siemens Industry, Inc.

CUSTOMER	
ORDER NO.	DWG. NO.
	3F3Y225FCD16CC SH 1 OF 2

SIEMENS


CATALOG NO. 3F3Y225FCD16CC SERIAL NO. SERIES H 225 kVA 60 Hz 3 PHASE 2.9 % IMP AT 135 °C		
115 °C RISE 30 °C AVG. AMBIENT 220 °C TEMP CLASS 40 °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V 10 kV BIL SECONDARY(X0 X1 X2 X3) 208Y/120V V 10 kV BIL	VOLTS CONNECT 504 1 492 2 480 3 468 4 456 5 444 6 432 7	TYPE J  LR 3902 SEISMIC QUALIFICATIONS, FLOOR MOUNT ONLY IBC 2012/ASCE 7-10 SDS<=2.0g Z/h=1 Ip=1.5 dsu0088e
WINDING MATERIAL CU ENCLOSURE TYPE - WEIGHT 1700 LBS ENERGY EFFICIENCY EXCEEDS CSA DOE 10 CFR PART 431:2016 C802.2-2012	SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class AN Dry Type Transformer	






All Dimensions in inches

H.V.1. TERMINAL DETAIL



L.V.1. TERMINAL DETAIL



CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT
- DIMENSIONS ARE APPROXIMATE

Confidential – Property of
Siemens Industry, Inc.

REVISION	DATE	BY	DATE	BY
		DRAWN	16/03/24	PP
		CHEK'D		
		VERIF'D		

CUSTOMER	
ORDER NO.	DWG. NO. 3F3Y225FCD16CC
SH 2 OF 2	