





REVISION	DATE	BY	DATE	BY
		DRAWN	03/09/09	VG
		CHEK'D		
		VERIF'D		

Confidential - Property of
Siemens Industry, Inc.
 Building Technologies Division



CUSTOMER	
ORDER NO.	DWG. NO.
	3F3Y112FTP1
SH 1 OF 2	

SIEMENS

CATALOG NO. 3F3Y112FTP1 SERIAL NO. SERIES H 112.5 kVA 60 Hz 3 PHASE 5.5 % IMP AT 135 °C		 <p>VOLTS 504 492 480 468 456 444 432</p> <p>CONNECT 1 2 3 4 5 6 7</p>
115 °C RISE °C AVG. AMBIENT 220 °C TEMP CLASS °C MAX. AMBIENT PRIMARY (H1 H2 H3) 480V V SECONDARY(X0 X1 X2 X3) 208Y/120V V WINDING MATERIAL AL ENCLOSURE TYPE NEMA-3R WEIGHT 800 LBS ENERGY EFFICIENCY NEMA TP 1-2002		
SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES 		TYPE K  
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA		dsu0082e



3F3Y112FTP1




All Dimensions in inches

ENCLOSURE COLOR :ANSI 61 GREY – OUTDOOR

H.V.1. TERMINAL DETAIL

L.V.1. TERMINAL DETAIL

MECHANICAL TYPE LUGS INCLUDED
SUITABLE FOR 250MCM-6 CU/AL
CONDUCTORS
1 CONDUCTOR PER PHASE



CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT COIL FACE

Confidential – Property of
Siemens Industry, Inc.
Building Technologies Division

REVISION	DATE	BY	DATE	BY
			03/09/09	VG
			CHEK'D	
			VERIF'D	

CUSTOMER	
ORDER NO.	DWG. NO. 3F3Y112FTP1
SH 2 OF 2	

0.3 rbhatia 2011/05/27 10:27