

To: SIEMENS  
Attn:  
Fax:

NOTES:

1. SIZE: 6.25" X 8.75" .125 rcr
2. MATERIAL: Semi-Gloss Paper  
Permanent Adhesive
3. INK COLOR: Black, Red PMS 185

SIEMENS

Cat. No. DTGNF323NR
Non-Fusible General Duty Double Throw Safety Switch
Type VB II

100 Amps Maximum
240 Volts AC (V~) Maximum
250 Volts DC (V-) Maximum

NEMA Type 3R
Rainproof
Suitable for use as Service Equipment

Horsepower Ratings

	240 VAC <sup>1</sup> 1Ø	240 VAC 3Ø	250 VDC <sup>1</sup>
<b>Max. HP</b>	15	40	20

Manually-operated switch suitable for use in accordance with Article 702 of the National Electrical Code, ANSI/NFPA 70.

**Fuse and Short Circuit Information**

This switch is suitable for use on a circuit capable of delivering not more than 100,000 amperes, RMS symmetrical, 240 volts maximum when protected by class J, R or T fuses rated 100 amperes maximum.

**Danger** – Unless Class J, R or T fuses are used to protect this switch, it may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 240 volts maximum, when protected by Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 240 volts maximum.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, 250 volts DC maximum, when protected by fuses marked with an interrupting rating of 10,000 amperes, 250 volts DC.

**Danger** – Unless fuses marked for an interrupting rating of 10,000 amperes at 250 volts DC are used to protect this switch, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

⚠ DANGER

Hazardous voltage.  
Will cause death or serious injury.

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

**Terminal & Wire Information** USE 75°C COPPER OR ALUMINUM WIRE

Terminal & Wire Information			
Description	Wire Range	Wire Tightening Torque <sup>5</sup>	Lug Mounting Torque <sup>5</sup>
Line, Load & Main Neutral	14-1/0 AWG	35 lb-ins, 14-10 AWG / 40 lb-ins, 8 AWG 45 lb-ins, 6-4 AWG / 50 lb-ins, 3-1/0 AWG	80 lb-ins.
Service Ground	14-4 AWG	35 lb-ins, 14-10 AWG / 40 lb-ins, 8 AWG 45 lb-ins, 6-4 AWG	24 lb-ins.

Inspection record number:

**Accessories**

Aux. Switch (1NO - 1NC)	HA161234	Neutral	HN263	Class T Fuse Kit
Aux. Switch (2NO - 2NC)	HA261234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234	Hub Kits ECHS125/HS125 (1 1/4") ECHS150/HS150 (1 1/2") ECHS200/HS200 (2")

**Replacement Parts**

Line Base	HNB623	Wire Grip Kit (Al)	HL63	Handle / Handle Guard	HHD61234
		Mechanism		Door	

Protected by one or more of the following US Patents: 6,134,979, 6,356,460, 5,945,650, 5,990,439.

<sup>1</sup>Use outer two poles.

<sup>5</sup>When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

LISTED

ENCLOSED SWITCH  
Issue No. AL-265  
File No. E4776

Siemens Energy & Automation, Inc.

Bellefontaine, Ohio 43311 U.S.A.

<http://www.sea.siemens.com/power>

Assembled in Mexico

Pc. No. 504117R01  
0104

6.25"

8.75"

R .125"  
X4

- OK to print
- OK to Print with corrections as marked
- Make corrections, resubmit corrected proof
- Job will not be printed unless approved by customer.

<small>Artwork By:</small>	<small>Date:</small>	AUTHORIZED BY	DATE	PART NUMBER	REV
<small>Proofer:</small>	<small>Date:</small>		06/21/06	504117R01	16P