



TEL (915) 590-8500
FAX (915) 590-8510

4.63"

Cat. No. GHN422NW **Fusible General Duty Safety Switch** **Type VB II**
60 Amps Maximum **240 Volts AC (V~) Maximum** **250 Volts DC (V-) Maximum**
Type 3R **Rainproof** **Suitable for use as Service Equipment**

.75"

Horsepower Ratings	240 VAC ¹ 1Ø	240 VAC 3Ø	250 VDC ¹
Std. HP (Std. Fuse) ⁴	3	7½	10
Max. HP (Time Delay)	10	15	—

Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

Fuse and Short Circuit Information

When used with Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 240 volts maximum, this switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 240 volts, maximum.

When used with Class R fuses and Class R fuse clip kit **HR612M** properly installed, this switch is suitable for use on a circuit capable of delivering not more than 100,000 amperes, RMS symmetrical, 240 volts maximum.

Danger – Unless Class R fuses are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

When used with fuses marked with DC ratings, this switch is suitable for use on a circuit capable of delivering not more than the DC interrupting rating marked on the fuse, at the DC voltage rating marked on the fuse, up to a maximum of 10,000 amperes, 250 volts DC.

Danger – Unless fuses marked for an interrupting rating of 10,000 amperes at 250 volts DC are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

Renewable link fuses are not recommended

⚠ DANGER

Hazardous voltage. Will cause death or serious injury.

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

3.70"

Terminal & Wire Information USE 60°C / 75°C COPPER OR ALUMINUM WIRE

Terminal & Wire Information			
Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	14-3 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG / 50 lb-ins. 3 AWG	24 lb-ins.
Service Ground	14-4 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	

Inspection record number:

Accessories

Aux. Switch (1NO - 1NC)	HA161234M	Neutral	HN612	Class R Fuse Kit (Rejects Class H & K Fuses)	HR612M
Aux. Switch (2NO - 2NC)	HA261234M	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234M	Hub Kits	ECHS075/HS075M (3/4") ECHS100/HS100M (1") ECHS125/HS125M (1 1/4")

Replacement Parts

Line Base	HFB612	Wire Grip Kit (AL)	HL612	Handle / Handle Guard	GH223
Load Base	HBB612	Mechanism	HM6123		

Protected by one or more of the following US Patents: 6,134,979, 6,356,460, 5,945,650, 5,990,439.

¹ Use outer two poles.

⁴ The starting current of motors more than the standard horsepower or kilowatt ratings may require the use of fuses with appropriate time delay characteristics.

⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

For questions on this device please call 1-800-964-4114



Murray Electrical Products
 Siemens Industry, Inc.
 Norcross, GA 30092 USA
<http://www.murrayelectrical.com>
 Assembled in Mexico

Pc. No. 502126D06
0202



R .125"
X4

7.44"

COMPANY NAME	MATERIAL	SIZE	JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.		PART NO.
SIEMENS INDUSTRY, INC.	Synthetic Paper	WIDTH 4.63"	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	502126D06
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	INK COLORS	LENGTH 7.44"	<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: Label
	BLACK 185 RED	CORNER RADIUS 1.25"	AUTHORIZED BY	DATE	REVISION LEVEL 37P
					DESIGNER Joel Ortega
					CHECKED BY DATE 04/18/11