



TEL (915) 590-8500  
FAX (915) 590-8510

4.00"

# SIEMENS

**Cat. No. HF321NX** Fusible Heavy Duty Safety Switch **Type VB II**  
**30 Amps Maximum** **240 Volts AC (V~) Maximum** **250 Volts DC (V---) Maximum**  
**Type 4 / 4X** **Watertight**

Suitable for use as Service Equipment.

Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

Horsepower Ratings	240 VAC	240 VAC <sup>2</sup>	250 VDC
	1Ø	3Ø	
Std. HP (Std. Fuse)*	1½	3	5
Max. HP (Time Delay)	3	7½	—

**Fuse and Short Circuit Information**

When used with Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 240 volts maximum, this switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 240 volts, maximum.

When used with Class R fuses and Class R fuse clip kit **HR21** properly installed, this switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, 240 volts maximum.

**Danger** - Unless Class R fuses are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

When used with fuses marked with DC ratings, this switch is suitable for use on a circuit capable of delivering not more than the DC interrupting rating marked on the fuse, at the DC voltage rating marked on the fuse, up to a maximum of 10,000 amperes, 250 volts DC.

**Danger** - Unless fuses marked for an interrupting rating of 10,000 amperes at 250 volts DC are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

**Renewable link fuses are not recommended**

**⚠ DANGER**

**Hazardous voltage. Will cause death or serious injury.**

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

6.00"

**Terminal & Wire Information** **USE 60°C / 75°C COPPER OR ALUMINUM WIRE**

Description	Wire Range	Wire Tightening Torque <sup>5</sup>	Lug Mounting Torque <sup>5</sup>
Line, Load & Main Neutral	(1) 14-6 AWG (2) 14-10 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	24 lb-ins.
Service Ground	14-4 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	24 lb-ins.

Inspection record number:

**Accessories**

Aux. Switch (1NO - 1NC)	HA161234	Neutral	HN612	Wire Grip Kit (CU)	HLC612
Aux. Switch (2NO - 2NC)	HA261234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234	Hub Kits	SSH075 (3/4") SSH100 (1")
Low Voltage Aux. Sw. (1NO - 1NC)	HA361234	Isolated Ground Lug Kit	HG261234	Fuse Puller Kit (3 Per Kit)	HP61
Compression Lug Neutral Barrier Kit	HCL612	Class R Fuse Kit (Rejects Class H & K Fuses)	HR21		

Protected by one or more of the following US Patents: 6,134,979, 6,356,460, 5,945,650, 5,990,439.

<sup>1</sup> Use outer two poles.

<sup>4</sup> The starting current of motors more than the standard horsepower or kilowatt ratings may require the use of fuses with appropriate time delay characteristics.

<sup>5</sup> When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

<sup>6</sup> If compression lugs are used for the neutral, order compression lug neutral barrier kit HCL612.

**For questions on this device please call 1-800-241-4453**

Siemens Industry, Inc.  
Norcross, GA 30092 USA  
<http://www.usa.siemens.com/powerdistribution> Pc. No. 500172AU04  
Assembled in Mexico 1103

8.00"

**UL Listed Compression Lugs (Refer to manufacturers instructions for proper installation)<sup>6</sup>**

Wire Size (AWG OR kcmil)	Burndy		Thomas & Betts		IlSCO	
	Cu Only	Cu / Al	Cu Only	Cu / Al	Cu Only	Cu / Al
14 - 10				60096 60097		
8	YA8C-L Box YA8C-L1 Box		54104 54130	60101 60102 61102	CRA-8	ACL - 8 ACN - 8
6				61107		

**Replacement Parts**

Line Base	HFB21	Wire Grip Kit (AL)	HL612	Mechanism	HM6123S
Load Base	HBB21				

R .125"  
X4

<b>COMPANY NAME</b>	<b>MATERIAL</b>	<b>SIZE</b>	<b>JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.</b>		PART NO.	
SIEMENS E&A	Semi-Gloss Paper	WIDTH	<input type="checkbox"/> OK TO PRINT AS IS	<input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF	<b>500172AU04</b>	
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	<b>INK COLORS</b>	4.00"			<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED	
	BLACK 185 RED	LENGTH	8.00"			<b>Label</b>
		CORNER RADIUS	.125"			<b>REVISION LEVEL 42P</b>
				<b>AUTHORIZED BY</b>	<b>DATE</b>	DESIGNER <b>Joel Ortega</b>
					CHECKED BY	
					DATE <b>01/31/13</b>	