

SIEMENS

Cat. No. HNF361SW **Non-Fusible Heavy Duty Safety Switch** **Type VB II**
30 Amps Maximum **600 Volts AC(V~) Maximum** **250 Volts DC(V=) Maximum**
NEMA Type 4 / 4X **Watertight Stainless Steel**

Horsepower Ratings	240 VAC ¹ 1Ø	240 VAC 3Ø	480 VAC ¹ 1Ø	480 VAC 3Ø	600 VAC ¹ 1Ø	600 VAC 3Ø	250 VDC ¹
Max. HP	5	10	7½	20	10	30	5

Horsepower ratings listed above are suitable for use with High Efficiency motors through 15 HP @ 480 V, 3Ø AC and 20 HP @ 600 V, 3Ø AC. Suitable for use as Service Equipment when used with factory installed ground bar on 3 phase, 3 wire systems or when used with HN612 neutral kit on 1 phase, 3 wire or 3 phase, 4 wire systems.

Fuse and Short Circuit Information

This switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, 600 volts maximum when protected by class J, R or T fuses rated 30 amperes maximum.

Danger – Unless Type NEB or NGB circuit breakers or Class J, R or T fuses are used to protect this switch, it may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 600 volts maximum, when protected by Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 600 volts maximum.

This switch is suitable for use on a circuit capable of delivering not more than 18,000 amperes, rms symmetrical up to 480 VAC, when protected by Type NEB or NGB circuit breakers rated 30 amperes maximum.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, 250 volts DC maximum, when protected by fuses marked with an interrupting rating of 10,000 amperes, 250 volts DC.

Danger – Unless fuses marked for an interrupting rating of 10,000 amperes at 250 volts DC are used to protect this switch, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

⚠ DANGER

Hazardous voltage. Will cause death or serious injury.

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

Terminal & Wire Information USE 60°C / 75°C COPPER OR ALUMINUM WIRE

Terminal & Wire Information			
Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	14-6 AWG	35 lb-ins, 14-10 AWG / 40lb-ins, 8 AWG 45 lb-ins, 6-4 AWG	24 lb-ins.
Service Ground	14-4 AWG	35 lb-ins, 14-10 AWG / 40lb-ins, 8 AWG 45 lb-ins, 6-4 AWG	24 lb-ins.

UL Listed Compression Lugs (Refer to manufacturers instructions for proper installation)⁶

Wire Size (AWG OR kcmil)	Burdny		Thomas & Betts		IIsco	
	Cu Only	Cu / Al	Cu Only	Cu / Al	Cu Only	Cu / Al
14 - 10					60096 / 60097	
8	YA8C-L Box YA8C-L1 Box		54104 54130	60101 / 60102 61102	CRA-8	ACL - 8 ACN - 8
6				61107		

Inspection record number:

Accessories

Aux. Switch (1NO - 1NC)	HA161234	Compression Lug Neutral Barrier Kit	HCL612	Isolated Ground Lug Kit	HG261234	Wire Grip Kit (CU)	HLC612
Aux. Switch (2NO - 2NC)	HA261234	Neutral	HN612	Fuse Puller Kit (3 per kit)		Hub Kits	SSH075 (3/4") SSH100 (1")
Low Voltage Aux. Sw. (1NO - 1NC)	HA361234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234	Class R Fuse Kit (Rejects Class H & K Fuses)			

Replacement Parts

Line Base	HNB612	Wire Grip Kit (AL)	HL612	Handle / Handle Guard	HH6123S
Load Base		Mechanism	HM6123S	Door	HNF361SWD00R

Protected by one or more of the following US Patents: 5,914,460, 6,134,979, 6,356,460, 5,945,650, 5,990,439.

¹ Use outer two poles.

⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

⁶ If compression lugs are used for the neutral, order compression lug neutral barrier kit HCL612.

For questions on this device
please call 1-800-241-3138

Siemens Industry, Inc.
Norcross, GA 30092
<http://www.usa.siemens.com/powerdistribution>
Assembled in Mexico

Pc. No. 500335A05
0102