

SIEMENS

Cat. No. DTNF362S Non-Fusible Heavy Duty Double Throw Safety Switch Type VB II
60 Amps Maximum 600 Volts AC (V~) Maximum 250 Volts DC (V=) Maximum
Type 4 / 4X Watertight Stainless Steel

Horsepower Ratings	240 VAC ¹ 1Ø	240 VAC 3Ø	480 VAC ¹ 1Ø	480 VAC 3Ø	600 VAC ¹ 1Ø	600 VAC 3Ø	250 VDC ¹
Max. HP	10	20	20	50	25	60	10

Suitable for use as Service Equipment when used with factory installed ground bar on 3 phase, 3 wire systems or when used with **HN263** neutral kit on 1 phase, 3 wire or 3 phase, 4 wire systems.

Manually-operated switch suitable for use in accordance with Article 702 of the National Electrical Code, ANSI/NFPA 70.

Fuse and Short Circuit Information

This switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, **600** volts maximum when protected by class J, R or T fuses rated 60 amperes maximum.

Danger – Unless Type NEB, NGB, NEG, NGG, ED4 or ED6 circuit breakers or Class J, R or T fuses are used to protect this switch, it may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.


This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, **600** volts maximum, when protected by Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, **600** volts maximum.

This switch is suitable for use on a circuit capable of delivering not more than 18,000 amperes, rms symmetrical up to 480 VAC, when protected by Type NEB, NGB, NEG, NGG, or ED4 circuit breakers rated **60** amperes maximum.

This switch is suitable for use on a circuit capable of delivering not more than 18,000 amperes, rms symmetrical, when protected by Type ED6 circuit breakers rated **60** amperes maximum.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, **250** Volts DC, maximum, when protected by fuses marked with an interrupting rating of 10,000 amperes, **250** Volts DC.

Danger – Unless fuses marked for an interrupting rating of 10,000 amperes at **250** Volts DC are used to protect this switch, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

⚠ DANGER	
	<p>Hazardous voltage. Will cause death or serious injury.</p> <ul style="list-style-type: none"> • Disconnect and lock out power supplying this switch before working on this switch. • Turn off switch before removing or installing fuses if so equipped. • Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off. • Close or replace cover before turning power on.

Terminal & Wire Information **USE 60°C / 75°C COPPER OR ALUMINUM WIRE**

Terminal & Wire Information			
Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	14-2 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG / 50 lb-ins. 3-2 AWG	80 lb-ins.
Service Ground	14-4 AWG	35 lb-ins. 14-10 AWG / 40 lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	24 lb-ins.

UL Listed Compression Lugs (Refer to manufacturers instruction for proper installation)⁶

Wire Size (AWG OR kcmil)	Burndy		Thomas & Betts		Ilco	
	Cu Only	Cu / Al	Cu Only	Cu / Al	Cu Only	Cu / Al
14-10			256-30695-1352	60097		
8	YA8C-L1 Box YA8C-TC14	YA8CA3	54130 54930BE	60102 61102		ACL-8
6	YA6C-L Box YA6C	YA6CA1	54105 54905BE	60107 61107	CRB-6 CRB-6L	ACL-6
4			54106	61112	CRB-4	

Inspection record number:

Accessories

Aux. Switch (1NO - 1NC)	HA161234	Neutral	HN263	Hub Kits	SSH075 (3/4") SSH100 (1") SSH125 (1 1/4")
Aux. Switch (2NO - 2NC)	HA261234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234		
Low Voltage Aux. Sw. (1NO - 1NC)	HA361234	Isolated Ground Lug Kit	HG261234		
Compression Lug Neutral Barrier Kit	HCL623	Wire Grip Kit (CU)	HLC612		

Replacement Parts

Line Base	HNB623	Wire Grip Kit (AL)	HL612	Handle / Handle Guard	HHD61234S
		Mechanism		Door	DTNF362SDOOR

Protected by one or more of the following US Patents: 6,134,979, 6,356,460, 5,945,650, 5,990,439.

¹ Use outer two poles.

⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire information Table.

⁶ If compression lugs are used for the neutral, order compression lug neutral barrier kit **HCL623**.

For questions on this device please call 1-800-241-4453

Siemens Industry, Inc.
 Norcross, GA 30092 USA
<http://www.usa.siemens.com/powerdistribution>
 Assembled in Mexico

Pc. No. 502168J04
1203