

SIEMENS

Ingenuity for life

TPS3 09

Type 1 Surge Protective Device (SPD) Mounts External to Electrical Distribution Equipment or Internal to P1, P2 Lighting Panelboards, P3 Power Panelboards and Busway Systems

Features:

- UL 1449 4th Edition Listed Type 1, CSA 22.2 No. 269.1
- Optional UL 1449-4 Type 2 SPD, CSA 22.2 No. 269.2
- Type 1 SPD
- Mounts external to electrical distribution equipment
 - Weatherproof hub included
- Mounts internal to P1 panelboards & busway
 - P1 - Field retrofit or factory install
 - P2 and P3 - Factory install only**Consult factory for field retrofit**
- Large block, individually fused, thermally protected, 50 kA MOVs
- 20 kA I_n (most models)
- 200 kA SCCR (most models)
- All UL required OCP & safety coordination included
 - Type 1 SPDs intended for Line or Load side of Main Disconnect
- UL96A Lightning Protection Master Label compliant (@20kA I_n)

- Designed, manufactured and tested consistent with:
 - ANSI/IEEE C62.41.1-2002, C62.41.2-2002, C62.45-2002, C62.62-2010, C62.72-2007 & CSA C22.2 No. 269.1
 - 1992/2000 NEMA LS-1
 - NEC Article 285
 - IEC 61643, CE
- 10 year warranty


SPD Specifications

Per Phase	L-N	L-G	N-G
100 kA	50 kA	50 kA	50 kA

- 100% monitoring (Every MOV is monitored, incl. N-G)
- Individually fused and thermally protected MOVs
- Solid state bi-directional operation
- Repetitive impulse: 5,000 hits
- Less than 1 nanosecond response time
- Relative humidity range: 0-95% non-condensing
- Operating frequency: 47-63 Hz
- Operating temperature: -40°C (-40°F) to +85°C (185°F)
- Standard Configuration
 - Standard NEMA 4X polycarbonate enclosure (UL 746C (f1), UL 94-5VA)
 - Wire size: Prewired with 3' (91.4 cm) of #10 AWG
 - Standard size: 8.3" x 3.6" x 3.0" (211 mm x 91 mm x 77 mm)
 - Standard weight: 3 lb. (1.4 kg)
- SPD Monitoring
 - LED indicators



Ordering Information



Example: TPS3C0910D0002 = Type 2 SPD for a 208/120V panelboard with a surge current capacity of 100 kA per phase with standard NEMA 4X enclosure, dry contacts and audible alarm option.

Available for field retrofit in P1 panels

When an option is not selected, include a zero (0) in the field

Available Accessories:

Ordered Separately

- RMSIE = Remote monitor
- XMFMKIT = Flush mount plate
- TPS9IKITP1 = Mounting bracket for installation in P1 panels
- TPS9IKITP2 = Mounting bracket for installation in P2 panels (factory install only)

UL 1449 Fourth Edition - Test Data Voltage Protection Rating (VPR - 6 kV, 3 kA)								
Voltage Code	Service Voltage	L-N	L-G	N-G	L-L	I _n	SCCR	MCOV
A	120/240V, 1Ø, 3W (Fig 1)	600	700	500	1000	20 kA	100 kA	150
B	120/240V, 3Ø, 4W (Fig 3)	600/1200	700 /1200	500	1000/1000	20 kA	200 kA	150/320
C	120/208V, 3Ø, 4W (Fig 2)	600	700	500	1000	20 kA	200 kA	150
D	240V, 3Ø, 3W (Fig 4)	—	1200	—	1200	20 kA	200 kA	320
E	277/480V, 3Ø, 4W (Fig 2)	1200	1200	1000	1800	20 kA	200 kA	320
F	480V, 3Ø, 3W (Fig 4)	—	1800	—	1800	10 kA	200 kA	552
G	600V, 3Ø, 3W (Fig 4)	—	2500	—	2500	10 kA	200 kA	690
K	380/220V, 3Ø, 4W (Fig 2)	1200	1200	1000	1800	20 kA	200 kA	320
L	600/347V, 3Ø, 4W (Fig 2)	1500	1500	1500	2500	10 kA	200 kA	420
S	400/230V, 3Ø, 4W (Fig 2)	1200	1200	1000	1800	20 kA	200 kA	320




Figure 1
Split
2 Hots, 1 Neu, 1 Grnd




Figure 2
Wye
3 Hots, 1 Neu, 1 Grnd




Figure 3
Hi-Leg Delta (B High)
3 Hots, (B High),
1 Neu, 1 Grnd




Figure 4
Delta & HRG Wye
3 Hots, 1 Grnd

Notes:

- ❶ Requires TPS9IKITP1 or TPS9IKITP2 mounting bracket accessory, see available Accessories. Prewired cables are extended from 3 feet to 6 feet.

Siemens Industry, Inc.

5400 Triangle Parkway
 Norcross, GA 30092

888-333-3545
 info.us@siemens.com

Order No. RPFL-S309C-0716
 Printed in USA

All Rights Reserved.
 ©2016 Siemens Industry, Inc.