

SIEMENS

Ingenuity for life

Save electrical room space

Siemens Skinny WL Sections

Introducing narrowest single main in industry at 25" wide

- UL listed up to 2500A
- Indoor: NEMA 1
- Outdoor: NEMA 3R with side/rear access
- Seismic rated
- Available as main or branch sections
- New hinged auxiliary compartment for ease of lug and bus splice access
- Includes same great features as 38" wide: PAC meter, SPDs, DAS (maintenance mode)

Standard Width



38 inches wide

Skinny Width



25 inches wide

usa.siemens.com/switchboards



Benefits

- * 13" narrower than current design
- Revolutionary hinged auxiliary compartment for access to lugs and disconnect
- Can be added to existing lineups
- Dual auxiliary compartments for more space than standard 38" wide auxiliary compartments
- Available as main or branch

Dimensions

Amperes	Height (in)	Width (in)	Depth (in)
2000A and less	90"	25"	28" or 38"
2500A	90"	25"	38" or 48"

Incoming / Outgoing Options

- Cable
- Busway (Temp + ASI rated)
- Thru-bus
- Transformer (pull section required)



Published by
Siemens Industry, Inc. 2016.

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

For more information, please contact
our Customer Support Center.
Phone: 1-800-241-4453
E-mail: info.us@siemens.com

usa.siemens.com/switchboards

Order No.: SMFL-SMWS-0916
Printed in U.S.A.
© 2016 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.