

The Siemens logo is displayed in a teal, sans-serif font.

*Ingenuity for life*

# SIEBREAK™ metal-enclosed switchgear

## Express ship program

### Footnotes:

<sup>1</sup>: Fused is 50 kA (80 kA momentary).

<sup>2</sup>: Units are supplied with provisions for mounting customer-furnished type CL-14 current-limiting fuses.

### Description

Siemens type SIEBREAK™ load-interrupter switchgear is a modular assembly of switches, fuses, and bus assemblies that are fully integrated both mechanically and electrically to provide the highest level of medium-voltage circuit protection. Under the SIEBREAK express ship program, shipment is offered within four weeks after purchase order receipt. An order can be placed for 5 kV or 15 kV rated switch with continuous current rating of 600 A or 1,200 A, 25 kA short time, and 40 kA momentary with cable terminations for top or bottom entry for express shipping. All of the catalog numbers described in the following table are available for express shipment. Contact your local Siemens sales representative for more details or order via Siemens Industry Mall.

Catalog number	Item description	Long description	Weight lbs (kg)	Inches (mm)			List price
				Length	Width	Height	
US2:S05064S1ASPWNX	5 kV, 600 A, load-interrupter switch, single, cable top entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 5 kV, 600 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, top incoming-line cables and top exit-load cables (lugs not included)	1,000 (455)	62 (1,575)	36 (914)	92 (2,337)	\$22,120
US2:S05124S1ASPXNX	5 kV, 1,200 A, load-interrupter switch, single, cable top entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 5 kV, 1,200 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, top incoming-line cables and top exit-load cables (lugs not included)	1,100 (499)	62 (1,575)	36 (914)	92 (2,337)	\$29,610

Catalog number	Item description	Long description	Weight lbs (kg)	Inches (mm)			List price
				Length	Width	Height	
US2:S15064S1ASPYNX	15 kV, 600 A, load-interrupter switch, single, cable top entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 15 kV, 600 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, top incoming-line cables and top exit-load cables (lugs not included)	1,000 (455)	62 (1,575)	36 (914)	92 (2,337)	\$22,750
US2:S15124S1ASPZNX	15 kV, 1,200 A, load-interrupter switch, single, cable top entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 15 kV, 1,200 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, top incoming-line cables and top exit-load cables (lugs not included)	1,100 (499)	62 (1,575)	36 (914)	92 (2,337)	\$30,730
US2:S05064S1BSPWNX	5 kV, 600 A, load-interrupter switch, single, cable bottom entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 5 kV, 600 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, bottom incoming-line cables and bottom exit-load cables (lugs not included)	1,000 (455)	62 (1,575)	36 (914)	92 (2,337)	\$22,120
US2:S05124S1BSPXNX	5 kV, 1,200 A, load-interrupter switch, single, cable bottom entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 5 kV, 1,200 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, bottom incoming-line cables and bottom exit-load cables (lugs not included)	1,100 (499)	62 (1,575)	36 (914)	92 (2,337)	\$29,610
US2:S15064S1BSPYNX	15 kV, 600 A, load-interrupter switch, single, cable bottom entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 15 kV, 600 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, bottom incoming-line cables and bottom exit-load cables (lugs not included)	1,000 (455)	62 (1,575)	36 (914)	92 (2,337)	\$22,750
US2:S15124S1BSPZNX	15 kV, 1,200 A, load-interrupter switch, single, cable bottom entry - express ship	Express ship, SIEBREAK metal-enclosed, load-interrupter switch, standalone bay unit, type 1 indoor enclosure, rated 15 kV, 1,200 A, 25 kA (40 kA momentary) <sup>1</sup> , three wire, 60 Hz, manually operated, equipped with provisions for CL-14, polyester supports, top incoming-line cables and top exit-load cables (lugs not included)	1,100 (499)	62 (1,575)	36 (914)	92 (2,337)	\$30,730

Published by Siemens Industry, Inc. 2016.

Siemens Industry  
7000 Siemens Road  
Wendell, North Carolina 27591

For more information, please contact our Customer Support Center.  
Phone: +1 (800) 347-6659

[www.usa.siemens.com/siebreak](http://www.usa.siemens.com/siebreak)

Article No. EMMS-C40052-00-4AUS

Printed in U.S.A.

© 2016 Siemens Industry, Inc.

Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.