


REVISION	DATE	BY	DATE	BY
			16/11/10	RB

Confidential - Property of
Siemens Industry, Inc.


CUSTOMER	
ORDER NO.	DWG. NO.
	3F3T000CD16
	SH 1 OF 2

SIEMENS

CATALOG NO. 3F3T0000CD16 SERIAL NO. SERIES H 1000 kVA 60 Hz 3 PHASE 5.4 % IMP AT 170 °C		 <p>VOLTS 504 492 480 468 456</p> <p>CONNECT 1-2 2-3 3-4 4-5 5-6</p>
150 °C RISE 220 °C TEMP CLASS PRIMARY (H1 H2 H3) 480V V 10 kV BIL SECONDARY(X0 X1 X2 X3) 208Y/120V V 10 kV BIL	°C AVG. AMBIENT °C MAX. AMBIENT 480V V 10 kV BIL 208Y/120V V 10 kV BIL	
WINDING MATERIAL CU ENCLOSURE TYPE 3R WEIGHT 5700LBS ENERGY EFFICIENCY CEE ACT DOE 10 CFR PART 431:2016 SOR/2011-182		
SPACINGS BETWEEN ANY VENTILATED ENCLOSURE PANEL AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 12 INCHES ALSO VERIFIED IN ACCORDANCE TO ENERGY STANDARD C802.2-12 BY UNDERWRITERS LABORATORIES INC. 3VJ6		
SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS BEFORE HANDLING, INSTALLING AND OPERATING; SEE INSTRUCTION MANUAL NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA <small>csu0086e</small>		




FRONT VIEW



** - Recommended cable entry locations only
cutouts & gland plates not provided.


SIDE VIEW




All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY - OUTDOOR

HV TERMINAL DETAIL



LV TERMINAL DETAIL



CUSTOMER NOTES:

- HV TERMINATED AT TOP FRONT
- LV TERMINATED AT BOTTOM FRONT

Confidential - Property of
Siemens Industry, Inc.

REVISION	DATE	BY	DATE	BY
		DRAWN	16/11/10	RB
		CHEK'D		
		VERIF'D		

CUSTOMER	
ORDER NO.	DWG. NO.
	3F3T000CD16
	SH 2 OF 2