



3B5Y112CD16 - Three-Phase Ventilated-USA-DOE

| PRODUCT DETAILS | | | |
|---|------------------------------|-------------------------|--------------------|
| KVA: | 112.50 | Enclosure: | NEMA 3R Ventilated |
| UPC#: | | Phase: | Three-Phase |
| Line Voltage | 208V-Delta | Load Voltage | 480Y/277V |
| E/S Shielded: | No | Windings: | Copper |
| Temp. rise: | 150° | Hertz: | 60 Hz |
| Taps: | 2 - 2.5% FCAN; 4 - 2.5% FCBN | Approvals: | UL, cUL, DOE |
| | | Wall Bracket: | n/a |
| WEIGHT AND DIMENSIONS | | | |
| Height(A): | 38.00" | Width(B): | 29.00" |
| Depth(C): | 29.00" | Shipping Weight: | 885 lbs |
| ADDITIONAL INFORMATION | | | |
| How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool | | | |


Wiring Diagram

Dimensional Drawing

T208D Wiring Diagram & Connections*

Wiring Diagram

Primary: 208 Volts Delta
Secondary: 480Y/277 Volts



Connections

| Primary Volts | On Each Coil Jumper Taps To | Primary Lines Connect To |
|---------------|-------------------------------|--------------------------|
| 218 | 1 | X1, X2, X3 |
| 213 | 2 | X1, X2, X3 |
| 208 | 3 | X1, X2, X3 |
| 203 | 4 | X1, X2, X3 |
| 198 | 5 | X1, X2, X3 |
| 192 | 6 | X1, X2, X3 |
| 187 | 7 | X1, X2, X3 |
| Sec. Volts | Secondary Lines Connect To | |
| 480 | H1, H2, H3 | |
| 277 | Between H0 and H1 or H2 or H3 | |
| 1 Phase | | |

Figure 24

