

# TALON

## Rainproof Combination Metering

Catalog Number

**LG0202B1100JLC**  
**LG0202L1125JLC**

Enclosure  
**Type 3R**


Panelboard Rating: 125 Amps Max - See Breaker Rating  
120/240V~, 1 Phase, 3 Wire ; 208Y/120V~, 1 Phase, 3 Wire  
Meter Socket Rating: 125 Amps Continuous

For installation by a qualified person in accordance with all local electrical codes and/or the National Electrical Code.®

### Suitable Only For Use As Service Equipment.

For Overhead or Underground Service.

### Use 60/75°C Copper or Aluminum Conductors.



TERMINAL	WIRE SIZE	TORQUE
A, B	#6 - 350 kcmil	375 lb-in
N1	#6 - 350 kcmil	375 lb-in
Branch Breaker	See Markings on Breaker	
Neutral/Ground Bar Slotted Scws	#14 - 1/0 AWG	50 lb in

Use with Siemens QP circuit breakers, 125 Amps Max.

Circuit breaker trip position is indicated by handle position midway between ON and OFF. To reset, move handle to OFF position then turn ON.

#### Short Circuit Current Rating (Wattour Meter not included in short circuit rating)

This panelboard has a short circuit rating of 10,000 Amps RMS symmetrical, 120/240V~.

#### CONDUIT HUBS (RX Type)

TRADE SIZE	CATALOG No.
1-1/4 INCH	EC38597 or H38597-2
1-1/2 INCH	EC38598 or H38598-2
2 INCH	EC38599 or H38599-2
2-1/2 INCH	EC38600 or H38600-2
Hub Cover Plate	EC38595 or H38595-1

**Warning:** This equipment has been designed for use only with Siemens Type QP circuit breakers. Use of other circuit breakers could result in personal injury or property damage and will void the warranty.

**Important:** Do not allow petroleum based (hydrocarbon) sprays, chemicals, solvents or any paint to contact interior components. Petroleum based chemicals can cause degradation of electrical insulating materials.

49311886

Siemens Industry, Inc. Norcross, Georgia U.S.A.

D

40901258 0101 Rev.A

® The National Electrical Code is a registered trademark of the National Fire Protection Association.

© 2015 Copyright Siemens Industry, Inc.