SIEMENS Ingenuity for life



PAC3200 Power Meter

Reliable and precise monitoring of electrical power systems

The PAC3200 is a powerful compact power monitoring device that is suitable for use in industrial, government and commercial applications where basic metering and energy monitoring is required. The meter may be used as a stand alone device monitoring over 50 parameters or as part of an industrial control, building automation or global power monitoring system.

Metering and monitoring applications range from simple analog volt and amp meter replacements to stand-alone sub billing or cost allocation installations with multiple tariffs. The PAC3200 can also be used to support LEED certification and provide the needed energy metering data for federal/local government energy reduction programs.

The PAC3200 provides open communications using Modbus RTU/TCP, PROFINET and PROFIBUS-DP protocols for easy integration into any local or remote monitoring system. Simple configuration of the meter can be done from the front display or by using a PC with SENTRON powerconfig setup software, supplied with the meter.



Full Graphic LCD Display to indicate:

- Display title or designation of the displayed measurements
- Phase
- Measured value Unit
- Labeling of function keys



Example of operating menu:

The texts can be displayed in several languages, which can be selected directly on the device. The large graphic LCD display facilitates reading even from a distance. For optimum visibility even in poor light conditions the PAC3200 comes with a gradually adjustable background illumination.


When, where and how much power is consumed?

PAC3200 makes consumption apparent

To accomplish a sustainable reduction of power costs, you must first analyze the electrical system's current consumption and power flows. The PAC3200 power meter precisely and reliably delivers the required information of power values to put you on the path to reduce your power cost.

Applications summary

- Replace multiple analog meters
 An ideal replacement for analog meters.
 Use it for stand-alone metering in custom panels, switchboards, switchgear, gensets, motor control center and UPS systems, PDU, RPPs, etc.
- Basic Metering
 The PAC3200 offers high-accuracy power, energy and demand measurements.



1 DI and 1 DO for remote switching, and DI also for kWh, kVAh, kvarh pulse measurement

for voltage and current measuring, control power (available with compression terminals)

- Cost allocation / Energy monitoring Perfect for monitoring right down to the tool level, the meter can help monitor cost centers, identify opportunities for demand control and check energy consumption patterns.
- Automation integration
 Monitor critical equipment processes and tie directly to the Siemens family of PLCs and automation networks.
- Sub-metering
 Low cost, high accuracy and simple retrofit installation enables economical measurement of commercial and residential tenant space. Integrate the PAC3200 with existing energy management systems and RTUs. Reduce energy consumption by eliminating previously uncontrolled expenses.

These revenue accurate values can be used for bill verification, monitoring backup power on critical systems and offering cost-effective energy solutions.

Power management and PAC3200

The PAC3200 can easily be integrated into a power management system using Modbus TCP (standard), Modbus RTU (option), PROFINET (option) or PROFIBUS. With communication, the PAC3200 transmits measured values to the supervisory systems, where the data can be further processed for display and control.

Siemens offers a low cost Powermanager or enterprise level WinPM.Net power monitoring software which can provide easy integration to the PAC3200 meter. Powermanager or WinPM.Net provide standard overview displays allowing detailed analysis of the electrical power, which allows for easy allocation of power consumption and cost. Additionally, unexpected operating conditions can be detected on a timely basis.

 Languages included as standard in the meter are English, German, French, Spanish, Italian, Portuguese, Polish, Turkish, Russian and Chinese.

Functional features

Instantaneous values			
Voltage	Phase-phase / phase-neutral		√
Currents	Per phase		· ✓
Apparent, active and reactive power	Per phase and total	→	
Power factor	Per phase and total	▼	
	4564 Hz	v ✓	
Frequency			
THD for voltage and current	Per phase		√
Min. / max. values	Voltage – phase-phase, phase-neutra Current / Power / Power factor / THD Frequency Three phase average voltage and cur	√	
Average values	Voltage – phase-phase, phase-neutra Voltage min. / max. for phase-phase- Current Current min. / max.	✓	
Energy measurement			
Active energy	Import / export; high / low tariff		√ √
Reactive energy	Positive / negative; high / low tariff		√ √
Apparent energy	High / low tariff		✓
Energy demand per measuring period	Three phase average rating for active	and reactive power	1 to 60 min.
n. / max. rating values within e measuring period			✓
Meter running counter	Uptime in hours	✓	
Universal counter	Pulse counting of external devices lik	e water, gas, etc.	✓
Measurement accuracy			
Voltages			±0.3%
Currents			±0.2%
Power factor and power			±0.5%
Active energy			Class 0.5S in acc. with IEC 62053-22 / ANSI 12.20 class 0.5
Reactive energy			Class 2 according to IEC61557-12 and/or IEC62053-23
Monitoring functions			
Set point monitoring	V, I, power, VAR, VA, Freq. THD, PF		Up to 6 values
Simple logic functions for alarming	Alarm via digital		Output or software
Phase unbalance	Voltage and / or >< current		✓
Communication			
Ethernet	Integrated		10 Base-T (10 Mbit/sec)
Modbus TCP	Integrated RJ45 port		10 Base-T (10 Mbit/sec)
PROFIBUS DP expansion module	Optional • Parameterization via device front or with SENTRON powerconfig software • Transition of data via GSD file	Support of all baud rates from 9600 BPS to 12 MBPS (9.6 Kbit/ sec to 12 Mbit/sec)	
Modbus RTU expansion module	Optional • Parameterization via device front or with SENTRON powerconfig software • Transition of data via MODBUS register based points	• Support of all baud rates of 4800, 9600, 19.2K and 38.4K BPS (4.8 / 9.6 / 19.2 and 38.4 kB/sec	
Switched Ethernet Expansion Module (Supports PROFINET and Dual RJ45 Ethernet Ports)	Optional • Parameterizatio via device front or with powerconfig software • Transition of data via GSDML file	Support of 10 and 100 Mbit/s baud rates	

Functional features (continued)

Functional reatures (continued)	
Inputs / Outputs	
Input voltage / at digital input • initial value for signal<1>-recognition • at DC / rated value	13 V 24 V
Full-scale value for signal <0> recognition	8 V
Number of digital outputs	1
Number of digital inputs	1
Digital output version	Switching or pulse output function
Input current / at digital input	
• for signal <1>	7 mA
Output current • at digital output / with signal <0 > / maximum • at digital output / for signal <1 > / minimum • at digital output / for signal <1 > / maximum • at the digital outputs / at DC / maximum	0.2 mA 27 mA 27 mA 100 mA
Output delay / at digital output • for signal <0> to <1> / maximum • for signal <1> to <0 > / maximum	5 ms 5 ms
Operating voltage / as output voltage / at DC / maximum permissible	30 V
Property of the output / Short-circuit proof	Yes
Input delay time / at digital input • for signal < 0 > to < 1 > / maximum • for signal < 1 > to < 0 > / maximum	5 ms 5 ms
Internal resistance / at the digital outputs	55 Ω
Measuring category / for digital signals	CATII
Switching frequency / at digital output / maximum	17 Hz
Measuring inputs Outer conductors and neutral conductors internal resistance / for voltage measurement	1.05 ΜΩ
Measurable supply voltage • between (PE)N and L / at AC / minimum • between (PE)N and L / at AC / maximum • between (PE)N and L / at AC / maximum rated value • between the outer conductors / at AC / minimum • between the outer conductors / at AC / maximum • between the outer conductors / at AC / maximum	40 V 480 V 400 V 70 V 831 V 690 V
Voltage measuring range extension / with external voltage transformers	Yes
Current measuring range extension / with external current transformers	Yes
Measuring category / for voltage measurement	CATIII
Supply voltage / between the outer conductors / at AC / maximum permissible	831 V
Consumed active power / for current measurement / per phase	115 mW
Continuous current / at AC / maximum permissible	10A
Measuring category / for current measurement	CATIII
Zero suppresion / for current measurement	0.110 %
Relative measurable current / at AC • minimum • maximum	1 % 120 %
Measuring procedure / for current measurement	TRMS
Measurable current / 1 / at AC / Rated value	1 A
Short-time current resistance (lcw) / limited to 1 s / rated value	100 A

Functional features (continued)

Standard inputs / outputs			
Integrated digital input	24 Vdc / 7 mA		1, dry contact, requires external power
Integrated digital output	30 Vdc max. / 10-27 mA; 100 mA max.		1
General			
Password protection			✓
Technical data			
Two-quadrant (import) / four-quadrant (import and export) measuring			4Q
Measurement types			1 ph, 2 ph or 3 ph
Applicable for network type			TN, TT, IT
Sampling rate	64 samples / cycle	at 60Hz	
Measured voltage	Direct connection up to max. delta/wye without transformer		690 V / 400 V (CAT III)
Current inputs	Settable on device		1A or 5A nominal
Power supply	AC/DC DC only		95240V AC (±10%) / 110340V DC (±10%) 2265V DC (=±10%)
Degree of protection	Front Rear		IP65, for UL IP54 IP20, NEMA 1A
Operating temperature	°C / °F		-10+55 <i>/</i> +14+131
Display	Type Resolution (pixels)		Background-illuminated graphic LCD 128 x 96
Text displays	Resolution (pixels)		Multilingual
Optional ports	1		One port is available for optional modules
MTBF	ı		185.8 Years
Connections			105.0 Tears
Type of electrical connection • at the measurement inputs for voltage • of the fast Ethernet interface		screw-type terminals RJ45 (8P8C)	
Mechanical Design			
Height		96 mm	
Height / of the display		54 mm	
Width		96 mm	
Width			
• of the display		72 mm	
Depth		56 mm	
Mounting position		vertical	
Installation depth		51 mm	
Mounting type / panel mounting		Yes	
Net weight		451 g	
Environmental conditions			
Installation altitude / at height above sea level / maximum		2 000 m	

Function features (continued)

Function reatures (continued)	
Standard	
• for EMC for industrial sector	IEC 61000-6-2 respectively IEC 61326-1:2005, table 2
• for EMC against unloading	IEC 61000-4-2: 2001-04
• for EMC against high frequency fields	IEC 61000-4-3: 2006-02
for EMC against conducted LF disturbance variables (industry)	IEC 61000-6-4, Group 1 Klasse A / CISPR11 Gruppe 1 Klasse A FCC Part 15 Subpart B Class A
• for EMC against conducted disturbance variables via HF fields	IEC 61000-4-6: 2001-12
• for EMC against magnetic fields with power engineering frequencies	IEC 61000-4-8: 2001-03
• for EMC against quick, transient electrical disturbances	IEC 61000-4-4: 2005-07
• for EMC against voltage drops and interruptions	IEC 61000-4-11: 2004-03
• for EMC against surge voltages	IEC 61000-4-5: 2001-12
• for free fall	IEC 60068-2-32: 1975
• for pulse emitter	according to IEC62053-31
• for cyclic, environmental damp heat check	IEC 60068-2-30
• for environmental coldness check	IEC 60068-2-1
• for environmental dry heat check	IEC 60068-2-2
Relative humidity / at 25 $^{\circ}$ C / without condensation / during operation	
• minimum	5 %
• maximum	95 %
Ambient temperature	
• during operation / minimum	-10 ℃
during operation / maximum	55 °C
during storage / minimum	-25 ℃
during storage / maximum	70 °C
Certificates	
Certificate of suitability	
as EC declaration of conformity	IEC 61010-1: 2001 (2nd Ed.) with Corr. 1, EN 61010-1: 2001 (2nd Ed.) and DIN EN 61010-1:2002 with "Berichtigung 1"
• as approval for Canada	UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
• as approval for USA	UL 61010-1, 2nd Ed. CAN/CSA-C22.2 NO. 61010-1-04
Reference identifier / acc. to DIN EN 61346-2	P

General Product Approval

Declaration of Conformity





Order information

Product	Order Number ¹⁾
PAC3200 compression terminals not suitable for use with ring tongue terminals, AC/DC	7KM2112-0BA00-3AA0
PAC3200 compression terminals not suitable for use with ring tongue terminals, DC only for 22-65V DC extra low voltage power supply	7KM2111-1BA00-3AA0
PAC PROFIBUS DP expansion module	7KM9300-0AB01-0AA0
PAC MODBUS RTU expansion module	7KM9300-0AM00-0AA0
Adapter Plate for 4700/4720 meter cutout	93-47ADAPTER
SITOP Power Supply AC 99-264VAC, 24 VDC, 0.5A	6EP1331-5BA00
PAC3200 In / Idiff, analog expansion module	7KM9200-0AD00-0AA0

¹⁾ Omit dashes from part numbers when ordering except on 93-47ADAPTER.

Published by Siemens Industry, Inc. 2018.

Siemens Industry, Inc. 5400 Triangle Parkway Norcross, GA 30092

For more information, please contact our Customer Support Center.
Phone: 1-800-333-7421

E-mail: pds.techsupport.us@siemens.com

usa.siemens.com/pds

Order No.: PCPM-P3200-0418

Printed in U.S.A.

© 2018 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.