



3C3Y030D16 - Three-Phase Ventilated-USA-DOE

PRODUCT DETAILS			
KVA:	30.00	Enclosure:	NEMA 3R Ventilated
UPC#:	804766143489	Phase:	Three-Phase
Line Voltage	240V-Delta	Load Voltage	208Y/120V
E/S Shielded:	No	Windings:	Aluminum
Temp. rise:	150°	Hertz:	60 Hz
Taps:	2 - 2.5% FCAN; 4 - 2.5% FCBN	Approvals:	UL, cUL, DOE
		Wall Bracket:	TWB75J
WEIGHT AND DIMENSIONS			
Height(A):	25.00"	Width(B):	22.00"
Depth(C):	22.00"	Shipping Weight:	330 lbs
ADDITIONAL INFORMATION			
How to Buy: Contact Siemens Distributor, Siemens Sales Rep or Configure in COMPAS Configuration Tool			


Wiring Diagram

Dimensional Drawing

T240B Wiring Diagram & Connections*

Wiring Diagram

Primary: 240 Volts Delta
Secondary: 208Y/120 Volts



SECONDARY

Connections		
Primary Volts	On Each Coil Jumper Taps To	Primary Lines Connect To
252	1	H1, H2, H3
246	2	H1, H2, H3
240	3	H1, H2, H3
234	4	H1, H2, H3
228	5	H1, H2, H3
222	6	H1, H2, H3
216	7	H1, H2, H3
Sec. Volts	Secondary Lines Connect To	
208	X1, X2, X3	
120	Between X0 and X1 or X2 or X3	
1 Phase		

Figure 24

